



Drain sensor

DBS1006 Series

High-reliability level sensor detects the entry of drainage into the pneumatic circuit.


- Port size: G1/2"



Specifications

Item		DBS1006-15-AC200V
Port size	Drain inlet	G1/2"
	Drain outlet port	G1/4"
Working conditions	Working fluid	Drain contained in compressed air
	Ambient temperature °C	1 to 60
	Working pressure MPa	0 to 1.6
Electro specs	Power supply	Single phase 200 VAC 50/60 Hz
	Max. power consumption	8.0VA
Alarm contact capacity		max. 250 VAC/1 A, max. 30 VDC/1 A, min. 5 VDC/10 mA
Degree of protection		IP65
Weight	kg	0.65

Applications



dimensions



- DBS1006-15

