

Pneumatic, Vacuum and Auxiliary Components
Catalog No. CB-024SA

Bracket

B-W/B Series

Joiner

J-W Series

P4 compliant
as standard



P4
Series

Pneumatic actuator
Hand/Chuck
related products
Cylinder
Switch

Vacuum components
Pneumatic valves


Clean air components
Speed controller
Fitting
Auxiliary valve
Silencer
Tube

Gas generator
Fluid control components

Motor specification
Electric actuator
Motorless specifications

Dimensions and applications

T-bracket set



• Material: Polyamide resin (B110-W)
Aluminum alloy die-casting (B310 to B810-W)
Painting (B310 to B810-W)


- Model No.: B110-W/B310-W/B410-W/B810-W
- Applications



Note: Select B410-W when using the 3000-W Series and 4000-W Series combined.

Model No.	Compatibility	A	B	C	D	E	F	G	H	I	J	K	Weight (kg)
B110-W	1000 Series	45	35	10	100	5.5	7.5	16	25	7.5	JASO-2013	40	0.024
B310-W	2000 Series	60	45	10	125	7	14	22	27	7	JISB2401-P21	45	0.086
	3000 Series												
B410-W	4000 Series	60	45	10	125	7	14	22	37	7	JISB2401-P21	55	0.094
B810-W	6000 Series	70	50	15	150	9	14	27	37	8	AS568-127	65	0.169
	8000 Series												

C-bracket



• Material: Steel
Zinc plated


- Applications

- Model No.: B120/B220/B320/B420/B620/B820
- Attachment: BW



Model No.	Compatibility	A	B	C	D	E	F	G	H	I	J	K	L	Weight (kg)
B120	1000 Series	44	68	40	t2.0	10	6.5	35	8.5	61.5	40	60	ø19.5	0.1
B220	2000 Series	28	54	50	t2.3	10	7	33	8	63	45	69	17.3	0.15
B320	3000 Series	34.5	67	63	t2.3	16.5	7	45	8.5	75.5	45	69	ø21.7	0.17
B420	4000 Series	55	84	80	t2.3	14.0	7	45	8.5	75.5	55	79	ø21.7	0.21
B620	6000 Series	68	104	90	t2.3	16	9	54	11	97.5	60	97	ø35	0.34
B820	8000 Series	68	104	100	t2.3	16	9	50	11	93.5	65	102	ø35	0.36

L-bracket



• Material: Steel
Zinc plated

- Applications


- Model No.: B130/B230/B330/B430
- Attachment: B3W

Loosen the mounting nut to remove the knob. After inserting the L-bracket, fix it by the mounting nut. Press the knob in manually after fixing.



Model No.	Compatibility	A	B	C	D	E	F	G	H	I	J	Other	Weight (kg)
B130	1000 Series	44	68	10	6.5	16	24.5	45	40	59	ø26.5		0.04
B230	2000 Series	28	54	10	7	18	26	52	45	69	38		0.06
B330	3000 Series	34.5	67	16.5	7	17.5	26	58 (63.5)	45	76	ø40	Values in () are for W3000/3100	0.07
	4000 Series												
B430	6000 Series	55	84	14	7	17.5	26	58	55	94	ø47		0.11
	8000 Series												

Joiner set



• Material: Polyamide resin (J100-W)
Aluminum alloy die-casting (J400 to J800-W)
Painting (J400, J800-W)

- Applications

- Model No.: C1000-J100-W
C4000-J400-W
C8000-J800-W

Model No.	Compatibility	A	B	C	D	E	Weight(kg)
C1000-J100-W	1000 Series	10	36	26	M3.5	JASO-2013	0.011
C4000-J400-W	2000 Series	21	44	32	M5	JIS B2401-P21	0.036
	3000 Series						
	4000 Series						
C8000-J800-W	6000 Series	26	65	50	M6	AS568-127	0.094
	8000 Series						