

タウ τ DISC[®] Servo Motor ND-S series

Standard

Rated torque: 3.4 ~ 500 N·m



◎ Popular standard Type pursuing cost performance. Suitable for various applications.

◎ Compact design. Higher torque density and optimized thermal structure and magnetic circuitry have reduced the volume ratio by 25% from previous models (ND and ND-c Series).



Ideal for converting the AC servo motor + reducer mechanism into a direct drive system

- Application examples**
- Wafer carrier devices/ ■ Food carrier devices/ ■ Filling machines/ ■ Capping machines/ ■ Roll feeders/
 - Laser beam machines/ ■ Laminating machines/ ■ FPD pasting machines/ ■ Die cutters/
 - Screen printing machines/ ■ Contact and non-contact inspection machines/ ■ Index tables

**Index drive and tightening drive :
Index machines, capping machines, etc.**

[Index machines]

- High-precision, flexible indexing
- Simple structure
- Quietness
- Improved maintainability

[Capping machine]

- The hollow structure makes the device simpler
- Faster response

**Rotary drive :
Die cutters, printing machines, etc.**

- Speed stability
- Simple structure
- Improved maintainability

**Transport robot drive :
Wafer transport robots, etc.**

- The hollow structure makes the device simpler.
- Quietness
- Improved maintainability

**Feeding and winding drive (roll-to-roll application devices) :
Laminating machines, coaters, surface inspection machines, etc.
Replacing a powder clutch or brake**

- Speed stability
- Quietness
- Improved maintainability
- Easy adjustment

**Table drive :
Laser beam machines, various processing machines, etc.**

- Stable operation
- High precision
- Improved maintainability

τ DISC[®] ND-s HS

series Rated torque: 8~24 N·m

High-speed rotation



- ◎ High-speed rotation specification model of the ND-s Series.
- ◎ Pursuing compactness and high-speed operation.
- ◎ Lineup of motors whose rated rotation speed ranges from 11 to 15 rps (660 to 900 rpm).



Ideal for applications that require high-speed and high-precision operation

Application examples

- Die bonders
- Sorters
- Spin coaters
- Spin washers

High-speed positioning examples

90-degree positioning time: **36 msec**


180-degree positioning time: **60 msec**

Accuracy at the arm tip: $\pm 4 \mu\text{m}$ (completion range: ± 10 pulses)

- Used motor Type and specifications
ND140-95-LS-HS Type
Rated/maximum torque: 15/37 N·m
Rated rotation speed: 11 rps
Rotor moment of inertia: 0.00134 kg·m²
Detection pulse: 1,600,000 ppr
- Load specifications
Arm load (double edge): Weight of 0.086 kg
(208 mm from center to tip)
Load inertia moment ratio: Approx. 0.5 times


High-speed pick-and-place drive : Die bonders and sorters

- Faster operation
- High-precision positioning
- Simple structure and space saving



Spin drive : Spin coaters, spin washers, etc.

- Speed stability
- Simple structure
- High acceleration



τ DISC[®] Servo Motor DD-s series

High rigidity and high precision


Rated torque: 10~2000 N·m

- ◎ High-rigidity Type pursuing high rigidity and high precision.
- ◎ Significant improvement in moment rigidity, axial rigidity, and rotor torsional rigidity.
- ◎ Pursuing positioning accuracy and run out accuracy.
- ◎ Enabling stable operation even at the inertia ratio of 2,000 times.*

* They are not guaranteed values. They depend on the installation status, operation conditions, mechanical rigidity, etc.



Ideal for applications that require stable operation for a load with large inertia



Application examples

- FPD pasting machines/ ■ FPD inspection machines/ ■ Screen printing machines/
- PE printing machines/ ■ Precision processing and measurement machines/
- Wafer dicing machines/ ■ Wafer processing machines/ ■ Wafer inspection machines/
- Scribes/ ■ Die casting machines/ ■ Packaging machines/ ■ X-ray analyzers/
- Surface polishing machines/ ■ Chamfering machines


High-precision roll drive :
Roll coaters, PE printing machines, etc.

- High-precision positioning
- Speed stability

Large inertia load turning drive :
FPD turning, alignment, and inspection machines

- Stable operation for a load with large inertia
- High-precision positioning
- Simple structure and space saving

▼ Positioning operation waveforms when the inertia ratio is 527 times



【Used motor Type and specifications】 DD160-146-LS Type

- Rated/maximum torque: 27/62.5 N·m
- Rotor moment of inertia: 0.0074 kg·m²
- Load specifications (disk) Load inertia moment: 3.9 kg·m²
(527 times larger than rotor moment of inertia)
- Positioning operation: 90°
- Paired servo driver: VPH-HA Type

* These values may vary depending on the load setting condition and other factors. They are not guaranteed values.

Ball screw drive :
Die casting machines, servo presses, etc.

- High-response operation
- The hollow structure makes the device simpler
- Improvement in environmental friendliness and safety due to not using a hydraulic system

Continuous rotation drive :
Surface polishing machines, chamfering machines, etc.

- High-precision positioning
- Speed stability

τDISC[®] HD-S

series

Rated torque: 27~68 N·m


High response

- High-response Type pursuing high-speed operation.
- World's top level high response performance with a high-torque, low-inertia structure.



Ideal for applications that require a small operation angle and high-speed operation

▼ Positioning operation waveform at 22.5° Positioning time: 18.2 msec



18.2 msec

- Used motor Type and specifications
HD140-160-LS Type
Rated/maximum torque: 27/67.5 N·m
Rotor moment of inertia: 0.0027 kg·m²
- Load specifications (disk)
Load weight: 0.79 kg
Load inertia moment: 0.00297 kg·m²
(1.1 times larger than rotor moment of inertia)
- Positioning operation: 22.5°
Completion range: ±10 pulses
(Load disk circumference conversion: ±1.5 μm)
Dwell time: 50 msec
- Paired servo driver:
VPH-HA Type


* These values may vary depending on the load setting condition and other factors. They are not guaranteed values.

Application examples ■ Test handlers/ ■ Taping machines/ ■ Appearance inspection machines/
■ Automotive parts testing machines/ ■ Torque testing machines/ ■ Various testing machines/ ■ Vibration generators

High-speed index drive :

High-speed test handlers and taping machines

High-speed indexing operation for 22.5 degrees




- Faster operation
- High-speed positioning
- Simple structure and space saving

τDISC

Testing machine drive :

Torque testing machines, material testing machines, durability testing machines, etc.

- High-response operation
- Space savings and improved quietness
- Improvement in environmental friendliness and safety



τDISC

In addition to the standard τDISC lineup, we can offer custom-made features, such as those shown below, to meet your needs for special specifications.

Custom Made

Custom Made

1

Improved speed stability

Based on the ND250-s and ND400-s Types of the ND-s Series, speed stability is improved by reducing motor torque ripples, mounting a high-precision encoder, etc.

Speed variation

[At speed of 2 rpm]

±0.1%

Actual value obtained under our measurement conditions


Custom Made

2

Built-in motor

[Example]

We provide an air bearing or ball bearing spindle with a rotor and a stator built in it or only a rotor and a stator.




<div style="border: 1px solid gray; padding: 5px; text-align: center;"> <p>Custom Made</p> <h1 style="font-size: 48px; margin: 0;">3</h1> </div> <h3 style="margin: 5px 0 0 0;">Anti-fretting specifications</h3>	<div style="border: 1px solid gray; padding: 5px; text-align: center;"> <p>Custom Made</p> <h1 style="font-size: 48px; margin: 0;">4</h1> </div> <h3 style="margin: 5px 0 0 0;">Improved positioning accuracy and rotation accuracy</h3>	<div style="border: 1px solid gray; padding: 5px; text-align: center;"> <p>Custom Made</p> <h1 style="font-size: 48px; margin: 0;">5</h1> </div> <h3 style="margin: 5px 0 0 0;">Improved torque accuracy</h3>
<div style="border: 1px solid gray; padding: 5px; text-align: center;"> <p>Custom Made</p> <h1 style="font-size: 48px; margin: 0;">6</h1> </div> <h3 style="margin: 5px 0 0 0;">Improved flatness and parallelism</h3>	<div style="border: 1px solid gray; padding: 5px; text-align: center;"> <p>Custom Made</p> <h1 style="font-size: 48px; margin: 0;">7</h1> </div> <h3 style="margin: 5px 0 0 0;">Increased rotation speed and torque</h3>	<div style="border: 1px solid gray; padding: 5px; text-align: center;"> <p>Custom Made</p> <h1 style="font-size: 48px; margin: 0;">8</h1> </div> <h3 style="margin: 5px 0 0 0;">Anti-dust specification</h3>
<div style="border: 1px solid gray; padding: 5px; text-align: center;"> <p>Custom Made</p> <h1 style="font-size: 48px; margin: 0;">9</h1> </div> <h3 style="margin: 5px 0 0 0;">Material and appearance changes</h3>	<div style="border: 1px solid gray; padding: 5px; text-align: center;"> <p>Custom Made</p> <h1 style="font-size: 48px; margin: 0;">10</h1> </div> <h3 style="margin: 5px 0 0 0;">Wider middle hole diameter and change in the mounting shape</h3>	<div style="border: 1px solid gray; padding: 5px; text-align: center;"> <p>Custom Made</p> <h1 style="font-size: 48px; margin: 0;">11</h1> </div> <h3 style="margin: 5px 0 0 0;">Connector and cable changes</h3>

We can support any special shipping inspection.

By conducting a dedicated inspection not supported as standard, it is possible to check whether your required specifications are met, regarding the specifications not provided as such.

- Positioning accuracy measurement using laser length measurement and a high-precision encoder
- Table rotation axis run out accuracy using a true sphere
- Load displacement amount measurement
- Speed stability, output torque accuracy, etc.

* For information about the availability of customization, contact our sales staff.
 * Our website offers "List of Practical Examples of Custom-Made Direct Drive Motors".
<https://www.nikkidenso.co.jp/product/custom/>

VPH Series

Developed exclusively for direct drive.
Maximizes the motor performance.
Output capacity 100 W ~ 15 kW



Lineup

◎ VPH-HA Type	I/O specification	Speed command operation, torque command operation, and pulse train command operation, and built-in command operation	
◎ VPH-HB Type	SSCNET III/H specification	Supports SSCNET III/H and SSCNET III. Speed command operation, torque command operation, and position control operation	
◎ VPH-HC Type	CC-Link specification	Supports CC-Link (Version 1.10) communication. Speed command operation, torque command operation, and pulse train command operation, and built-in command operation	
◎ VPH-HD Type	EtherCAT specification	Supports EtherCAT communication (CIA402 drive profile). Speed command operation, torque command operation, and position control operation	
◎ VPH-HE Type	MECHATROLINK-III specification	Supports MECHATROLINK-III communication. Speed command operation, torque command operation, and position control operation	

Features

Superb speed stability

Significant reduction in torque ripples

Reducing torque ripples improves speed stability even more.
(Reduced by 20% from the conventional model.)

Easy tuning even for a load with large inertia

Automatic feedback filter setting function

Since the feedback filter appropriate for the load is automatically set during auto tuning, the speed detection ripples are reduced, allowing easy tuning even for a load with large inertia. Smooth operation can be achieved easily.

Improved stability during stop

Filtering function during stop

Improved torque accuracy during stop

Vibration of a load with large inertia during stop is reduced.

Enhanced low-speed gain switching function

Not only speed but also other items, such as deviation and the presence or absence of a command, can be set as the conditions for switching between normal gain and low-speed gain.

Smooth operation reduces the positioning time.

Two-stage, s-curve acceleration and deceleration control function

Making the torque waveform a quadratic curve significantly eases the impact at the time of acceleration and deceleration and reduces the positioning time without causing vibration even when the acceleration and deceleration is shortened.

System support tool

The enhanced adjustment, monitoring, operation, analysis, and editing functions assist in mechanical system matching and enable efficient start-up.

Analysis functions

Oscilloscope function

- The servo data of up to 11 channels can be displayed in real time.
(* Data resolution: 0.4 ms or more; Only IO setting for Channel 4 and later)
- The motor load ratio during repeated operations can be displayed easily.
- The normal trigger function makes it easy to identify changes before and after adjustment.


Frequency response measurement function

- By measuring the frequency response of the mechanical system through automatic motor excitation, the mechanical resonance filter can be set easily.


Frequency spectrum measurement function

- By finding the mechanical resonance point through the measurement of the frequency spectrum during the operation, the mechanical resonance filter can be set easily.


Oscilloscope screen



Frequency response measurement screen



Frequency spectrum measurement screen



Status display screen

Status display

Status display function

- Various operation information, such as the actual motor operation speed, actual torque command, and current position, is displayed in real time.
- The alarm history, device information, and so on are displayed.

Input/output signal status display function

- The input and output signals can be checked easily during the start-up operation.

Device monitoring function

- The memory area inside the driver can be displayed and edited in real time.

No.	Item	Data	Unit
C001	Actual operation speed of motor	-1799.557	deg/sec
C002	Operable max. speed	1800.000	deg/sec
C003	Analog speed command value	0.181	deg/sec
C004	Actual motor operating rotational speed	-299	rpm
C005	Actual torque command value	-8.8	%
C006	Peak torque command value	42.0	%
C007	Analog Torque command value	0.0	%
C008	Load factor of motor	8.8	%
C009	+ Torque limit value	250.0	%

Data Editing Software

* Download the latest version of the VPH Series system support tool from our website.
<https://www.nikkidenso.co.jp/systemtool/>

Data editing

Parameter editing function

- The parameters such as gain, filter, command, and signal are grouped to make the editing work easier.


Program editing function

- Programs can be created and edited using the operation commands in internal command mode.

Indirect data editing function

- This function creates and edits the indirect data to be used for program operation.

Parameter editing screen



Remote operation

Switch box function

- Remote operation can be done easily from a PC with the master controller disconnected.

Switch box screen



Automatic servo gain adjustment function "NiEAT"

New functions of the system support tool (For details, refer to p.13 to p.14.)

- Interactive initial setup is supported for the major control method.
- Enter selection conditions to the direct drive motor selection calculation tool, and you can have the filter and gain value automatically adjusted until the selection conditions are met.
- A special motor parameter read function has been added. Special motor parameters can be created easily.

NiEAT Nikkidenso
Engineering
Auto Tuning

Supported OS

- Windows 10 32bit/64bit
- Windows 8.1 32bit/64bit
- Windows 7 32bit/64bit

Supported languages

- Japanese, English, and Korean
- Chinese (simplified/traditional)

New!

Automatic servo gain adjustment function

NiEAT

Nikkidensu
Engineering
Auto Tuning

The system support tool features a new function - the automatic servo gain adjustment function "NiEAT"! The formerly difficult task of adjusting the direct drive motor gain is now easy to do!

Comparison between automatic servo gain adjustment of NiEAT and conventional adjustment

Conventional adjustment...

Setting a large number of parameters is cumbersome.

Which do I need to use to drive the motor?


I'm not sure what to set.

How do I know if I'm finished with adjusting the gain waveform?





I don't know how to cope with mechanical resonance.

"NiEAT" solves all these problems!


To start the tool, click the NiEAT button!




The wizard takes you through the adjustment process. All you need to do is make settings according to on-screen instructions!



Input the adjustment conditions and click the Start button, and automatic adjustment will start! There is no need to check the adjustment status by monitoring waveforms or set a filter for the mechanical resonance point by using another function.



The automatic adjustment of the direct drive motor will be complete in 5 minutes or so!



* If NiEAT cannot automatically adjust the motor, you need to make adjustments individually.
 * The NiEAT function does not include adjustments other than the gain adjustment, such as the height and level adjustments for motor parallelism.