



# EBS/EBR Model Selection Check Sheet → CKD (Contact )

Fill in the form and send to the nearest CKD Sales Office. We will respond with the model selection results.

Customer:

Company		Department	
Name		E-mail	
TEL		FAX	

Selecting conditions:

Desired model	(EBS/EBR)-		
Basic specifications	Max. stroke length:	mm, ball screw lead:	mm
Operating conditions	Travel stroke:	mm, travel time:	s
	Set speed:	mm/s	
	Set acceleration/deceleration:	mm/s <sup>2</sup> (set acceleration/deceleration time: s)	
	Repeatability: ±	mm	
Load conditions	Slider		Rod
	Load weight: kg		
	Mounting orientation: Horizontal / wall mounted / vertical / ceiling mounted / other 		Mounting orientation: Horizontal / wall mounted / vertical / ceiling mounted / other 
	Distance from slider and rod center to the center of gravity of load		
	Direction A: mm Direction B: mm Direction C: mm		Direction X: mm Direction Y: mm Direction Z: mm
	Pressing load: No / Yes ( N) Operating / Stopped Direction of the force applied to slider center ( )		
Working environment	Ambient temperature: °C, ambient humidity: %		
	Atmosphere:		
Interface specifications	Parallel I/O / IO-Link / CC-Link / EtherCAT / EtherNet/IP		
Remarks			