


MR10R Series

Working pressure 0.2 MPa, miniature, space-saving.

Attains high analysis accuracy and impressive control of trace amounts of chemical liquids.



Ideal for the dispensing process of analysis equipment.

2, 3-port solenoid valve MR10R series for chemical liquids

that has eliminated metal by using resin and rubber as the materials for wetted parts.

Valve with excellent overall performance **including slimness / space-saving, excellent installability, safe structure, reliability, long service life design.**

10 million times long service life

These test results are based on CKD test conditions.

Volumetric capacity 19μℓ

Washing inside the solenoid valve is easy.
Wasted reagents can also be reduced.

Designed to suppress heat generation

Minimizes the impact on analysis accuracy of coil heat generation, and also implements power-saving.

Piping method 2 types

Select according to your application



● Actuator type



● Direct piping type

2-port valve and 3-port valve have the same shape