

FFLD Series model selection check sheet → CKD(Contact)

Fill in the form and send to the nearest CKD Sales Office. We will respond with the model selection results.

Customers:

Company		Department	
Name		E-mail	
Tel.		Fax	

Selecting conditions:

Desired model	FFLD-		
Basic specifications	Max. stroke length (per side): mm		
Operating conditions	Travel stroke (per side): mm, travel time: s		
	Gripping force(per side): N		
	Open/close speed (per side): mm/s, gripping speed: mm/s		
	Repeatability: ± mm, positioning repeatability: ± mm		
Load conditions	<p>Mounting orientation: Orientation 1 Orientation 2 Orientation 3</p> <p>Orientation 1 / Orientation 2 / Orientation 3 / Others</p>		
	<p>Weight of workpiece: kg Workpiece material:</p> <p>Number of attachments: Attachment material:</p> <p>Attachment length:</p> <p>H: mm</p> <p>L: mm</p>		
	<p>External force on finger: Yes / No</p>		
Working environment	<p>Ambient temperature: °C, Ambient humidity: %</p> <p>Atmosphere:</p>		
Interface	IO-Link		
Remarks			