


LSH-A / LSHL-A·LSHM-A Series







Gripping power performance data LSH-A**D / LSHL-A**D / LSHM-A**D (double acting)

- The gripping power indicates the thrust (for one finger) in the direction of the arrow shown in the figure.
- The gripping power operating in the opening/closing directions against the length (ℓ) of the attachment when the supply pressure is 0.7 MPa or less is shown.







- Open direction (←)
- Closed direction (→)



Closed direction




Open direction









Gripping power performance data LSH-A**S / C (single acting)

- The gripping power indicates the thrust (for one finger) in the direction of the arrow shown in the figure.
- The gripping power operating in the opening/closing directions against the length (ℓ) of the attachment when the supply pressure is 0.7 MPa or less is shown.







- Open direction (←)
- Closed direction (→)



Closed direction



Open direction




LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending
LSH-HP
LSH
FH100
BSA2
BHABHG
LHA
LHAG
HAP
HKP
HCP
HGP
HLF2
HLA/HLB
HLAGHLBG
HLC
HLD
HMF
HMF-G
HMFB
HFP
FH500
HBL
HJL
HMD
HDL
HJD
BHE

LSH-G / LSHL-G / LSHM-G Series







Gripping power performance data LSH-G / F**D / LSHL-G / F**D / LSHM-G / F**D (double acting)

- The gripping power indicates the thrust (for one finger) in the direction of the arrow shown in the figure.
- The gripping power operating in the opening/closing directions against the length (ℓ) of the attachment when the supply pressure is 0.7 MPa or less is shown.







- Open direction (←)
- Closed direction (→)



Closed direction




Open direction




Gripping power performance data LSH-G / F**S / C (single acting)

- The gripping power indicates the thrust (for one finger) in the direction of the arrow shown in the figure.
- The gripping power operating in the opening/closing directions against the length (ℓ) of the attachment when the supply pressure is 0.7 MPa or less is shown.


- Open direction (←→)
- Closed direction (→→)



Closed direction



Open direction




LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending

LSH-HP
LSH
FH100
BSA2
BHABHG
LHA
LHAG
HAP
HKP
HCP
HGP
HLF2
HLA/HLB
HLAGHLBG
HLC
HLD
HMF
HMF-G
HMFB
HFP
FH500
HBL
HJL
HMD
HDL
HJD
BHE


Attachment length

When mounting an L-shaped attachment, use within the range given in the figure at right.







Closed direction









Open direction



Closed direction



Open direction



LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MecHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending

LSH-HP
LSH
FH100
BSA2
BHA/BHG
LHA
LHAG
HAP
HKP
HCP
HGP
HLF2
HLA/HLB
HLAG/HLBG
HLC
HLD
HMF
HMF-G
HMFB
HFP
FH500
HBL
HJL
HMD
HDL
HJD
BHE