





Discontinued some variations

ETS Multi-Axis Series

Sales of ETS-210A to ETS-440A, ETS-530F, 640F
ETS-760G, 870G discontinued.

Series variation

Combinations of multiple axes * Set model No. Check the following table for combinations of axes.
[2-axis combination]

Specifications	Set model No.	Combination	1st axis	2nd axis	1st axis stroke	2nd axis stroke	Page
X · Y 	ETS-210	A	ETS-06-10	ETS-05-10	100 to 800	50 to 350	166
	ETS-430	A	ETS-12-20	ETS-10-20	100 to 1050	50 to 550	
	ETS-440	A	ETS-12-20	ETS-12-20	100 to 1050	50 to 550	
	ETS-650	A	ETS-14-20	ETS-13-20	100 to 1050	50 to 650	
	ETS-760	A	ETS-17-20	ETS-14-20	100 to 1250	50 to 650	
	ETS-870	A	ETS-22-25	ETS-17-20	100 to 1500	50 to 750	
G type (with support guide) 	ETS-760	G	ETS-17-20	ETS-14-20	100 to 1250	200 to 850	204
	ETS-870	G	ETS-22-25	ETS-17-20	100 to 1500	200 to 1050	
X · Z 	ETS-650	P	ETS-14-20	ETS-13-10	100 to 1050	50 to 550	218
	ETS-760	P	ETS-17-20	ETS-14-10	100 to 1250	50 to 650	
	ETS-880	P	ETS-22-25	ETS-22-05	100 to 1500	50 to 950	
Y · Z 	ETS-530	F	ETS-13-20	ETS-10-10	100 to 1050	50 to 350	232
	ETS-640	F	ETS-14-20	ETS-12-10	100 to 1050	50 to 350	
	ETS-760	F	ETS-17-20	ETS-14-10	100 to 1250	50 to 550	

List of servo motors recommended for mounting

Code	Manufacturer	Series	100 W *2 (ETS-05/06/10/12/13 Series)
M	Mitsubishi Electric Corporation	MELSERVO J4	HG-KR13
		MELSERVO J5	HK-KT_13W
M	Delta Electronics Co., Ltd.	ECMA-C *1	ECMA-C10401
M	Sanyo Corporation, Ltd.	SANMOTION R	R2□A04010
Y	YASKAWA Electric Corporation	Σ-V	SGMJV-01
Y	Keyence Corporation	SV	SV-□010
P	Panasonic Corporation	MINAS A5	MSMD01
O	OMRON Corporation	G5	R88M-K10030

Code	Manufacturer	Series	200 W *2 *3 (ETS-10/12/13/14 Series)	400 W (ETS-13/14/17 Series)	750 W *4 (ETS-17/22 Series)
M	Mitsubishi Electric Corporation	MELSERVO J4	HG-KR23	HG-KR43	HG-KR73
		MELSERVO J5	HK-KT_23W	HK-KT_43W	HK-KT_7M3W
M	Delta Electronics Co., Ltd.	ECMA-C *1	ECMA-C10602	ECMA-C10604	ECMA-C10807
M	Sanyo Corporation, Ltd.	SANMOTION R	R2□A06020	R2□A06040	-
Y	YASKAWA Electric Corporation	Σ-V	SGMJV-02	SGMJV-04	SGMJV-08
Y	Keyence Corporation	SV	SV-□020	SV-□040	SV-□075
P	Panasonic Corporation	MINAS A5	MSMD02	MSMD04	MSMD08
O	OMRON Corporation	G5	R88M-K20030	R88M-K40030	R88M-K75030

*Contact CKD for mounting other than the above motors and products of other motor manufacturers.


*1: ECMA series (with brake) cannot be used with built-in mounting.

*2: Contact CKD when using an OMRON motor with ETS-12 built-in mounting.


*3: ETS-10 and 12 200 W cannot be used with built-in mounting. *4: ETS-17 750 W cannot be used with built-in mounting.

2-axis combination load capacity

■ X-Y axes (A type/G type)



■ X-Z axes (P type)



■ Y-Z axes (F type)

