



Attachment

- Material: Iron, engineering plastic



Features

Attachments machined for use with a variety of models are available to match user workpieces.

- Spigot section machined

Troublesome reference section (spigot section) machined.


Wide series variation to select according to workpiece shape and dimension.

- 2 types of material for attachment


Iron (S50C) and engineering plastic (MC nylon) are available for optimum selection according to material and working condition of workpiece.

Compatible model for standard attachment

CK type




CKA/CKG type




Attachment applications

Chuck applications


Soft jaw




Compact workpiece




Large workpiece



For large and small workpieces



For inner tensive large and small workpieces



How to order (Note: When ordering repair parts, 1 pc. is provided.)

CKA - **Y1** - **610**


A Model **B** Material **C** Attachment No.

A Model		B Material		C Attachment No.	
Code	Description	Code	Description	Code	Compatibility
CKG	3-way jaw bearing chuck	Y1	Material S50C	510	CKG-16CS,CKA-15CS,CKF-15CS
CK	3-way jaw long stroke chuck	Y2	Material MC nylon	520	CKG-25CS,CKA-20CS,CKF-20CS
CKA	3-way jaw thin chuck			530	CKG-32CS,CKA-25CS,CKF-25CS
CKF	Hollow chuck			540	CKG-40CS,CKA-30CS,CKF-30CS
				610	CKG-25CS,CKA-20CS,CKF-20CS
				620	CKG-32CS,CKA-25CS,CKF-25CS
				630	CKG-40CS,CKA-30CS,CKF-30CS
				710	CKG-50CS,CKA-40CS,CKF-40CS
				720	CK-1CS
				730	CK-1.5CS
				740	CK-2CS
				750	CKA-50CS
				760	CKA-60CS
				770	CKA-70CS

Dimensions



● 510 to 540 (For external diameter chuck)




*1 Y1 : Material S50C

*2 Y2 : Material MC nylon

Code		A	B	C	D	E	F	øG	H	I	J	K	øL	M	Weight (g)	
Attachment No.	Compatibility														Y1*1	Y2*2
510	CKA-15CS CKG-16CS CKF-15CS	17.5	25	3.5	2.5	2	20	6	8	6	3.5	7	3.5	1	17	5
520	CKA-20CS CKG-25CS CKF-20CS	24	30	4.5	3.5	2	24.5	8	12	8	4.5	9	4.5	1.5	45	11
530	CKA-25CS CKG-32CS CKF-25CS	31	40	4.5	3.5	3	34.5	8	14	10	4.5	10	4.5	1.5	103	21
540	CKA-30CS CKG-40CS CKF-30CS	37	50	6	4.5	4	43	9.5	14	10	6	13	5.5	2	136	30

● 610 to 630 (For internal diameter chuck)




*1 Y1 : Material S50C

*2 Y2 : Material MC nylon

Code		A	B	C	D	E	F	øG	H	I	J	K	øL	M	N	Weight (g)	
Attachment No.	Compatibility															Y1*1	Y2*2
610	CKA-20CS CKG-25CS CKF-20CS	30	30	4.5	3.5	2	24.5	8	12	8	4.5	9	4.5	1.5	8	65	10
620	CKA-25CS CKG-32CS CKF-25CS	35	40	4.5	3.5	3	34.5	8	14	10	4.5	10	4.5	1.5	8	126	19
630	CKA-30CS CKG-40CS CKF-30CS	45	50	6	4.5	4	43	9.5	14	10	6	13	5.5	2	10.5	188	28

● 710 to 770



*1 Y1 : Material S50C

*2 Y2 : Material MC nylon

Code		A	B	C	D	E	F	øG	H	I	J	K	øL	M	Weight (g)	
Attachment No.	Compatibility														Y1*1	Y2*2
710	CKA-40CS CKG-50CS CKF-40CS	44.5	60	6	5	4	52	11	18	14	6	14	6.5	2	285	43
720	CK-1CS	33.5	50	6	5	4	43	9.5	14	10	6	14	5.5	2	128	19
730	CK-1.5CS	43.5	65	7	6.5	5	56	11	18	14	7	18	6.5	2	302	45
740	CK-2CS	55.5	80	8	7	6	71	14	19	14	8	20	8.5	2	471	70
750	CKA-50CS	51.5	70	6	5	5	58	11	18	14	6	15	6.5	2	402	62
760	CKA-60CS	64	80	8	6	6	68	14	20	16	8	18	9	2	608	94
770	CKA-70CS	74	100	8	7	6	88	14	20	16	8	20	9	2	913	140

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending
CKL2
CKLG2
CKL2-HC
CKH2
CKLB2
CKG
CK
CKA
CKS
CKS-F
CKF
CKJ
CHC

Attachment

How to order attachment and dimensions

How to order (Note: When ordering repair parts, 1 pc. is provided.)


CKL2 - Y1 - 810

A Material

B Attachment No.

Code	Description
A Material	
Y1	Material S50C
Y2	Material MC nylon
Code	Compatibility
B Attachment No.	
810	CKL2-20CS,CKLG2-20CS,CKLB2-20CS
820	CKL2-25CS,CKLG2-25CS,CKLB2-25CS
830	CKL2-32CS,CKLG2-32CS,CKLB2-32CS
840	CKL2-40CS,CKLG2-40CS,CKLB2-40CS
850	CKL2-50CS,CKLG2-50CS,CKH2-50CS,CKLB2-50CS
860	CKL2-63CS,CKLG2-63CS,CKH2-63CS,CKLB2-63CS
870	CKL2-80CS,CKLG2-80CS,CKH2-80CS,CKLB2-80CS
880	CKL2-100CS,CKLG2-100CS,CKH2-100CS,CKLB2-100CS

Dimensions



Code Attachment No.	A	B	C	D	E	F	ØG	H	I	J	K	ØL	M	N	Weight (g)	
															Y1	Y2
810	29.5	29	3.5	2.5	2	23	6.5	10	6	12	7	3.5	1	13	64	10
820	34.5	33.5	4.5	3.5	2	24	8	10	7	12.5	9	4.5	1.5	16.5	86	13
830	39.5	33.5	4.5	3.5	3	24	8	12	8	14	10	4.5	1.5	19	118	18
840	49.5	39	6	4.5	3	31	9	12	8	18.5	12	5.5	2	23.5	171	26
850	54.5	44	6	5	4	33	11	14	10	18.5	14	6.5	2	27	250	37
860	69.5	49	8	5.5	5	38	11	16	12	24.5	16	6.5	2	34.5	408	61
870	84.5	59	10	6	6	47	14	18	14	28	18	9	2	44.5	676	101
880	99.5	64	10	7	6	52	14	20	16	31.5	20	9	2	55	962	144

How to order attachment and dimensions

How to order (Note: When ordering repair parts, 1 pc. is provided.)

CKS - **Y1** - **910**


Model

A Material

B Attachment No.

Code	Description
A Material	
Y1	Material S50C
Y2	Material MC nylon
Code	Compatibility
B Attachment No.	
910	CKS-08CS
920	CKS-12CS
930	CKS-16CS,CKS-F-16CS
940	CKS-20CS,CKS-F-20CS
950	CKS-25CS,CKS-F-25CS
960	CKS-32CS,CKS-F-32CS

Dimensions



Code		A	B	C	D	E	F	G	H	I	J	K	L	M	N	P	Q	S	Weight (g)	
Attachment No.	Compatible models																		Y1	Y2
910	CKS-08CS	42.5	30	6.5	15	20	27.5	23	6.5	10	6	10.5	7	14	1.7	2	3.5	1	74	12
920	CKS-12CS	48	35	7.5	19	25	34	27	8	11	7	12.5	9	17	2.7	2	4.5	1	108	17
930	CKS-16CS,CKS-F-16CS	56.5	35	9.5	21	25	40.5	27	8	12	8	15	10	20	2.7	3	4.5	1	145	23
940	CKS-20CS,CKS-F-20CS	66.5	40	11	25	30	48	32	9.5	12	8	17.5	12	23.5	2.7	3	5.5	1.5	192	31
950	CKS-25CS,CKS-F-25CS	85.5	45	16	28	35	60	33	11	14	10	23	14	30	2.7	4	6.5	1.5	335	53
960	CKS-32CS,CKS-F-32CS	97	50	18	31	40	67	38	11	16	12	25.5	16	33.5	2.7	5	6.5	1.5	500	79

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechMndChuk
ShkAbs
FJ
FK
SpdContr
Ending
CKL2
CKLG2
CKL2-HC
CKH2
CKLB2
CKG
CK
CKA
CKS
CKS-F
CKF
CKJ
CHC