




Selection guide


Allowable lateral load




● STM-B-6



● STM-B-10




Allowable torque



Unit: N·m

Bore size (mm)	Model No.	Stroke length (mm)			
		5	10	15	20
ø6	STM-B-6	0.018	0.012	0.009	-
ø10	STM-B-10	0.034	0.023	0.018	0.014


Non-rotating accuracy (reference value)



Bore size (mm)	Non-rotating accuracy θ (degree)
ø6	± 0.08
ø10	± 0.08

Allowable absorbed energy value

Use in the range below and to the left of the curve. For use in the upper right range, provide an external shock absorber.



SCPD3

SCM

SSD2

MDC2

SMG

LCM

LCR

LCG

LCX

STM

STG

STR2

MRL2

GRC

Cylinder Switch

MN3E

MN4E

4GA/B

M4GA/B

MN4GA/B

F.R. (module unit)

Clean F.R

Precision R

Press gauge

Diff. press gauge

Electro-pneumatic R

Speed controller

Auxiliary valve

Fitting/tube

Clean air unit

Pressure sensor

Flow rate sensor

Valve for air blow

Ending