



EBS-G-P4 Series

Series variation

Controller	ActuatorModel No.		Motor Size	Motor Mounting Direction	Body width (mm)	Screw lead (mm)	Max. load capacity (kg)		Max. Pressing force (N)	
							Horizontal	Vertical		
  ECG Series		EBS-04GE-06-P4	□35	Straight	44	6	20.0	9.2	155	
		EBS-04GE-12-P4				12	15.0	3.3	77	
		EBS-04GR/D/L-06-P4		Left/Right/Bottom		6	20.0	9.2	155	
		EBS-04GR/D/L-12-P4				12	11.7	3.3	77	
	 	EBS-05GE-02-P4	□42	Straight	54	2	45.0	18.3	550	
		EBS-05GE-05-P4				5	40.0	14.0	220	
		EBS-05GE-10-P4				10	27.5	7.0	110	
		EBS-05GE-20-P4				20	18.3	2.5	55	
		EBS-05GR/D/L-02-P4		Left/Right/Bottom		2	45.0	18.3	550	
		EBS-05GR/D/L-05-P4				5	40.0	10.0	220	
		EBS-05GR/D/L-10-P4				10	27.5	3.3	110	
		EBS-05GR/D/L-20-P4				20	18.3	0.8	55	
	 	EBS-08GE-05-P4	□56	Straight	82	5	80.0	43.3	965	
		EBS-08GE-10-P4				10	70.0	28.3	482	
		EBS-08GE-20-P4				20	30.0	3.3	241	
		EBS-08GR/D/L-05-P4		Left/Right/Bottom		5	80.0	33.3	965	
		EBS-08GR/D/L-10-P4				10	70.0	18.3	482	
		EBS-08GR/D/L-20-P4				20	30.0	3.3	241	



	Stroke (mm) and max. speed (mm/s)																						Listed page
	50 mm	100	150	200	250	300	350	400	450	500	550	600	650	700	750	800	850	900	950	1000	1050	1100	
	260 mm/s																						4
	400																						
	200																						8
	320																						
	100													95	80	70							14
	230														200	185							
	400															370							
	680																						
	80															70							18
	200															185							
	320																						
	560																						
	120																			110	100		24
	200																						
	400																						
	100																						28
	200																						
	320																						

* This data is at acceleration/deceleration 0.3G...

* The load capacity when wall mounted is the same as for horizontal installation.

EBS-P4
(With motor)

EBR-P4
(With motor)

ECC-A
(Controller)

Safety
precautions