



EBS/EBR Model Selection Check Sheet → CKD(Contact)

Fill in the form and send to the nearest CKD Sales Office. We will respond with the model selection results.

Customer:

Company		Department	
Name		E-mail	
Tel.		Fax	

Selecting conditions:

Desired model	(EBS/EBR)-		
Basic specifications	Max. stroke length: mm, ball screw lead: mm		
Operating conditions	Travel stroke: mm, travel time: s		
	Set speed: mm/s		
	Set acceleration/deceleration: mm/s ² (set acceleration/deceleration time: s)		
	Repeatability: ± mm		
Load conditions	Slider		Rod
	Load weight: kg		
	Mounting orientation: Horizontal / wall mounted / vertical / ceiling mounted / other 		Mounting orientation: Horizontal / wall mounted / vertical / ceiling mounted / other 
	Distance from slider and rod center to the center of gravity of load		
	A direction: mm		X direction: mm
	B direction: mm		Y direction: mm
	C direction: mm		Z direction: mm
	Pressing load: No / Yes (N) Operating / Stopped Direction of the force applied to slider center ()		
Working environment	Ambient temperature: °C, Ambient humidity: %		
	Atmosphere:		
Interface specifications	Parallel I/O / IO-Link / CC-Link / EtherCAT / EtherNet/IP		
Remarks			