



CONTENTS

Product introduction	Intro Page
Series variation	2
● Specifications/How to order/Dimensions	
● KHL-300	4
● KHL-400	6
● KHL-500	8
● KHL-600	10
● KHL-700	12
● Name and internal structure of each part	14
● Option descriptions	18
● System configuration	20
⚠ Safety precautions	26

	Max. speed *1					Cycle time (2 kg load) s	Max. load capacity (Rating) kg	Allowable moment of inertia kg/m ²	Listed Page
	1-axis deg/s	2-axis deg/s	3-axis (Z-axis) mm/s	4-axis (Z-axis rotation) deg/s	Synthesis m/s				
	660	660	1120	1500	5.1	0.48	5 (2)	0.05	4
	660	660	1120	1500	6.3	0.47	5 (2)	0.05	6
	450	450	2000	1700	6.3	0.45	10 (2)	0.2	8
	450	450	2000	1700	7.1	0.45	10 (2)	0.2	10
	450	450	2000	1700	7.9	0.50	10 (2)	0.2	12


*1 There are restrictions on speed and acceleration depending on the operation pattern, load weight and degree of offset.

*2 300 mm in horizontal direction, 25 mm in vertical direction (reciprocating), rough positioning. Continuous operation exceeding the effective load factor is not allowed.

Option list

Model No.	Z-axis long stroke length	Z-axis bottom bellows	Z-axis top cap	Ceiling mount specifications	Cable extension (longest)	For mounting hand tool flange	Simple clean-room
KHL-300	X	OK	OK	X	15 m	OK	OK
KHL-400	X	OK	OK	OK	15 m	OK	OK
KHL-500	OK (300 mm)	OK	OK	OK	15 m	OK	OK
KHL-600	OK (300 mm)	OK	OK	OK	15 m	OK	OK
KHL-700	OK (300 mm)	OK	OK	OK	15 m	OK	OK

OK: Compatible X: Not compatible



SCARA robot

KHL-300

● Arm length: 300 mm (125 mm + 175 mm)

How to order

KHL - 300 N NNN - KSL3 N NN NN - N N

A Arm length
300 mm

B Z-axis stroke
*1 N Standard

C Option
*4
NNN None
BNN Lower bellows
CNN Upper cap
SCN Simple clean-room

D External signal polarity
N N-Type (standard)
P P-Type

E Robot controller cable
NN 3.5 m (standard)
05 5 m
08 8 m
10 10 m
15 15 m

F Network
NN None
CC CC-Link
DN DeviceNet
PB PROFIBUS
EN EtherNet/IP
EC EtherCAT
PN PROFINET

G Expansion IO unit
*2
N 0 units
1 1 units
2 2 units

H IO cable
*3
N None
1 1 set
2 2 set
3 3 set

*1 160 stroke.
*2 A unit with 28 inputs and 20 outputs.
*3 A 2-piece set with 6 m cable length.
*4 KHL-TF (tool flange) is also required.

Product subject to the EAR (EAR99)


Specifications

Model No.			KHL-300
Type			Horizontal articulation
Number of axes			4
Arm length			mm 300 (125+175)
Operating range	1-axis	deg	±125
	2-axis	deg	±145
	3-axis (Z-axis)	mm	0 to 160
	4-axis (Z-axis rotation)	deg	±360
Max. speed	1-axis	deg/s	660
	2-axis	deg/s	660
	3-axis (Z-axis)	mm/s	1120
	4-axis (Z-axis rotation)	deg/s	1500
	Synthesis	m/s	5.1
*1			
Cycle time (2kg load) *2			s 0.48
Max. load capacity			kg 5 (Rating 2)
Allowable moment of inertia			kg·m ² 0.05
Position repeat	X-Y	mm	±0.01
	Z (3-axis)	mm	±0.015
	4-axis (Z-axis rotation)	deg	±0.007
Accuracy *3			
Hand wiring			8 input points/8 output points
Hand fitting *4			ø4 x 3 pcs
Position detection method			Absolute method
Robot controller cable			m 3.5
Power capacity			kVA 0.7
Body weight			kg 12

- *1 There are restrictions on speed and acceleration depending on the operation pattern, load weight and degree of offset.
- *2 300 mm in horizontal direction, 25 mm in vertical direction (reciprocating), rough positioning. Continuous operation exceeding the effective load factor is not allowed.
- *3 One-way positioning repeatability when the ambient temperature and airframe temperature are constant. Not the absolute positioning accuracy. For X-Y and C, the values are at the Z upper limit. The track accuracy is not guaranteed.
- *4 A fitting for hand piping is available on the base side. Customers are responsible for piping.

Dimensions


● KHL-300




Optional dimensions

● Tool flange


Model No.: KHL-TF3



● Bellows



Note: When ordering the SCARA robot body and the tool flange at the same time, the tool flange will be "assembled at shipment".



SCARA robot

KHL-400

● Arm length: 400 mm (225 mm + 175 mm)

How to order

KHL - 400 N NNN - KSL3 N NN NN - N N

A Arm length
400 mm

B Z-axis stroke
*1 N Standard

C Option

NNN	None
BNN	Lower bellows
CNN	Upper cap
TNN	Ceiling mount
*2 BCN	Lower bellows, top cap
*2 BTN	Lower bellows, ceiling mount
*2 BCT	Lower bellows, top cap, ceiling mount
CTN	Top cap, ceiling mount
SCN	Simple clean-room

D External signal polarity

N	N-Type (standard)
P	P-Type

E Robot controller cable

NN	3.5 m (standard)
05	5 m
08	8 m
10	10 m
15	15 m

F Network

NN	None
CC	CC-Link
DN	DeviceNet
PB	PROFIBUS
EN	EtherNet/IP
EC	EtherCAT
PN	PROFINET

G Expansion IO unit
*3

N	0 units
1	1 units
2	2 units

H IO cable
*4

N	None
1	1 set
2	2 set
3	3 set

*1 160 stroke.
*2 KHL-TF (tool flange) is also required.
*3 A unit with 28 inputs and 20 outputs.
*4 A 2-piece set with 6 m cable length.
*5 KHL-TF (tool flange) is also required.

Product subject to the EAR (EAR99)


Specifications

Model No.			KHL-400
Type			Horizontal articulation
Number of axes			4
Arm length			400 (225+175) mm
Operating range	1-axis	deg	±125
	2-axis	deg	±145
	3-axis (Z-axis)	mm	0 to 160
	4-axis (Z-axis rotation)	deg	±360
Max. speed	1-axis	deg/s	660
	2-axis	deg/s	660
	3-axis (Z-axis)	mm/s	1120
	4-axis (Z-axis rotation)	deg/s	1500
	Synthesis	m/s	6.3
*1			
Cycle time (2kg load) *2			0.47 s
Max. load capacity			5 (Rating 2) kg
Allowable moment of inertia			0.05 kg·m ²
Position repeat			X-Y mm ±0.01
Accuracy *3	Z (3-axis)	mm	±0.015
	4-axis (Z-axis rotation)	deg	±0.007
Hand wiring			8 input points/8 output points
Hand fitting *4			ø4 x 3 pcs
Position detection method			Absolute method
Robot controller cable			3.5 m
Power capacity			0.7 kVA
Body weight			13 kg

*1 There are restrictions on speed and acceleration depending on the operation pattern, load weight and degree of offset.
*2 300 mm in horizontal direction, 25 mm in vertical direction (reciprocating), rough positioning. Continuous operation exceeding the effective load factor is not allowed.
*3 One-way positioning repeatability when the ambient temperature and airframe temperature are constant. Not the absolute positioning accuracy. For X-Y and C, the values are at the Z upper limit. The track accuracy is not guaranteed.
*4 A fitting for hand piping is available on the base side. Customers are responsible for piping.

Dimensions


● KHL-400




Optional dimensions

● Tool flange

Model No.: KHL-TF3



● Bellows



Note: When ordering the SCARA robot body and the tool flange at the same time, the tool flange will be "assembled at shipment".



SCARA robot

KHL-500

● Arm length: 500 mm (200 mm + 300 mm)

How to order

KHL - 500 N NNN - KSL3 N NN NN - N N

A Arm length
500 mm

B Z-axis stroke
*1 N Standard
Z 300

C Option
*5 NNN None
BNN Lower bellows
CNN Upper cap
TNN Ceiling mount
*2 BCN Lower bellows, top cap
*2 BTN Lower bellows, ceiling mount
*2 BCT Lower bellows, top cap, ceiling mount
CTN Top cap, ceiling mount
SCN Simple clean-room

D External signal polarity
N N-Type (standard)
P P-Type

E Robot controller cable
NN 3.5 m (standard)
05 5 m
08 8 m
10 10 m
15 15 m

F Network
NN None
CC CC-Link
DN DeviceNet
PB PROFIBUS
EN EtherNet/IP
EC EtherCAT
PN PROFINET

G Expansion IO unit
*3 N 0 units
1 1 units
2 2 units

H IO cable
N None *4
1 1 set
2 2 set
3 3 set

*1 150 stroke.
*2 KHL-TF (tool flange) is also required.
*3 A unit with 28 inputs and 20 outputs.
*4 A 2-piece set with 6 m cable length.
*5 KHL-TF (tool flange) is also required.

Product subject to the EAR (EAR99)


Specifications

Model No.			KHL-500
Type			Horizontal articulation
Number of axes			4
Arm length			500 (200+300) mm
Operating range	1-axis	deg	±125
	2-axis	deg	±145
	3-axis (Z-axis)	mm	0 to 150
	4-axis (Z-axis rotation)	deg	±360
Max. speed	1-axis	deg/s	450
	2-axis	deg/s	450
	3-axis (Z-axis)	mm/s	2000
	4-axis (Z-axis rotation)	deg/s	1700
	Synthesis	m/s	6.3
*1			
Cycle time (2kg load) *2			0.45 s
Max. load capacity			10 (Rating 2) kg
Allowable moment of inertia			0.2 kg·m ²
Position repeat			X-Y mm ±0.01
Accuracy *3	Z (3-axis)	mm	±0.015
	4-axis (Z-axis rotation)	deg	±0.007
Hand wiring			8 input points/8 output points
Hand fitting *4			ø6 x 3 pcs
Position detection method			Absolute method
Robot controller cable			3.5 m
Power capacity			1.4 kVA
Body weight			22 kg

*1 There are restrictions on speed and acceleration depending on the operation pattern, load weight and degree of offset.
*2 300 mm in horizontal direction, 25 mm in vertical direction (reciprocating), rough positioning. Continuous operation exceeding the effective load factor is not allowed.
*3 One-way positioning repeatability when the ambient temperature and airframe temperature are constant. Not the absolute positioning accuracy. For X-Y and C, the values are at the Z upper limit. The track accuracy is not guaranteed.
*4 A fitting for hand piping is available on the base side. Customers are responsible for piping.

Dimensions


● KHL-500




Optional dimensions

● Tool flange


Model No.: KHL-TF5



● Bellows



Note: When ordering the SCARA robot body and the tool flange at the same time, the tool flange will be "assembled at shipment".



SCARA robot

KHL-600

● Arm length: 600 mm (300 mm + 300 mm)

How to order

KHL - 600 N NNN - KSL3 N NN NN - N N

A Arm length
600 mm

B Z-axis stroke
*1 N Standard
Z 300

C Option
*5 NNN None
BNN Lower bellows
CNN Upper cap
TNN Ceiling mount
*2 BCN Lower bellows, top cap
*2 BTN Lower bellows, ceiling mount
*2 BCT Lower bellows, top cap, ceiling mount
CTN Top cap, ceiling mount
SCN Simple clean-room

D External signal polarity
N N-Type (standard)
P P-Type

E Robot controller cable
NN 3.5 m (standard)
05 5 m
08 8 m
10 10 m
15 15 m

F Network
NN None
CC CC-Link
DN DeviceNet
PB PROFIBUS
EN EtherNet/IP
EC EtherCAT
PN PROFINET

G Expansion IO unit
*3 N 0 units
1 1 units
2 2 units

H IO cable
N None *4
1 1 set
2 2 set
3 3 set

*1 150 stroke.
*2 KHL-TF (tool flange) is also required.
*3 A unit with 28 inputs and 20 outputs.
*4 A 2-piece set with 6 m cable length.
*5 KHL-TF (tool flange) is also required.

Product subject to the EAR (EAR99)


Specifications

Model No.			KHL-600
Type			Horizontal articulation
Number of axes			4
Arm length			600 (300+300) mm
Operating range	1-axis	deg	±125
	2-axis	deg	±145
	3-axis (Z-axis)	mm	0 to 150
	4-axis (Z-axis rotation)	deg	±360
Max. speed	1-axis	deg/s	450
	2-axis	deg/s	450
	3-axis (Z-axis)	mm/s	2000
	4-axis (Z-axis rotation)	deg/s	1700
	Synthesis	m/s	7.1
*1			
Cycle time (2kg load) *2			0.45 s
Max. load capacity			10 (Rating 2) kg
Allowable moment of inertia			0.2 kg·m ²
Position repeat			X-Y mm ±0.01
Accuracy *3	Z (3-axis)	mm	±0.015
	4-axis (Z-axis rotation)	deg	±0.007
Hand wiring			8 input points/8 output points
Hand fitting *4			ø6 x 3 pcs
Position detection method			Absolute method
Robot controller cable			3.5 m
Power capacity			1.4 kVA
Body weight			23 kg

*1 There are restrictions on speed and acceleration depending on the operation pattern, load weight and degree of offset.
*2 300 mm in horizontal direction, 25 mm in vertical direction (reciprocating), rough positioning. Continuous operation exceeding the effective load factor is not allowed.
*3 One-way positioning repeatability when the ambient temperature and airframe temperature are constant. Not the absolute positioning accuracy. For X-Y and C, the values are at the Z upper limit. The track accuracy is not guaranteed.
*4 A fitting for hand piping is available on the base side. Customers are responsible for piping.

Dimensions


● KHL-600




Optional dimensions

● Tool flange


Model No.: KHL-TF5



● Bellows



Note: When ordering the SCARA robot body and the tool flange at the same time, the tool flange will be "assembled at shipment".



SCARA robot

KHL-700

● Arm length: 700 mm (400 mm + 300 mm)

How to order

KHL - 700 N NNN - KSL3 N NN NN - N N

A Arm length
700 mm

B Z-axis stroke
*1 N Standard
Z 300

C Option
*5 NNN None
BNN Lower bellows
CNN Upper cap
TNN Ceiling mount
*2 BCN Lower bellows, top cap
*2 BTN Lower bellows, ceiling mount
*2 BCT Lower bellows, top cap, ceiling mount
CTN Top cap, ceiling mount
SCN Simple clean-room

D External signal polarity
N N-Type (standard)
P P-Type

E Robot controller cable
NN 3.5 m (standard)
05 5 m
08 8 m
10 10 m
15 15 m

F Network
NN None
CC CC-Link
DN DeviceNet
PB PROFIBUS
EN EtherNet/IP
EC EtherCAT
PN PROFINET

G Expansion IO unit
*3 N 0 units
1 1 units
2 2 units

H IO cable
N None *4
1 1 set
2 2 set
3 3 set

*1 150 stroke.
*2 KHL-TF (tool flange) is also required.
*3 A unit with 28 inputs and 20 outputs.
*4 A 2-piece set with 6 m cable length.
*5 KHL-TF (tool flange) is also required.

Product subject to the EAR (EAR99)


Specifications

Model No.			KHL-700
Type			Horizontal articulation
Number of axes			4
Arm length			700 (400+300) mm
Operating range	1-axis	deg	±125
	2-axis	deg	±145
	3-axis (Z-axis)	mm	0 to 150
	4-axis (Z-axis rotation)	deg	±360
Max. speed	1-axis	deg/s	450
	2-axis	deg/s	450
	3-axis (Z-axis)	mm/s	2000
	4-axis (Z-axis rotation)	deg/s	1700
	Synthesis	m/s	7.9
Cycle time (2kg load) *2			0.50 s
Max. load capacity			10 (Rating 2) kg
Allowable moment of inertia			0.2 kg·m ²
Position repeat			±0.01 mm
Accuracy *3	Z (3-axis)	mm	±0.015
	4-axis (Z-axis rotation)	deg	±0.007
Hand wiring			8 input points/8 output points
Hand fitting *4			ø6 x 3 pcs
Position detection method			Absolute method
Robot controller cable			3.5 m
Power capacity			1.4 kVA
Body weight			24 kg

*1 There are restrictions on speed and acceleration depending on the operation pattern, load weight and degree of offset.
*2 300 mm in horizontal direction, 25 mm in vertical direction (reciprocating), rough positioning. Continuous operation exceeding the effective load factor is not allowed.
*3 One-way positioning repeatability when the ambient temperature and airframe temperature are constant. Not the absolute positioning accuracy. For X-Y and C, the values are at the Z upper limit. The track accuracy is not guaranteed.
*4 A fitting for hand piping is available on the base side. Customers are responsible for piping.

Dimensions


● KHL-700




Optional dimensions

● Tool flange

Model No.: KHL-TF5




● Bellows



Note: When ordering the SCARA robot body and the tool flange at the same time, the tool flange will be "assembled at shipment".

Section names



Internal structure

