



YASKAWA MOTOMAN Robot Compatible Gripper Long Stroke Type

RHLF-YS Series

With Speed Controller, Cylinder Switch
Connection Port Diameter: $\phi 4$ One-touch Fitting



For suitable detailed model No.s, please see our website.


RHLF-YS Series

Gripping Force Performance Data/External Dimensions


Gripping Force Performance Data

- Gripping force represents the thrust (for one finger) in the direction of the arrow shown in the figure.
- This represents the gripping force acting in the opening and closing directions at a gripper's attachment length L when the supply pressure is 0.3, 0.5, and 0.7 MPa.

Open direction (\leftarrow), closed direction (\rightarrow) (solid line)



Model No. Notation Method



① Robot Flange

| Code | Content |
|-------|-------------------------------------|
| Blank | No Robot Flange |
| F | With Robot Flange ^(Note) |

^(Note) Robot flange mounting bolts included

② Accessories

| Code | Content |
|-------|--|
| Blank | No Attachments |
| Y2 | Attachment for testing ^{*1} |
| V | Directional Control Valve · Tube ^{*2} |

^{*1} Made of resin, so use for gripping tests. (Weight is 30 g per piece)

^{*2} The directional control valve is a $\phi 4$ one-touch fitting (air supply port, A/B port) with silencer (R1/R2 port) and mounting plate. Tubes are $\phi 4$ outer diameter, 2.5 m length x 2 pieces.

Specifications

| Item | | RHLF |
|-------------------------|--------------------|-----------------------------------|
| Bore size | mm | $\phi 16 \times 2$ |
| Actuation method | | Double Acting Type |
| Operating Fluid | | Compressed Air |
| Max. Operating Pressure | MPa | 0.7 |
| Min. Working Pressure | MPa | 0.2 |
| Port Size | | $\phi 4$ One-touch Fitting |
| Ambient Temperature | $^{\circ}\text{C}$ | 5 to 50 |
| Operating Stroke | mm | 32 |
| Repeatability | mm | ± 0.03 |
| Weight | kg | 1.0 |
| Indicator LED | | Blue/Green |
| Cylinder Switch | | With T2H (Red LED ON when lit) |

^(Note) For attachments manufactured to match workpieces, refer to P. 568.

[Switch Specifications]


| Item | Solid state 2-wire type | |
|----------------------|----------------------------------|------------|
| | F2H | T2H |
| Applications | For programmable controller only | |
| Load Voltage/Current | 10 to 30 VDC, 5 to 20 mA | |
| Leakage current | 1 mA or less | |
| Shock resistance | 980 m/s ² | |
| Weight | g | 10 18 |

[Directional Control Valve (V) Specifications]

| Item | 4GA120R-C4-E21P-FLA28482-3-ST |
|-----------------------------------|---|
| Valve Type and Operation Method | Pilot Operated Soft Spool Valve |
| Switching Position Classification | 2-position double solenoid |
| Max. Operating Pressure | MPa 0.7 |
| Min. Working Pressure | MPa 0.2 |
| Ambient Temperature | $^{\circ}\text{C}$ -5 to 55 (No freezing) |
| Fluid Temperature | $^{\circ}\text{C}$ 5 to 55 |
| Manual Override | Non-lock/Lock Common Type |
| Response Time | ms 9 |
| Flow Characteristics | P \rightarrow A/B: C=1.2, b=0.47 A/B \rightarrow R1/R2: C=0.72, b=0.37 |
| Rated voltage | V 24 VDC |
| Voltage Fluctuation Range | $\pm 10\%$ |
| Holding Current | A 0.017 |
| Power Consumption | W 0.40 |
| Surge Suppressor | Built-in |
| Indicator | Built-in Lamp |

For other specification products, please refer to "Directional Control Valve ① (No.RJ-011AA)".

Outline Dimension Drawing



Outline Dimension Drawing

