



Kawasaki Robot K-AddOn Registered Gripper Compact Type

RLSH-KW Series

With Speed Controller, Cylinder Switch
Connection Port Diameter: $\phi 4$ One-touch Fitting



For suitable detailed model No.s, please see our website.



RLSH-KW Series

Gripping Force Performance Data/External Dimensions

Gripping Force Performance Data

- Gripping force represents the thrust (for one finger) in the direction of the arrow shown in the figure.
- This represents the gripping force acting in the opening and closing directions at a gripper's attachment length L when the supply pressure is 0.3, 0.5, and 0.7 MPa.

Open direction (←) ----- (broken line)
Closing direction (→) ----- (solid line)



Model No. Notation Method

RLSH - **A20D1N** - **L1** - **F** **Y2V** - **KW**

Model No.

1 Robot Flange
2 Accessories
K-AddOn Registered Products

1 Robot Flange

Code	Content
Blank	No Robot Flange
F	With Robot Flange

Note) Robot flange mounting bolts included

2 Accessories

Code	Content
Blank	No Attachments
Y2	Attachment for testing
V	Directional Control Valve · Tube

*1 Made of resin, so use for gripping tests. (Weight is 25 g per piece)
*2 The directional control valve is a $\phi 4$ one-touch fitting (air supply port, A/B port) with silencer (R1/R2 port) and mounting plate. Tubes are $\phi 4$ outer diameter, 2.5 m length x 2 pieces.

Specifications

Item	RLSH
Bore size	mm $\phi 20$
Actuation method	Double Acting Type
Operating Fluid	Compressed Air
Max. Operating Pressure	MPa 0.7
Min. Working Pressure	MPa 0.1
Port Size	$\phi 4$ One-touch Fitting
Ambient Temperature	$^{\circ}\text{C}$ 0 to 50
Operating Stroke	mm 18
Repeatability	mm ± 0.01
Weight	kg 0.8
Indicator LED	Blue/Green
Cylinder Switch	With F2H (Yellow LED ON when lit)

Note) For attachments manufactured to match workpieces, refer to P. 568.

[Switch Specifications]


Item	Solid state 2-wire type	
	F2H	T2H
Applications	For programmable controller only	
Load Voltage/Current	10 to 30 VDC, 5 to 20 mA	
Leakage current	1 mA or less	
Shock resistance	980 m/s ²	
Weight	g 10	18

[Directional Control Valve (V) Specifications]

Item	4GA120R-C4-E21P-FLA28482-3-ST
Valve Type and Operation Method	Pilot Operated Soft Spool Valve
Switching Position Classification	2-position double solenoid
Max. Operating Pressure	MPa 0.7
Min. Working Pressure	MPa 0.2
Ambient Temperature	$^{\circ}\text{C}$ -5 to 55 (No freezing)
Fluid Temperature	$^{\circ}\text{C}$ 5 to 55
Manual Override	Non-lock/Lock Common Type
Response Time	ms 9
Flow Characteristics	P → A/B: C=1.2, b=0.47 A/B → R1/R2: C=0.72, b=0.37
Rated voltage	V 24 VDC
Voltage Fluctuation Range	$\pm 10\%$
Holding Current	A 0.017
Power Consumption	W 0.40
Surge Suppressor	Built-in
Indicator	Built-in Lamp

For other specification products, please refer to "Directional Control Valve ① (No.RJ-011AA)".

Outline Dimension Drawing



Outline Dimension Drawing

