

SCP3 Variation and option selection table

- ⊙ : Option variation (check category 2)
- : C5 compatible (check category 3)
- △ : Available depending on conditions (Estimation)
- : Not available

		Code	Clean room specifications				
			Exhaust treatment	Vacuum treatment	Exhaust treatment	Vacuum treatment	
			P7	P71	P5	P51	
Variation	Double acting	Blank	○	○	○	○	
	With cylinder switch	L	○	○	○	○	
	Fine speed	F	○	○	■	■	
	Double acting double rod	D	○	○	○	○	
	Heat resistant (120°C)	T	■	■	■	■	
	Low speed	O	○	○	■	■	
	High load	K	△	△	△	△	
	Non-rotation	M	■	■	■	■	
	With speed controller	Z	■	■	■	■	
	With valve	V	■	■	■	■	
	Single acting push	SCPS3	■	■	■	■	
	Single acting pull	SCPH3	■	■	■	■	
	Cushion	Rubber-air cushioned	C	○	○	○	○
Option	Rod nut material stainless steel	M	○	○	○	○	
	Axial port position	O	○	○	○	○	
	Customized piston rod end form	N**	○	○	○	○	

- Precision R
- Press gauge
Diff. press gauge
- Electro-pneumatic R
- Speed controller
- Auxiliary valve
- Fitting/tube
- Clean air unit
- Pressure sensor
- Flow rate sensor
- Valve for air blow
- Ending