

Variation and option selection table

- ◎ : Option variation (check category 2)
- : C5 compatible (check category 3)
- △ : Available depending on conditions (Estimation)
- : Not available

		Clean room specifications				
		Exhaust treatment	Vacuum treatment	Exhaust treatment	Vacuum treatment	
SCPD3						
SCM						
SSD2						
MDC2						
SMG						
LCM						
LCR						
LCG						
LCX		Code	P7	P71	P5	P51
Variation	Double acting single rod	Blank	◎	◎	○	○
	With cylinder switch	L	◎	◎	○	○
	Fine speed	F	◎	◎	■	■
	Single acting push	X	■	■	■	■
	Single acting pull	Y	■	■	■	■
STM						
STG						
STR2						
MRL2						
GRC						
Cylinder switch						
MN3E MN4E						
4GA/B						
M4GA/B						
MN4GA/B						
F.R (module unit)						
Clean F.R						
Precision R						
Press gauge Diff. press gauge						
Electro-pneumatic R						
Speed controller						
Auxiliary valve						
Fitting/tube						
Clean air unit						
Pressure sensor						
Flow rate sensor						
Valve for air blow						
Ending						