

## Variation and option selection table

- ◎ : Option variation (check category 2)
- : C5 compatible (check category 3)
- △ : Available depending on conditions (estimation)
- : Not available

		Code	Clean room specifications	
			Vacuum treatment	Vacuum treatment
			P73	P53
Variation	Basic	Blank	◎	○
	High accuracy	K	◎	○
	Fine speed	F	◎	■
Port thread	NPT (50, 80)	N	○	○
	G (50, 80)	G	○	○

- SCPD3
- SCM
- SSD2
- MDC2
- SMG
- LCM
- LCR
- LCG
- LCX
- STM
- STG
- STR2
- MRL2
- GRC**
- Cylinder switch
- MN3E  
MN4E
- 4GA/B
- M4GA/B
- MN4GA/B
- F.R (module unit)
- Clean F.R
- Precision R
- Press gauge  
Diff. press gauge
- Electro-pneumatic R
- Speed controller
- Auxiliary valve
- Fitting/tube
- Clean air unit
- Pressure sensor
- Flow rate sensor
- Valve for air blow
- Ending