

Variation and option combination selection table

- ⊙ : Option variation (check category 2)
- : C5 compatible (check category 3)
- △ : Available depending on conditions (Estimation)
- : Not available

Category		Category	Clean room specifications		
		Code	Clean room specifications (exhaust treatment)	Clean room specifications (vacuum treatment)	
Variation	Double acting basic	B	⊙	⊙	
	Position locking	Q	△	△	
	With air cushion	C			
	Heat resistant (120°)	T			
	Packing seal material fluoro rubber	T2	△	△	
	Low speed	O	○	○	
	Powerful scraper	G			
	Coil scraper	G1			
	Coolant proof scraper (NBR)	G2			
	Coolant proof scraper (FKM)	G3			
	Spatter adherence prevention	G4			
	Port thread	NPT (ø20 and over)	N	○	○
		G (ø20 and over)	G	○	○
	Option	Rubber-air cushioned	C		
Corrosion proof		M			
	Copper and PTFE free	P6			

- SCPD3
- SCM
- SSD2
- MDC2
- SMG
- LCM
- LCR
- LCG
- LCX
- STM
- STG
- STR2
- MRL2
- GRC
- Cylinder switch
- MN3E  
MN4E
- 4GA/B
- M4GA/B
- MN4GA/B
- F.R (module unit)
- Clean F.R
- Precision R
- Press gauge  
Diff. press gauge
- Electro-pneumatic R
- Speed controller
- Auxiliary valve
- Fitting/tube
- Clean air unit
- Pressure sensor
- Flow rate sensor
- Valve for air blow
- Ending