

STR2-B Series

Variation and option selection table

- ◎ : Option variation (check category 2)
- : C5 compatible (check category 3)
- △ : Available depending on conditions (estimation)
- : Not available

		Clean room specifications				
		Exhaust treatment	Vacuum treatment	Exhaust treatment	Vacuum treatment	
		Code	P72	P73	P52	P53
Variation	Double acting basic (ball bearing)	B	◎	◎	○	○
	Fine speed	F	○	○	■	■
	Double rod	D	○	○	○	○
	Position locking	Q	△	△	△	△
	Low speed	O	○	○	■	■
Port thread	NPT1/8 (ø32)	N	○	○	○	○
	G 1/8 (ø32)	G	○	○	○	○
Option	End plate material: steel	F	○	○	○	○
	Piping port position on the 180° opposite side	O	◎	◎	○	○
	Rear piping	R	■	■	■	■

- SCPD3
- SCM
- SSD2
- MDC2
- SMG
- LCM
- LCR
- LCG
- LCX
- STM
- STG
- STR2
- MRL2
- GRC
- Cylinder switch
- MN3E
MN4E
- 4GA/B
- M4GA/B
- MN4GA/B
- F.R (module unit)
- Clean F.R
- Precision R
- Press gauge
Diff. press gauge
- Electro-pneumatic R
- Speed controller
- Auxiliary valve
- Fitting/tube
- Clean air unit
- Pressure sensor
- Flow rate sensor
- Valve for air blow
- Ending