




Series variation

Unit cylinder UCA2 Series

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MecHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending

Variation	Model No. JIS symbol	Bore size (mm)	Standard stroke length (mm)							
			25	50	75	100	125	150		
Metal bush bearing with switch	UCA2 UCA2-L (with switch) 	ø10	●	●	●	●				
		ø16/ø25/ø32	●	●	●	●	●	●		
Ball bearing with switch	UCA2-B UCA2-BL (with switch) 	ø10	●	●	●	●				
		ø16/ø25/ø32	●	●	●	●	●	●		

Product introduction



●: Standard, ◎: Option, ■: Not available

Standard stroke length (mm)			Min. stroke length	Max. stroke length	Fixing method		Option				Switch	Page
					Body fixing	Plate fixing	Single adjusting stopper plate A side	Single adjusting stopper plate B side	Double adjusting stoppers	Copper and PTFE free		
	175	200			X	Y	P1A	P1B	P2	P6		
			25	100	●	●	◎	◎	◎	●	◎	640
	●	●		200	●	●	◎	◎	◎	●		
			25	100	●	●	◎	◎	◎	●	◎	650
	●	●		200	●	●	◎	◎	◎	●		


LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending

Variation and option combination selection table

- : Standard
- ◎ : Option
- : Available (made-to-order product)
- △ : Available depending on conditions (Contact CKD.)
- × : Not available

	Category	Category	Variation			Port thread			Option				
			Metal bush bearing	Ball bearing	With cylinder switch	NPT	G		Stroke adjusting stopper	Adjustable range of double stoppers 5 mm	Adjustable range of double stoppers 12.5 mm	Adjustable range of A side stopper 25 mm	Adjustable range of B side stopper 25 mm
		Code	Blank	B	L	N	G		Blank	P2	P1A	P1B	
	Variation	Metal bush bearing	Blank	×	◎	○	○		●	◎	◎	◎	
		Ball bearing	B		◎	○	○		●	◎	◎	◎	
		With cylinder switch	L			○	○		●	◎	◎	◎	
	Port thread	NPT	N				×		○	○	○	○	
		G	G						○	○	○	○	
	Option	Stroke adjusting stopper											
		Both sides Double stoppers Adjustable range 5 mm / side	Blank							×	×	×	
		Double stoppers Adjustable range 12.5 mm /side	P2								×	×	
		With A side Adjustable range 25 mm	P1A									×	
		With B side Adjustable range 25 mm	P1B										
	Accessory	Cylinder switch	Listed separately	◎	◎	◎	○	○		◎	◎	◎	◎

[Example of model No.]



Model No.: Unit cylinder

- Variation: Ball bearing, with switch
- A Bore size : $\varnothing 16$ mm
- B Port thread : Rc thread
- C Stroke length : 50 mm
- D Switch model No. : Proximity T2H switch, lead wire 1 m
- E Switch quantity : 2
- F Option : Double adjusting stoppers, adjustable range 12.5 mm per side

LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending