


Technical data

Accuracy of the slide table





Item		LCM*-4.5 to 8
Parallelism	C-plane against A-plane	0.03
	D-plane against B-plane	0.03
Parallelism during movement	C-plane against A-plane	0.005 ^{Note}
	D-plane against B-plane	0.005 ^{Note}
Tolerance of E		±0.05
Tolerance of F		±0.05
Tolerance of G		±0.05



Note : 0.006 in LCM-6, 8 with 30 mm stroke

Displacement angle of the slide table due to bending moment (reference value)



M1 Moment



M2 Moment



M3 Moment



LCM
LCR
LCG
LCW
LCX
STM
STG
STS/STL
STR2
UCA2
ULK*
JSK/M2
JSG
JSC3/JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3*
NHS
HRL
LN
Hand
Chuk
MechHnd/Chuk
ShkAbs
FJ
FK
SpdContr
Ending