

Series variation



Free position locking flat cylinder UFCD Series

●: Standard ○: Option

Variation	Model No.	Bore size (mm)	Standard stroke length (mm)								Min. stroke length (mm)	Custom stroke length (mm)	Max. stroke length (mm)	Option	Switch	Page
			5	10	15	20	25	30	40	50				Rod end male thread		
Double acting/ single rod	UFCD-KL	ø25 equivalent/ ø32 equivalent/ ø40 equivalent/ ø50 equivalent/ ø63 equivalent	●	●	●	●	●	●	●	●	1	1	150	○	○	888

- LCM
- LCR
- LCG
- LCW
- LCX
- STM
- STG
- STS/STL
- STR2
- UCA2
- ULK*
- JSK/M2
- JSG
- JSC3/JSC4
- USSD
- UFCD**
- USC
- UB
- JSB3
- LMB
- LML
- HCM
- HCA
- LBC
- CAC4
- UCAC2
- CAC-N
- UCAC-N
- RCS2
- RCC2
- PCC
- SHC
- MCP
- GLC
- MFC
- BBS
- RRC
- GRC
- RV3*
- NHS
- HRL
- LN
- Hand
- Chuk
- MechHnd/Chuk
- ShkAbs
- FJ
- FK
- SpdContr
- Ending