



Series variation

Lightweight clamp cylinder/position locking and lightweight clamp cylinder CAC-N32/40, UCAC-N32/40 Series

●: Standard ○: Option

Variation	Model No. JIS symbol	Bore size (mm)	Stroke (mm)	Min. stroke (mm)	Max. stroke (mm)	Accessory	Switch	Page
						Rod clevis Y		
Lightweight clamp cylinder	CAC-N32/40 	ø32/ø40	50/75/100/ 125/150	5	150	○	○	1046
Lightweight position locking clamp cylinder	UCAC-N32/40 	ø32/ø40	50/75/100/ 125/150	5	150	○	○	1052

- LCM
- LCR
- LCG
- LCW
- LCX
- STM
- STG
- STS/STL
- STR2
- UCA2
- ULK*
- JSK/M2
- JSG
- JSC3/JSC4
- USSD
- UFCD
- USC
- UB
- JSB3
- LMB
- LML
- HCM
- HCA
- LBC
- CAC4
- UCAC2
- CAC-N**
- UCAC-N**
- RCS2
- RCC2
- PCC
- SHC
- MCP
- GLC
- MFC
- BBS
- RRC
- GRC
- RV3*
- NHS
- HRL
- LN
- Hand
- Chuk
- MechHnd/Chuk
- ShkAbs
- FJ
- FK
- SpdContr
- Ending