
















機種選定ガイド

: 対応不可
 接続口径欄
○ : Rp ● : JISフランジ
▲ : DINフランジ ● : RpとJISフランジの2種

機種シリーズ名			使用圧力			水素ガス対応	開動作		接続口径														記載ページ		
			低圧	中間圧	中圧		クイック	スロー	8A	15A	20A	25A	32A	40A	50A	65A	80A	100A	125A	150A	200A	250A			
									1/4	1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4	5	6	8	10			
ガス複合弁	GHV		○	○		○	○																3		
	GRV		○	○	○	○																		7	
電磁弁	DSG		○			○	○																	9	
	DSG-W		○			○	○																	13	
	VNA		○	○		○	○																	15	
	VLA		○	○		○		○																	21
	VNA-R/RH		○	○	○	○	○																		25
	VNR		○	○		○	○																		29
中圧ガス安全遮断制御システム	TAC-25				○		○	○																	31
	VNM		○	○	○	○	○																		35
	VLM		○	○	○	○		○																	37
	C25N-B				○																				39
安全遮断弁	VNM-25-K		○	○	○		○																	41	
液動弁	HK1		○	○	○	○		○																	43
	HS		○	○	○	○		○																	47