


先导式3·5通阀

M4GB1※R·MN4GB1※R

隔板型先导单向阀




3,5 PORT PILOT OPERATED VALVE M4GB1※R/MN4GB1※R Series

特点


- 最适用于气管直径为φ32的气缸驱动
- 可手动排出2次侧残压

用途

- 可进行长时间的气缸的中间停止、位置保持。




防坠落



2位单电控·双电控


中间停止




ABR连接

残压排出用手动装置


■ 非锁定手动装置



■ 锁定手动装置



■ 无手动装置



使用前请务必阅读背面的“使用注意事项”和《空压阀综合》(样本编号:CB-023SC)中的“使用注意事项”。

CKD Corporation

CC-1527C

4G隔板型先导单向阀

规格

项目	4G1R-PC-M※
使用流体	压缩空气
最高使用压力	MPa 0.7
最低使用压力	MPa 0.2
耐压力	MPa 1.05
有效截面积	mm ² 1.5(带电磁阀)
环境温度	°C -5~55(不得冻结)
使用流体温度	°C 5~55
给油 ^{注1}	无需
环境	无法在腐蚀性气体环境下使用
重量	g 22


注1:给油时,请使用1种ISO VG32透平油。给油过多会导致动作不稳定。

关于刊载型号



本样本中仅记载此次追加的先导单向阀的型号。
有关4GB・M4GB・MN4GB系列的详情(规格・型号・使用注意事项等),请参阅《空压阀综合》(样本编号:CB-023SC)。

集成阀型号表示方法

集成阀型号



模块集成型号



单体型号





先导单向阀

残压排气功能	
M	非锁定手动装置
M1	锁定手动装置
无符号	无手动装置

型号选择时的注意事项

- 注1: 请在集成规格书中标明隔板的安装位置、残压排气功能的选择。
注2: A/B口接头为弯管型时,无法选择隔板型先导单向阀。
注3: 不对应隔板的多级叠加。
注4: 不能组合隔板与遮蔽板。
注5: 可装载隔板型先导单向阀的配管方式只有底板配管型。
注6: 在省配线集成阀上追加垫块时,插座组件的导线长度不够将无法连接。请更换阀模块。

外形尺寸图



需从日本出口本产品及其相关技术或软件时, 根据日本法律请务必注意防止将其用于与军火、武器相关的用途中。
If the goods and/or their replicas, the technology and/or software found in this catalog are to be exported from Japan, Japanese laws require the exporter makes sure that they will never be used for the development and/or manufacture of weapons for mass destruction.

喜开理(上海)机器有限公司

营业本部

上海市徐汇区虹梅路1905号远中科研大楼6楼601
电话 (021) 61911888 传真 (021) 60905357

200233

<Website>
<https://www.ckd.sh.cn/>

●出于改良的目的, 本样本上记载的产品规格及外观可能会进行变更, 恕不另行通知, 敬请谅解。
©CKD Corporation 2021 All copy rights reserved.
©喜开理(上海)机器有限公司 2021版权所有