





LCM
LCR
LCG
LCW
LCX
STM
STG
STS・STL
STR2
UCA2
ULK※
JSK/M2
JSG
JSC3・JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3※
NHS
HRL
LN
卡爪
卡盘
机械卡爪・卡盘
缓冲器
FJ
FK
速度控制器
卷末

种类	型 号 JIS符号	缸径 (mm)	行程(mm)									
			10	20	30	40	50	75	100	125	150	
双作用・单活塞杆型	LCR 	φ6	●	●	●	●	●					
		φ8	●	●	●	●	●	●				
		φ12	●	●	●	●	●	●	●			
		φ16	●	●	●	●	●	●	●	●		
		φ20・φ25	●	●	●	●	●	●	●	●	●	
双作用・防坠落型	LCR-Q 	φ8	●	●	●	●	●	●				
		φ12	●	●	●	●	●	●	●			
		φ16	●	●	●	●	●	●	●	●		
		φ20・φ25	●	●	●	●	●	●	●	●	●	
双作用・单活塞杆型 洁净规格	LCR-P7※ 	φ6	●	●	●	●	●					
		φ8	●	●	●	●	●	●				
		φ12	●	●	●	●	●	●	●			
		φ16	●	●	●	●	●	●	●	●		
		φ20・φ25	●	●	●	●	●	●	●	●	●	
双作用・微速型	LCR-F 	φ12	●	●	●	●	●	●	●			
		φ16	●	●	●	●	●	●	●	●		
		φ20・φ25	●	●	●	●	●	●	●	●	●	
双作用・微速型 洁净规格	LCR-F-P7※ 	φ12	●	●	●	●	●	●	●			
		φ16	●	●	●	●	●	●	●	●		
		φ20・φ25	●	●	●	●	●	●	●	●	●	

●：标准 ◎：准标准 ○：可制作 ■：不可制作

	选择项																							开关	记载页码			
	行程调整用挡块						缓冲器型挡块						两侧并用型双挡块						单侧混载型挡块混合				带缓冲					
	挡块位置 ①	挡块位置 ②	挡块位置 ③	挡块位置 ④	挡块位置 ①・③	挡块位置 ②・④	挡块位置 ①	挡块位置 ②	挡块位置 ③	挡块位置 ④	挡块位置 ①・③	挡块位置 ②・④	A1＋金属挡块	A2＋金属挡块	A3＋金属挡块	A4＋金属挡块	A5＋金属挡块	A6＋金属挡块	A1＋S3	A2＋S4	A3＋S1	A4＋S2	不带开关槽			带开关槽	附带螺堵	
	S1	S2	S3	S4	S5	S6	A1	A2	A3	A4	A5	A6	W1	W2	W3	W4	W5	W6	C1	C2	C3	C4	B	BL	N			
	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	58
	○	○					○	○					○	○									○	○		○	84	
	○	○	○	○	○	○																			○	○	94	
	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○			○	○	112	
	○	○	○	○	○	○																			○	○	118	

● 挡块位置



LCM
LCR
LCG
LCW
LCX
STM
STG
STS・STL
STR2
UCA2
ULK※
JSK/M2
JSG
JSC3・JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3※
NHS
HRL
LN
卡爪
卡盘
机械卡爪・卡盘
缓冲器
FJ
FK
速度控制器
卷末