

()内的数值表示低速型、微速型或低流量型。

机种名称・外观	型号	配管口径 (Rc或R)						适用气管外径						有效截面积 (mm ²)		流量(ℓ/min)ANR 0.5MPa时		适用缸径 (mm)	记载 页码	
		M3	M5	1/8	1/4	3/8	1/2	φ1.8	φ3.2	φ4	φ6	φ8	φ10	φ12	自由流向	控制流向	自由流向			控制流向
● 带刻度盘 调速阀 	DSC-C-M5-4-P7※		●							●					1.5	0.9(0.3)(0.1)	100	60(20)(6.7)	φ6~φ25	900
	DSC-C-M5-6-P7※		●								●				1.5	0.9(0.3)(0.1)	100	60(20)(6.7)	φ6~φ25	
	DSC-(C)-6-4-P7※			●						●					3.2	2.4(0.9)(0.2)	210	160(60)(13)	φ15~φ32	
	DSC-(C)-6-6-P7※			●						●					4	3(0.9)(0.2)	270	200(60)(13)	φ15~φ32	
	DSC-(C)-6-8-P7※			●							●				4	3(0.9)(0.2)	270	200(60)(13)	φ15~φ32	
	DSC-8-6-P7※				●					●					7	5(2)	470	320(130)	φ20~φ50	
	DSC-8-8-P7※				●						●				8	6(2)	530	400(130)	φ20~φ50	
	DSC-8-10-P7※				●								●		8	6(2)	530	400(130)	φ20~φ50	
	DSC-10-6-P7※					●				●					10	6(4)	670	400(270)	φ32~φ75	
	DSC-10-8-P7※					●					●				15	10.5(4)	1000	700(270)	φ32~φ75	
	DSC-10-10-P7※					●						●			16	12(4)	1070	800(270)	φ32~φ75	
	DSC-10-12-P7※					●							●		16	12(4)	1070	800(270)	φ32~φ75	
	DSC-15-10-P7※						●						●		22	17(6)	1470	1120(400)	φ40~φ100	
	DSC-15-12-P7※						●							●	24	17.5(6)	1600	1200(400)	φ40~φ100	
● 气口直接连接・ 弯管型 	SC3R-M5-P7※		●											1.2	0.7	80	47	φ6~φ16	908	
	SC3R-6-P7※			●										4.0	3.6	270	240	φ15~φ32		
	SC3R-8-P7※				●									7.5	7	500	470	φ20~φ50		
	SC3R-10-P7※					●								16	15	1100	1100	φ32~φ75		
	SC3R-15-P7※						●							24	24	1600	1600	φ40~φ110		
● 弯管型・ 带快插接头 	SC3W-M3-3-P7※	●						●						0.4(0.3)	0.3(0.08)	27(20)	20(5.9)	φ4~φ8	910	
	SC3W-M3-4-P7※	●							●					0.4(0.3)	0.3(0.08)	27(20)	20(5.9)	φ4~φ8		
	SC3W-M5-3-P7※							●						1.3(1.2)	1.2(0.1)	87(80)	80(6.7)	φ6~φ25		
	SC3W-M5-4-P7※		●						●					1.3(1.2)	1.2(0.1)	87(80)	80(6.7)	φ6~φ25		
	SC3W-M5-6-P7※		●							●				1.3(1.2)	1.2(0.1)	87(80)	80(6.7)	φ6~φ25		
	SC3W-6-4-P7※			●					●					3.2(3.2)	2.8(0.2)	210(210)	190(13)	φ15~φ32		
	SC3W-6-6-P7※			●						●				4.0(4.0)	3.6(0.2)	270(270)	240(13)	φ15~φ32		
	SC3W-6-8-P7※			●							●			4	3.6	270	240	φ15~φ32		
	SC3W-8-6-P7※				●					●				7	6.5	470	430	φ20~φ50		
	SC3W-8-8-P7※				●						●			7.5	7	500	470	φ20~φ50		
	SC3W-8-10-P7※				●							●		8	7	530	470	φ20~φ50		
	SC3W-10-6-P7※					●				●				10	10	650	650	φ32~φ75		
	SC3W-10-8-P7※					●					●			15	14	1000	930	φ32~φ75		
	SC3W-10-10-P7※					●						●		16	15	1100	1000	φ32~φ75		
	SC3W-10-12-P7※					●							●	16	15	1100	1000	φ32~φ75		
	SC3W-15-10-P7※						●					●		22	22	1500	1500	φ40~φ100		
	SC3W-15-12-P7※						●						●	24	24	1600	1600	φ40~φ100		

()内的数值表示低速型。

机种名称・外观	型号	配管口径 (Rc或R)						适用气管外径						有效截面积(mm ²)		流量(ℓ/min)ANR 0.5MPa时		适用缸径 (mm)	记载 页码	
		M3	M5	1/8	1/4	3/8	1/2	φ1.8	φ3.2	φ4	φ6	φ8	φ10	φ12	自由流向	控制流向	自由流向			控制流向
● 中口径型 Rc1/8~Rc1/2 	SCL1-6-P7※			●											11	8	730	530	φ20~φ50	914
	SCL1-8-P7※				●										14	13	930	870	φ32~φ75	
	SCL1-10-P7※					●									39	22	2600	1500	φ50~φ140	
	SCL1-15-P7※						●								43	36	2900	2400	φ80~φ160	
● 直管型 带快插接头 	SCL2-04-H22-P7※							●							(0.2)	(0.15)	13	10	φ4~φ25	916
	SCL2-04-H42(24)-P7※							●	●						(0.2)	(0.15)	13	10	φ4~φ25	
	SCL2-04-H44-P7※								●						1.9	1.9(0.2)	130	130(13)	φ4~φ25	
	SCL2-06-H66-P7※									●					4.5	4.5(0.2)	300	300(13)	φ6~φ40	
	SCL2-08-H66-P7※									●					6	6	400	400	φ20~φ50	
	SCL2-08-H88-P7※										●				8	8	550	550	φ20~φ50	
	SCL2-10-H88-P7※										●				13.5	13.5	900	900	φ32~φ75	
	SCL2-10-H1010-P7※											●			16.5	16.5	1100	1100	φ32~φ75	
	SCL2-10-H1212-P7※												●		18	18	1200	1200	φ32~φ75	
● 进排气直管型 带快插接头 	SCD2-04-H22-P7※							●							—	(0.15)	—	(10)	φ4~φ25	916
	SCD2-04-H42-P7※							●	●						—	(0.15)	—	(10)	φ4~φ25	
	SCD2-04-H44-P7※								●						—	1.5(0.2)	—	100(13)	φ4~φ25	
	SCD2-06-H66-P7※									●					—	3.7(0.2)	—	250(13)	6~φ40	
	SCD2-08-H66-P7※									●					—	5	—	330	φ20~φ50	
	SCD2-08-H88-P7※										●				—	6	—	400	φ20~φ50	
	SCD2-10-H88-P7※										●				—	11	—	750	φ32~φ75	
	SCD2-10-H1010-P7※											●			—	12.5	—	850	φ32~φ75	
	SCD2-10-H1212-P7※												●		—	13	—	900	φ32~φ75	
● 针阀 带快插接头 	SCL2-N-04-H44-010								●						—	0.2	—	13	—	920
	SCL2-N-04-H44-050								●						—	0.7	—	50	—	
	SCL2-N-06-H66-010									●					—	0.2	—	13	—	
	SCL2-N-06-H66-050									●					—	0.7	—	50	—	
	SCL2-N-06-H66-150									●					—	2.2	—	150	—	
	SCL2-N-08-H66-300									●					—	4.5	—	300	—	
	SCL2-N-08-H88-300										●				—	4.5	—	300	—	