










4GA 4GB TT1 系列													
电动执行器		空压气缸		助力装置		空压阀		FRL·辅助元件		真空元件		流体控制阀	
F P 1		F P 1		F P 1		F P 1		F P 1		F P 1		F P 1	
系列外观													
机种型号													
位置 先导气口数 JIS符号													
阀能力													
流量特性 C (dm³/(s·bar))													
适用缸径(φ)													
单体	4GA		直接配管	3 通	3GA1		● 3通阀 2位单电控NC型 	0.70	20~40				
					3GA2				40~80				
					3GA3				63~100				
				5 通	4GA1		2位单电控NO型 	0.66~0.70	20~40				
					4GA2				40~80				
					4GA3				63~100				
	4GB		底板配管	5 通	4GB1		● 5通阀 2位单电控 	1.1~1.3	20~40				
					4GB2				40~80				
					4GB3				63~100				
集成阀(金属底板)	M4GA		直接配管	直接安装型	M4GA1		2位双电控 	0.7~1.0	20~40				
					M4GA2				40~80				
					M4GA3				63~100				
				DIN 导轨 安装型(-D)	M4GA1		3位中封 	0.7~1.0	20~40				
					M4GA2				40~80				
					M4GA3				63~100				
	M4GB		底板配管	直接安装型	M4GB1		3位A·B·R连接 	0.68~1.0	20~40				
					M4GB2				40~80				
					M4GB3				63~100				
				DIN 导轨 安装型(-D)	M4GB1		3位P·A·B连接 	0.68~1.0	20~40				
					M4GB2				40~80				
					M4GB3				63~100				

注1:有效截面积S与音速导率C的换算为 $S \approx 5.0 \times C$ 。

	切换位置								A · B 气口配管气口								选型页码	
	3 通		单电控	双电控	中封	A B R 连接	P A B 连接	混合型	快插接头				内螺纹					
	常闭	常通							φ 4	φ 6	φ 8	φ 10	M 5	R C 1 / 8	R C 1 / 4	R C 3 / 8		
									C4	C6	C8	C10	M5	06	08	10		
	●	●							●	●			●				181	
	●	●							●	●	●			●				
	●	●								●	●	●			●			
			●	●	●	●	●		●	●			●					
			●	●	●	●	●		●	●	●			●				
			●	●	●	●	●			●	●	●			●			
			●	●	●	●	●							●			183	
			●	●	●	●	●								●			
			●	●	●	●	●								●	●		
	●	●	●	●	●	●	●	●	●	●			●				181	
									●	●	●			●				
										●	●	●				●		
	●	●	●	●	●	●	●	●	●	●			●				183	
									●	●	●			●				
										●	●	●				●		
			●	●	●	●	●	●	●	●			●				183	
									●	●	●			●				
										●	●	●				●		
		●	●	●	●	●	●	●	●			●				183		
								●	●	●			●					
									●	●	●				●			

电动执行器	空压气缸	助力装置	空压阀	FRL·辅助元件 电子元件	真空元件	主管路元件	流体控制阀	主管路元件	抗菌·除菌过滤器	真空元件	流体控制阀
-------	------	------	-----	------------------	------	-------	-------	-------	----------	------	-------