


体系表

带高精度导向 无杆气缸 SRM3系列

SCP※3
CMK2
CMA2
SCM
SCG
SCA2
SCS2
CKV2
CAV2・COVP/N2
SSD2
SSG
SSD
CAT
MDC2
MVC
SMG
MSD・MSDG
FC※
STK
SRL3
SRG3
SRM3
SRT3
MRL2
MRG2
SM-25
缓冲器
FJ
FK
调速阀
卷末

种类	型号 JIS符号	缸径(mm)	标准行程 (mm)												
			200	300	400	500	600	700	800	900	1000	1100	1200	1300	1400
双作用型	SRM3 	相当于φ25・ 相当于φ32	●	●	●	●	●	●	●	●	●				
		相当于φ40・ 相当于φ63	●	●	●	●	●	●	●	●	●	●	●	●	
双作用・防坠落型	SRM3-Q	相当于φ25・ 相当于φ32	●	●	●	●	●	●	●	●	●				
		相当于φ40・ 相当于φ63	●	●	●	●	●	●	●	●	●	●	●	●	

●：标准、◎：准标准、■：不可制作

标准行程 (mm)							最小行程	最大行程	中间行程	缓冲				选择项								开关	记载页码
										不带缓冲	两侧带缓冲	R侧带缓冲	L侧带缓冲	全行程调整两侧带缓冲	全行程调整R侧带缓冲	全行程调整L侧带缓冲	全行程调整部件后置型	全行程调整两侧轻负荷带缓冲	全行程调整R侧轻负荷带缓冲	全行程调整L侧轻负荷带缓冲	防紫色化		
										N	B	R	L	A	A1	A2	A3	E	E1	E2	P6		
	1500	1600	1700	1800	1900	2000	(mm)	(mm)	(每mm)	N	B	R	L	A	A1	A2	A3	E	E1	E2	P6		
							50	1000	1	●	●	●	●	◎	◎	◎	◎	◎	◎	◎	●	◎	1676
	●	●	●	●	●	●	80	2000		●	●	●	●	◎	◎	◎	◎	◎	◎	◎	●		
							50	1000	1	●	●	●	●	◎	◎	◎	◎	◎	◎	◎	●	◎	1676
	●	●	●	●	●	●	80	2000		●	●	●	●	◎	◎	◎	◎	◎	◎	◎	●		

SCP※3
CMK2
CMA2
SCM
SCG
SCA2
SCS2
CKV2
CAV2・COVP/N2
SSD2
SSG
SSD
CAT
MDC2
MVC
SMG
MSD・MSDG
FC※
STK
SRL3
SRG3
SRM3
SRT3
MRL2
MRG2
SM-25
缓冲器
FJ
FK
调速阀
卷末