

体系表

新移栽系统 NHS系列

LCM
LCR
LCG
LCW
LCX
STM
STG
STS・STL
STR2
UCA2
ULK※
JSK/M2
JSG
JSC3・JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3※
NHS
HRL
LN
卡爪
卡盘
机械卡爪・卡盘
缓冲器
FJ
FK
速度控制器
卷末

种类	可搬送重量 (kg)															
	X轴				Z轴									X轴		
	10	15	30	50	3	4	5	6	7	10	12	20	33	10	15	
NSR (X轴模块)	●	●	●	●										50~2000	50~2000	
NHS-H (H : Z轴模块 HRL)	●	●	●	●			●		●	●	●	●	●	50~2000	50~2000	
NHS-S (S : Z轴模块 STL-B)	●	●	●	●	●				●		●		●	50~2000	50~2000	

●：标准、■：不可制作

行程(mm)															X轴 最大行程	Z轴气缸	记载页码
	X轴		Z轴														
	30	50	30	40	50	75	100	125	150	175	200	250	300	301 ~ 600			
	50~2000	50~2000													2000	—	1422
	50~2000	50~2000			●	●	●	●	●		●	●	●	●	2000	HRL	1430
	50~2000	50~2000			●	●	●	●	●	●	●				2000	STL-B	1440

LCM
LCR
LCG
LCW
LCX
STM
STG
STS・STL
STR2
UCA2
ULK※
JSK/M2
JSG
JSC3・JSC4
USSD
UFCD
USC
UB
JSB3
LMB
LML
HCM
HCA
LBC
CAC4
UCAC2
CAC-N
UCAC-N
RCS2
RCC2
PCC
SHC
MCP
GLC
MFC
BBS
RRC
GRC
RV3※
NHS
HRL
LN
卡爪
卡盘
机械卡爪・卡盘
缓冲器
FJ
FK
速度控制器
卷末