



与电流成正比进行流量控制 超小型的10mm阀宽, 优异的静音性。

最大功耗1W的节能设计。
搭载在集成阀上, 可集成。

宽度10mm




● 流量特性




※根据个体差异、配管条件不同, 流量会产生差异, 敬请注意。

● 用途示例



半导体制造工序的绝缘涂覆



线圈绕线机等的张力控制

小型电磁比例阀 3QB Series

CKD Corporation

<https://www.ckd.co.jp/zh/>

LN-015CS

●本产品为特殊规格产品, 请垂询本公司营业担当。

型号表示方法

■ 单体阀

3QB110P-M5-FL*****-4

①配管口径

②电压

■集成型号

M3QB110P-M5-FL***-4**

※1

①电压

①配管口径	
M5	M5
T6	φ4倒钩接头
②电压	
3	DC24V
4	DC12V

①电压	
3	DC24V
4	DC12V

※1. “*”选择订购型号后, 由我司填写6位数的字符。

规格

基本规格

项 目	内 容
使用流体	压缩空气、N ₂
最低使用压力 MPa	0
最高使用压力 MPa	0.7
耐压力 MPa	1.05
环境温度 ℃	-5~50(不得冻结)
流体温度 ℃	5~50
给油	不可
防护等级	防尘
耐振动 m ² /s	30以下
耐冲击 m ² /s	150以下

电气规格


项 目	内 容	
	DC12V	DC24V
线圈电流	mA	0~80
功耗	W	0~1
绝缘等级		B
浪涌吸收器		无
指示器		无

流量特性

项 目	内 容	
	DC12V	DC24V
流量调节范围 L/min	0~9	
迟滞量 %	10	20

※为特性值，并非保证值。

外形尺寸图



需从日本出口本产品及其相关技术或软件时，根据日本法律请务必注意防止将其用于与军火、武器相关的用途中。
If the goods and/or their replicas, the technology and/or software found in this catalog are to be exported from Japan, Japanese laws require the exporter makes sure that they will never be used for the development and/or manufacture of weapons for mass destruction.

喜开理(上海)机器有限公司

营业本部

上海市徐汇区虹梅路1905号远中科研大楼6楼601
电话 (021) 61911888 传真 (021) 60905357

200233

<Website>

<https://www.ckd.sh.cn/>

●出于改良的目的，本样本上记载的产品规格及外观可能会进行变更，恕不另行通知，敬请谅解。

©CKD Corporation 2025 All copy rights reserved.

©喜开理（上海）机器有限公司 2025版权所有



官方公众号



官方视频号

2025.3