

将执行器侧无法安装的调速阀 与电磁阀集成一体化

电磁阀部

调整针阀

- 每45°的防回转机构
- 增强分段定位感
提升操作性



速度控制阀

有效截面积[自由流向]：1.0mm²


有效截面积[控制流向]：0.3mm²

流量调节范围：0.8~7.0L/min (0.35MPa)

特点

- 执行器的动作速度可调节
(排气节流回路)
- 采用速度控制阀一体化的紧凑设计，
减少了执行器侧的空间
- 可通过电磁阀集成调节点动执行器的
速度控制

回路图符号



带速度控制阀 MN3/4E0 Series

CKD Corporation

<https://www.ckd.co.jp/zh/>

LN-019CS

●本产品为特殊规格产品，请垂询本公司营业担当。

型号表示方法 ■MN3E0、MN4E0系列



※1. “*”表示选择订购型号后，由我司填写6位数的字符。
※2. 有关MN3E0、MN4E0系列的详情(规格、型号等)，请参阅《方向控制阀①》(样本编号：RJ-011CS)。
※3. 无法选择切换位置分类“3”、“4”、“5”。



规格


通用规格

项 目	内 容
使用流体	压缩空气
最低使用压力 MPa	0.2
最高使用压力 MPa	0.7
耐压力 MPa	1.05
给油	不可
防护等级	防尘
使用温度 ℃	5~55
流体温度 ℃	5~55
耐振动 m/s ²	50以下
耐冲击 m/s ²	300以下
环境	不可在腐蚀性气体环境中使用

速度控制阀规格

项 目	内 容
回路形式	排气节流
有效截面积 自由流向 mm ²	1.0
(最大流量时) 控制流向 mm ²	0.3

外形尺寸图



需从日本出口本产品及其相关技术或软件时，根据日本法律请务必注意防止将其用于与军火、武器相关的用途中。
If the goods and/or their replicas, the technology and/or software found in this catalog are to be exported from Japan, Japanese laws require the exporter makes sure that they will never be used for the development and/or manufacture of weapons for mass destruction.

喜开理(上海)机器有限公司

营业本部

上海市徐汇区虹梅路1905号远中科研大楼6楼601
电话 (021) 61911888 传真 (021) 60905357

200233

<Website>
<https://www.ckd.sh.cn/>

●出于改良的目的，本样本上记载的产品规格及外观可能会进行变更，恕不另行通知，敬请谅解。
©CKD Corporation 2025 All copy rights reserved.
©喜开理（上海）机器有限公司 2025版权所有



官方公众号



官方视频号