


Intrinsically safe explosion-proof Pilot operated 3, 5-port valve **4GD/E EX Series**



Smallest explosion-proof class

Intrinsically safe explosion-proof solenoid valves from valve widths of 10 mm and up

4GD/E1 to 4

Explosion-proof performance Ex ib IIC T4 Gb



China Conformity Certificate No. (CCC) 2020322307000310



China explosion-proof standard NEPSI acquired GYJ19.1311X




IECEx IBE 19.0008



Korea Conformity Certificate No. 20-KA4B0-0766



Taiwan Conformity Certificate No. TD040272



Smallest explosion-proof class Intrinsically safe explosion-proof solenoid valves from valve widths of 10 mm and up **4GD/E1 to 4 Series**

Explosion-proof performance Ex ib IIC T4 Gb

CCC China Conformity Certificate No. (CCC) 2020322307000310

NEPSI China explosion-proof standard NEPSI acquired GYJ19.1311X

IEC IECEx IBE 19.0008

Korea Conformity Certificate No. 20-KA4B0-0766

Taiwan Conformity Certificate No. TD040272



Degree of protection

IP67

Space saving/lightweight Ideal for narrow explosion-proof areas.



Lineup of types with two 3-port valves integrated

4GE3 and 4F3 footprint and weight comparison


Footprint
84%
Reduced

Ultra-lightweight
82%
Reduced

*Conventional 8-station model comparison



High durability



CAE analysis used to optimize seal function

Durability count
50 million
or more

Wide-ranging series lineup

Model	Cylinder operation	Compatible cylinder bore													
		20	25	30	32	40	50	63	75	80	100	125	140	160	
4G1	Low speed	●					●								
	High speed	●			●										
4G2	Low speed	●								●					
	High speed	●					●								
4G3	Low speed	●									●				
	High speed	●						●							
4G4	Low speed	●												●	
	High speed	●												●	

* The table is for reference. Varies according to piping conditions, load factor, etc.
For details of Component selection, refer to Pneumatic Valves (No. CB-023SA) system selection.

High environmental performance, reliability and ease of use

Prevents manual malfunction


Manual override has a protective cover.



Helps prevent misoperation problems

[Exhaust check valve]

Equipped as standard with both metal base and resin block. (4G*1 to 4G*3 EX compatible)



2-direction wiring outlet


Wiring direction can be selected according to the solenoid valve installation location.



Air supply/exhaust spacer

[Air supply spacer]

Pressure can be changed and air supplied for each valve. Ideal for cylinder thrust adjustment by increasing/decreasing individual valve pressure.



[Exhaust spacer]

Individual exhaust prevents single acting cylinder malfunction.

Applications Ideal explosion-proof specifications for narrow spaces

Coating equipment




Liquid conditioning equipment



Analysis equipment



Solenoid valve space can be greatly reduced when intrinsic safety explosion-proof structures are required.



Discrete valve
Body piping


3GD1, 2/4GD1, 2, 3, 4*0EX Series

● Cylinder bore size: ø20 to ø140




JISCode


- Two 3-port valves integrated
(A side valve: NC, B side valve: NC)




- 5-port valve
2-position single




- 2-position double




- 3-position
All ports closed



- 3-position A/B/R connection



- 3-position P/A/B connection



Common specifications

Item	Description
Valve and operation	Pilot operated soft spool valve
Working fluid	Compressed air
Max. working pressure MPa	0.7
Min. working pressure MPa	0.2
Proof pressure MPa	1.05
Ambient temperature °C	-5 to 55 (no freezing)
Fluid temperature °C	5 to 55
Manual override	Non-locking/locking common
Pilot exhaust method	Main valve/pilot valve common exhaust
Lubrication *1	Not required
Degree of protection *2	IP67
Vibration resistance cm/s ²	50 or less
Shock resistance m/s ²	300 or less
Atmosphere	Cannot be used in corrosive gas environments

Solenoid specifications

Item	Description
Rated voltage V	12 DC
Voltage fluctuation range	+10% -20%
Rated current A	0.05
Power consumption W	0.6
Thermal class	B

*1 Use turbine oil Class 1 ISO VG32 for lubrication. Excessive or intermittent lubrication results in unstable operation.

*2 Tested according to the test method for IP67 (IEC60529) standards. Note that while the unit is protected from dust and water, it cannot be used immersed in water. Countermeasures such as covering the unit should also be taken if using in environments where it will be constantly exposed to dust or water.

Intrinsic safety explosion-proof specifications

Item	Description
Types of explosion-proof structures	Intrinsic safety explosion-proof structure (ib)
Target gas or above listed ignitability and flame-proof grade	Ex ib IIC T4 Gb
Barrier input voltage	24 VDC
Intrinsic safety circuit allowable voltage U _i	30 VDC
Intrinsic safety circuit allowable current I _i	200 mA
Intrinsic safety circuit allowable power P _i	0.68 W
Internal inductance L _i	Value that can be ignored
internal capacitance C _i	Value that can be ignored

Individual specifications

Port size	3GD1/4GD1	3GD2/4GD2	4GD3	4GD4
2, 4-port (Port A/B)	Push-in fitting ø4, ø6 M5	Push-in fitting ø4, ø6, ø8 Rc1/8	Push-in fitting ø6, ø8, ø10 Rc1/4	Push-in fitting ø8, ø10, ø12 Rc3/8
1, 3, 5-port (Port P/R1/R2)	M5	Rc1/8	Rc1/4	Rc1/4

Performance/characteristics by model

Item		3GD1		3GD2		4GD1		4GD2		4GD3		4GD4	
		ON	OFF	ON	OFF	ON	OFF	ON	OFF	ON	OFF	ON	OFF
Response time ms	Two 3-port valves integrated	15	35	20	50	-	-	-	-	-	-	-	-
	2-position	Single	-	-	-	15	35	20	40	25	60	100	110
		Double	-	-	-	25	25	30	30	35	35	110	110
	3-position ABR connection	-	-	-	-	20	40	25	45	35	60	100	160

The response times are values under continuous operation at supply pressure of 0.5 MPa, at rated voltage and at 20°C without lubrication. They depend on the pressure and the lubricant quality.

Weight

Item	4GD1	4GD2	4GD3	4GD4
Weight g	2-position Single	61(54)	120(90)	155(112)
	Double	81(74)	140(110)	176(133)
	3-position ABR connection	84(77)	148(118)	187(143)

• Values in () do not include the pipe adaptor. These values include the M8 connector (straight).

• The weight of the two 3-port valves integrated type is the same as that of 2-position double.

3GD1, 2/4GD1, 2, 3, 4*0EX Series

Discrete valve; Body piping

Flow characteristics

Model No.	Solenoid position		P → A/B		A/B → R1/R2	
			C[dm ³ /(s·bar)]	b	C[dm ³ /(s·bar)]	b
3GD1 4GD1	Two 3-port valves integrated		0.98	0.45	0.71	0.34
	2-position		1.2	0.47	0.72	0.37
	3-position	All ports closed	1.1	0.39	0.70	0.34
		ABR connection	1.1	0.33	0.72	0.34
		PAB connection	1.3	0.61	0.72	0.36
3GD2 4GD2	Two 3-port valves integrated		1.8	0.29	2.3	0.32
	2-position		2.4	0.33	2.8	0.30
	3-position	All ports closed	2.2	0.28	2.5	0.28
		ABR connection	2.3	0.26	2.8	0.27
		PAB connection	2.5	0.38	2.4	0.30
4GD3	2-position		3.4	0.29	4.0	0.24
	3-position	All ports closed	3.1	0.27	3.4	0.28
		ABR connection	3.1	0.33	4.1	0.20
		PAB connection	3.5	0.43	3.4	0.32
4GD4	2-position		8.1	0.4	8.0	0.31
	3-position	All ports closed	6.9	0.37	7.5	0.42
		ABR connection	6.9	0.38	8.4	0.34
		PAB connection	8.9	0.37	7.6	0.27

*1 : Formula for converting effective cross-sectional area S and sonic conductance C is $S=5.0 \times C$.

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

3GD1, 2/4GD1, 2, 3, 4*0EX Series

Discrete valve; Body piping

How to order (solenoid valve single unit)

● Single unit

4GD1 1 0 EX - M5 - RN - 4
3GD1 66 0 EX - C4 - RN - 4

A Model No.

B Solenoid position

C Explosion-proof Series

D Port size

E Electrical connections

F Option

G Voltage

A Model No.

3GD1 3GD2 4GD1 4GD2 4GD3 4GD4

Code	Description	3GD1	3GD2	4GD1	4GD2	4GD3	4GD4
B Solenoid position							
1	2-position single			●	●	●	●
2	2-position double			●	●	●	●
3	3-position all ports closed			●	●	●	●
4	3-position ABR connection			●	●	●	●
5	3-position PAB connection			●	●	●	●
66	Two 3-port valves integrated *1 A side valve: Normally Closed B side valve: Normally Closed	●	●				
C Explosion-proof Series							
EX	CCC and NEPSI certification (China) IECEX certified (international) KCs (South Korea), TS (Taiwan) compliant product	●	●	●	●	●	●
D Port size[4(A),2(B)Port]							
Port	4(A)/2(B)Port	Port P/R1/R2 (1)=M5 (2)= Rc1/8 (3)=Rc1/4					
C4	ø4 push-in fitting	(1)	(2)	(1)	(2)		
C6	ø6 push-in fitting	(1)	(2)	(1)	(2)	(3)	
C8	ø8 push-in fitting		(2)		(2)	(3)	(3)
C10	ø10 push-in fitting					(3)	(3)
C12	ø12 push-in fitting						(3)
M5	M5	(1)		(1)			
06	Rc1/8		(2)		(2)		
08	Rc1/4					(3)	
10	Rc3/8						(3)
E Electrical connections *2							
RN	M8 Without connector cable	●	●	●	●	●	●
R1	M8 connector straight cable	●	●	●	●	●	●
R2	M8 L-type connector cable	●	●	●	●	●	●
F Option							
Blank	Manual override of non-locking/locking common (standard)	●	●	●	●	●	●
H	With exhaust check valve *3	●	●	●	●	●	
P	Mounting plate included (2-position single only)			●	●	●	
F	Port A/B filter *4	●	●	●	●	●	●
G Voltage							
4	12 VDC	●	●	●	●	●	●

⚠ Precautions for model No. selection

*1: Dimensions is the same dimensions as the respective 2-position double solenoid.

*2: M8 connector length is 300mm. Select other lengths from page 64 as needed.

*3: 3-position all ports closed and PAB connection are not provided with exhaust check valve specifications (H).

*4: A filter is built into port P as standard.


*5: Explosion-proof barrier sold separately. Select from page 69.

Internal structure diagram and parts list

3GD1660EX

- Two 3-port valves integrated M8 connector Without cable (RN)


A side valve: Normally Closed,
B side valve: Normally Closed



3GD2660EX

- Two 3-port valves integrated M8 connector Without cable (RN)

A side valve: Normally Closed,
B side valve: Normally Closed



Main parts list

Part No.	Part name	Material
1	Coil assembly	-
2	Adapter	Resin
3	Pilot exhaust check valve	Hydrogenated nitrile rubber
4	PistonDAssembly	-
5	Manual override	Resin
6	Piston chamber	Resin
7	Manual protection cover	Resin
8	Cartridge push-in fitting	-
9	Spool assembly	-
10	Body	Aluminum alloy die-casting
11	Pipe adaptor	Aluminum alloy die-casting

Parts list

Part No.	Part name	Model No.
8	Cartridge push-in fitting and related parts	ø4 straight 4G1R-JOINT-C4
		ø6 straight 4G1R-JOINT-C6
		Plug cartridge 4G1R-JOINT-CPG

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use



4GD1*0EX Series

Discrete valve; Body piping

Internal structure diagram and parts list



4GD110EX

- 2-position single
- M8 connector Without cable (RN)




4GD120EX

- 2-position double
- M8 connector Without cable (RN)




4GD1³/₅0EX



- 3-position
- M8 connector Without cable (RN)
- All ports closed



ABR connection



PAB connection



Main parts list

Part No.	Part name	Material
1	Coil assembly	-
2	Adapter	Resin
3	Pilot exhaust check valve	Hydrogenated nitrile rubber
4	Piston D assembly	-
5	Manual override	Resin
6	Piston chamber	Resin
7	Manual protection cover	Resin
8	Cartridge push-in fitting	-
9	Spool assembly	-
10	Body	Aluminum alloy die-casting
11	Spool spring	Stainless steel
12	Cap	Resin
13	Pipe adaptor	Aluminum alloy die-casting


Parts list

Part No.	Part name	Model No.
8	Cartridge push-in fitting and related parts	ø4 straight 4G1R-JOINT-C4
		ø6 straight 4G1R-JOINT-C6
		Plug cartridge 4G1R-JOINT-CPG

Internal structure diagram and parts list


4GD210EX/4GD310EX

- 2-position single
- M8 connector Without cable (RN)




4GD220EX/4GD320EX

- 2-position double
- M8 connector Without cable (RN)



4GD2^{3/4/5}0EX/4GD3^{3/4/5}0EX

- 3-position
- M8 connector Without cable (RN)
- All ports closed



Main parts list

Part No.	Part name	Material
1	Coil assembly	-
2	Adapter	Resin
3	Pilot exhaust check valve	Hydrogenated nitrile rubber
4	Piston D assembly	-
5	Manual override	Resin
6	Piston chamber	Resin
7	Manual protection cover	Resin
8	Cartridge push-in fitting	-
9	Spool assembly	-
10	Body	Aluminum alloy die-casting
11	Spool spring	Stainless steel
12	Cap	Resin
13	Pipe adaptor	Aluminum alloy die-casting

Parts list

Part No.	Part name	Model No.
8	Cartridge push-in fitting and related parts	4G2 ø4 straight 4G2R-JOINT-C4
		4G2 ø6 straight 4G2R-JOINT-C6
		4G2 ø8 straight 4G2R-JOINT-C8
		4G3 ø6 straight 4G3R-JOINT-C6
		4G3 ø8 straight 4G3R-JOINT-C8
		4G3 ø10 straight 4G3R-JOINT-C10

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use



4GD4*0EX Series

Discrete valve; Body piping

Internal structure diagram and parts list



4GD410EX

- 2-position single
- M8 connector Without cable (RN)




4GD420EX

- 2-position double
- M8 connector Without cable (RN)




4GD4³0EX



- 3-position
- M8 connector Without cable (RN)
- All ports closed



ABR connection



PAB connection



Main parts list

Part No.	Part name	Material
1	Coil assembly	-
2	Piston assembly	-
3	Manual override	Resin
4	Piston chamber	Resin
5	Manual protection cover	Resin
6	Spool assembly	-
7	Fitting adapter	Aluminum
8	Body	Aluminum alloy die-casting
9	Cap	Resin
10	Cartridge push-in fitting	-
11	Spool spring	Stainless steel



Parts list

Part No.	Part name	Model No.
-	Cartridge push-in fitting and related parts	4G4-JOINT-C8
-		4G4-JOINT-C10
-		4G4-JOINT-C12



Dimensions

4GD110EX


● 2-position single without connector (RN)





● Mounting plate (P)





Push-in fitting $\varnothing 4$, $\varnothing 6$ (selection)
4(A) port





● M5 female thread (M5)



● M8 connector/straight cable (R1)



● M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

4GD1*0EX Series

Discrete valve; Body piping

Dimensions

4GD120EX

- 2-position double without connector (RN)

3GD1660EX

- Two 3-port valves integrated without connector (RN)

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX



M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX



Related products

Manifold
specifications sheet



Precautions for use





- M5 female thread (M5)



- M8 connector/straight cable (R1)





- M8 connector/L-type cable (R2)





Dimensions

4GD1³EX



- 3-position without connector (RN)





- M5 female thread (M5)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

4GD2*0EX Series





Discrete valve; Body piping

Dimensions




4GD210EX

● 2-position single without connector (RN)



● Mounting plate (P)



*Refer to page 79 for details on mounting holes.







● Rc1/8 female thread (06)



● M8 connector/straight cable (R1)

● M8 connector/L-type cable (R2)





Dimensions

4GD220EX



- 2-position double without connector (RN)

3GD2660EX



- Two 3-port valves integrated without connector (RN)





- Rc1/8 female thread (06)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX











Related products

Manifold
specifications sheet

Precautions for use

Dimensions


● 3-position without connector (RN)




Dimensions

4GD310EX


- 2-position single without connector (RN)




- Mounting plate (P)




- Rc1/4 female thread (08)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use




4GD3*0EX Series

Discrete valve; Body piping



Dimensions

4GD320EX



- 2-position double without connector (RN)





- Rc1/4 female thread (08)



- M8 connector/straight cable (R1)





- M8 connector/L-type cable (R2)





Dimensions

4GD3³/₅0EX



- 3-position without connector (RN)





- Rc1/4 female thread (08)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use





4GD4*0EX Series

Discrete valve; Body piping



Dimensions

4GD410EX



- 2-position single Without connector (RN)





- Rc3/8 female thread (10)



- M8 connector/straight cable (R1)






- M8 connector/L-type cable (R2)





Dimensions

4GD420EX



- 2-position double without connector (RN)





- Rc3/8 female thread (10)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use





4GD4*0EX Series

Discrete valve; Body piping



Dimensions

4GD4³/₅0EX



● 3-position Without connector (RN)





● Rc3/8 female thread (10)



● M8 connector/straight cable (R1)



● M8 connector/L-type cable (R2)



3GD*0EX 4GD*0EX	3GE*0EX 4GE*0EX	M3GD*0EX M4GD*0EX	M3GE*0EX M4GE*0EX	Related products	Manifold specifications sheet	Precautions for use
--------------------	--------------------	----------------------	----------------------	------------------	----------------------------------	---------------------

MEMO



Discrete valve
Base piping


3GE1, 2/4GE1, 2, 3, 4*0EX Series

● Applicable cylinder bore size: ø20 to ø160




JIS symbol


- Two 3-port valves integrated
(A side valve: NC, B side valve: NC)



- 5-port valve




2-position double mounting




3-position


All ports closed



3-position A/B/R connection



3-position P/A/B connection



Common specifications

Item	Description
Valve and operation	Pilot operated soft spool valve
Working fluid	Compressed air
Max. working pressure MPa	0.7
Min. working pressure MPa	0.2
Proof pressure MPa	1.05
Ambient temperature °C	-5 to 55 (no freezing)
Fluid temperature °C	5 to 55
Manual override	Non-locking/locking common (standard)
Pilot exhaust method	Internal pilot
	Main valve/pilot valve common exhaust
Lubrication *1	Not required
Degree of protection *2	IP67
Vibration resistance m/s ²	50 or less
Shock resistance m/s ²	300 or less
Atmosphere	Cannot be used in corrosive gas environments

Solenoid specifications

Item	Description
Rated voltage V	12 DC
Voltage fluctuation range	+10% -20%
Rated current A	0.05
Power consumption W (*3)	0.6
Thermal class	B

*1 Use turbine oil Class 1 ISOVG32 for lubrication. Excessive or intermittent lubrication results in unstable operation.

*2 Tested according to the test method for IP67 (IEC60529) standards. Note that while the unit is protected from dust and water, it cannot be used immersed in water. Countermeasures such as covering the unit should also be taken if using in environments where it will be constantly exposed to dust or water.

Intrinsic safety explosion-proof specifications

Item	Description
Types of explosion-proof structures	Intrinsic safety explosion-proof structure (ib)
Target gas or above listed ignitability and flame-proof grade	Ex ib IIC T4 Gb
Barrier input voltage	24 VDC
Intrinsic safety circuit allowable voltage Ui	30 VDC
Intrinsic safety circuit allowable current Ii	200 mA
Intrinsic safety circuit allowable power Pi	0.68 W
Internal inductance Li	Value that can be ignored
Internal capacitance Ci	Value that can be ignored

Individual specifications

Port size	3GE1/4GE1	3GE2/4GE2	4GE3	4GE4
2, 4-port (Port A/B)	Rc1/8	Rc1/4	Rc1/4, Rc3/8	Rc3/8, Rc1/2
1, 3, 5-port (Port P/R1/R2)	Rc1/8	Rc1/4	Rc1/4, Rc3/8	Rc3/8, Rc1/2

Performance/characteristics by model

Item		3GE1		3GE2		4GE1		4GE2		4GE3		4GE4	
		ON	OFF	ON	OFF	ON	OFF	ON	OFF	ON	OFF	ON	OFF
Response time	Two 3-port valves integrated		15	35	20	50	-	-	-	-	-	-	-
	2-position	Single	-	-	-	-	15	35	20	40	25	60	100
			-	-	-	-	25	25	30	30	35	110	110
	3-position	A/B/R connection		-	-	-	-	20	40	25	45	35	60

The response times are values under continuous operation at supply pressure of 0.5 MPa, at rated voltage and at 20°C without lubrication. They depend on the pressure and the lubricant quality.

Weight

Item			4GE1	4GE2	4GE3	4GE4
Weight g	2-position	Single	97 (54)	173 (91)	246 (117)	551 (241)
		Double	118 (74)	194 (112)	267 (138)	584 (275)
	3-position	ABR connection	120 (77)	202 (120)	277 (148)	616 (306)

• Values in () do not include the pipe adaptor. These values include the M8 connector (straight).

• The weight of the two 3-port valves integrated type is the same as that of 2-position double.

3GE1, 2/4GE1, 2, 3, 4*0EX Series

Discrete valve; Base piping

Flow characteristics

Model No.	Solenoid position		P → A/B		A/B → R1/R2	
			C[dm ³ /(s·bar)]	b	C[dm ³ /(s·bar)]	b
3GE1 4GE1	Two 3-port valves integrated		0.92	0.08	1.1	0.26
	2-position		1.3	0.27	1.2	0.22
	3-position	All ports closed	1.1	0.31	1.1	0.27
		A/B/R connection	1.1	0.31	1.3	0.29
		P/A/B connection	1.4	0.30	1.1	0.26
3GE2 4GE2	Two 3-port valves integrated		1.7	0.42	2.1	0.26
	2-position		2.6	0.20	2.6	0.19
	3-position	All ports closed	2.3	0.32	2.2	0.22
		A/B/R connection	2.2	0.23	2.6	0.16
		P/A/B connection	2.4	0.10	2.4	0.22
4GE3	2-position		4.3	0.24	4.2	0.24
	3-position	All ports closed	3.3	0.40	3.4	0.27
		A/B/R connection	3.3	0.36	4.2	0.18
		P/A/B connection	4.5	0.28	3.4	0.30
4GE4	2-position		11.0	0.19	13.0	0.19
	3-position	All ports closed	9.1	0.11	12.0	0.27
		A/B/R connection	8.8	0.28	13.9	0.25
		P/A/B connection	10.0	0.06	12.0	0.24

*1: Formula for converting effective cross-sectional area S and sonic conductance C is $S \approx 5.0 \times C$.

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

3GE1, 2/4GE1, 2, 3, 4*0EX Series

Discrete valve; Base piping

How to order (solenoid valve single unit)

● Single unit

4GE1 1 0 EX - 06 - RN - 4
3GE2 66 0 EX - 08 - RN - 4

A Model No.

3GE1 3GE2 4GE1 4GE2 4GE3 4GE4

A Model No.

B Solenoid position

C Explosion-proof Series

D Port size

E Electrical connections

F Option

G Voltage

Code	Description	3GE1	3GE2	4GE1	4GE2	4GE3	4GE4
B Solenoid position							
1	2 position single			●	●	●	●
2	2-position double			●	●	●	●
3	3-position all ports closed			●	●	●	●
4	3-position ABR connection			●	●	●	●
5	3-position PAB connection			●	●	●	●
66	Two 3-port valves integrated *1 A side valve: Normally Closed B side valve: Normally Closed	●	●				
C Explosion-proof Series							
EX	CCC and NEPSI certification (China) IECEx certified (international) KCs (South Korea), TS (Taiwan) compliant product	●	●	●	●	●	●
D Port size [ports 4(A), 2(B)]							
Port	4(A)/2(B) port	Port P/R1/R2 (2) = Rc1/8 (3) = Rc1/4 (4) = Rc3/8 (5)=Rc1/2					
06	Rc1/8	(2)	(2)				
08	Rc1/4		(3)	(3)	(3)		
10	Rc3/8				(4)	(4)	
15	Rc1/2					(5)	(5)
00	Valve for base mounting	●	●	●	●	●	●
E Electrical connections *2							
RN	M8 connector without cable	●	●	●	●	●	●
R1	M8 connector straight cable	●	●	●	●	●	●
R 2	M8 connector L-type cable	●	●	●	●	●	●
F Option							
Blank	Manual override of non-locking/locking common (standard)	●	●	●	●	●	●
H	With exhaust check valve *3	●	●	●	●	●	●
F	Port A/B filter *4	●	●	●	●	●	●
G Voltage							
4	12 VDC	●	●	●	●	●	●

⚠ Precautions for model No. selection

*1: Dimensions are the same as the respective 2-position double solenoid.

*2: M8 connector length is 300mm. Select other lengths from page 64 as needed.

*3: 3-position all ports closed and PAB connection are not provided with exhaust check valve specifications (H).

*4: A filter is built into port P as standard.



*5: Explosion-proof barrier sold separately. Select from page 69.

Internal structure diagram and parts list

3GE1660EX

- Two 3-port valves integrated
M8 connector without cable (RN)



A side valve: Normally Closed,
B side valve: Normally Closed
NC/NC



3GE2660EX

- Two 3-port valves integrated
M8 connector without cable (RN)

A side valve: Normally Closed,
B side valve: Normally Closed
NC/NC



Main parts list

Part No.	Part name	Material	Part No.	Part name	Material
1	Coil assembly	-	6	Piston chamber	Resin
2	Adapter	Resin	7	Manual protection cover	Resin
3	Pilot exhaust check valve	Hydrogenated nitrile rubber	8	Spool assembly	-
4	Piston assembly	-	9	Body	Aluminum alloy die-casting
5	Manual override	Resin	10	Sub-plate	Aluminum alloy die-casting

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use



4GE1*0EX Series

Discrete valve; Base piping

Internal structure diagram and parts list



4GE110EX

- 2 position single
- M8 connector without cable (RN)



4GE120EX


- 2-position double
- M8 connector without cable (RN)




4GE1³0EX

- 3-position
- M8 connector without cable (RN)



All ports closed



A/B/R connection



P/A/B connection





Main parts list

Part No.	Part name	Material	Part No.	Part name	Material
1	Coil assembly	-	7	Manual protection cover	Resin
2	Adapter	Resin	8	Spool assembly	-
3	Pilot exhaust check valve	Hydrogenated nitrile rubber	9	Body	Aluminum alloy die-casting
4	Piston D assembly	-	10	Spool spring	Stainless steel
5	Manual override	Resin	11	Cap	Resin
6	Piston chamber	Resin	12	Sub-plate	Aluminum alloy die-casting

Internal structure diagram and parts list



4GE210EX/4GE310EX

- 2 position single
- M8 connector without cable (RN)



4GE220EX/4GE320EX


- 2-position double
- M8 connector without cable (RN)




4GE2³₄0EX/4GE3³₄0EX

- 3-position
- M8 connector without cable (RN)



All ports closed



A/B/R connection



P/A/B connection



Main parts list

Part No.	Part name	Material	Part No.	Part name	Material
1	Coil assembly	-	7	Manual protection cover	Resin
2	Adapter	Resin	8	Spool assembly	-
3	Pilot exhaust check valve	Hydrogenated nitrile rubber	9	Body	Aluminum alloy die-casting
4	Piston D assembly	-	10	Spool spring	Stainless steel
5	Manual override	Resin	11	Cap	Resin
6	Piston chamber	Resin	12	Sub-plate	Aluminum alloy die-casting



4GE4*0EX Series

Discrete valve; Base piping

Internal structure diagram and parts list



4GE410EX

- 2 position single
- M8 connector without cable (RN)



4GE420EX


- 2-position double
- M8 connector without cable (RN)




4GE430EX

- 3-position
- M8 connector without cable (RN)



All ports closed



A/B/R connection



P/A/B connection





Main parts list

Part No.	Part name	Material	Part No.	Part name	Material
1	Coil assembly	-	6	Manual protection cover	Resin
2	Check valve	Hydrogenated nitrile rubber	7	Spool assembly	-
3	Piston assembly	-	8	Body	Aluminum alloy die-casting
4	Manual override	Resin	9	Cap	Resin
5	Piston chamber	Resin	10	Discrete sub-plate	Aluminum alloy die-casting
			11	Spool spring	Stainless steel



Dimensions

4GE110EX



- 2-position single without connector (RN)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

4GE1*0EX Series

Discrete valve; Base piping






Dimensions

4GE120EX



- 2-position double without connector (RN)

3GE1660EX



- Two 3-port valves integrated without connector (RN)



- M8 connector/straight cable (R1)





- M8 connector/L-type cable (R2)





Dimensions

4GE1³/₈0EX



- 3-position without connector (RN)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

4GE2*0EX Series






Discrete valve; Base piping

Dimensions



4GE210EX

● 2-position single without connector (RN)



3GD*0EX 4GD*0EX	3GE*0EX 4GE*0EX	M3GD*0EX M4GD*0EX	M3GE*0EX M4GE*0EX	Related products	Manifold specifications sheet	Precautions for use
--------------------	--------------------	----------------------	----------------------	------------------	-------------------------------	---------------------



● M8 connector/straight cable (R1)



● M8 connector/L-type cable (R2)





Dimensions

4GE220EX



- 2-position double without connector (RN)

3GE2660EX



- Two 3-port valves integrated without connector (RN)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use






4GE2*0EX Series

Discrete valve; Base piping



Dimensions

4GE20EX



- 3-position without connector (RN)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products






Manifold
specifications sheet

Precautions for use



Dimensions

4GE310EX



- 2-position single without connector (RN)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use


4GE3*0EX Series

Discrete valve; Base piping





Dimensions

4GE320EX



- 2-position double without connector (RN)





2-Rc1/4, Rc3/8 (selection)
4(A), 2(B) port



- M8 connector/straight cable (R1)




- M8 connector/L-type cable (R2)







Dimensions

4GE3₃0EX



- 3-position without connector (RN)





2-Rc1/4, Rc3/8 (selection)
4(A), 2(B) port



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use






4GE4*0EX Series

Discrete valve; Base piping

Dimensions



4GE410EX

● 2 position single Without connector (RN)





Related products

● M8 connector/straight cable (R1)



Manifold specifications sheet




● M8 connector/L-type cable (R2)





Dimensions

4GE420EX



- 2-position double without connector (RN)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*OEX
M4GE*OEX

Related products

Manifold
specifications sheet

Precautions for use





4GE4*0EX Series

Discrete valve; Base piping



Dimensions

4GE4³₄⁵0EX



● 3-position Without connector (RN)



● M8 connector/straight cable (R1)



● M8 connector/L-type cable (R2)



3GD*0EX 4GD*0EX	3GE*0EX 4GE*0EX	M3GD*0EX M4GD*0EX	M3GE*0EX M4GE*0EX	Related products	Manifold specifications sheet	Precautions for use
--------------------	--------------------	----------------------	----------------------	------------------	----------------------------------	---------------------

MEMO



Individual wiring manifold
Body piping
Direct mount


M3GD1, 2EX/M4GD1, 2, 3, 4EX Series

● Applicable cylinder bore size: ø20 to ø140




JIS symbol


- Two 3-port valves integrated
(A side valve: NC, B side valve: NC)



- 5-port valve
2 position single




2-position double




3-position


All ports closed



3-position A/B/R connection



3-position P/A/B connection



Manifold common specifications

Item	Description
Manifold	Integrated base
Mounting method	Direct mount/DIN rail mount
Air supply and exhaust method	Common supply/common exhaust (With internal exhaust check valve)
Pilot exhaust method	Internal pilot
Piping direction	Valve top direction
Valve and operation	Pilot operated soft spool valve
Working fluid	Compressed air
Max. working pressure MPa	0.7
Min. working pressure MPa	0.2
Proof pressure MPa	1.05
Ambient temperature °C	-5 to 55 (no freezing)
Fluid temperature °C	5 to 55
Manual override	Non-locking/locking common
Lubrication *1	Not required
Degree of protection *2	IP67
ResistanceVibration m/s ²	50 or less
ResistanceImpact m/s ²	300 or less
Atmosphere	Cannot be used in corrosive gas environments

- *1 Use turbine oil Class 1 ISO VG32 for lubrication. Excessive or intermittent lubrication results in unstable operation.
- *2 Tested according to the test method for IP67 (IEC60529) standards. Note that while the unit is protected from dust and water, it cannot be used immersed in water. Countermeasures such as covering the unit should also be taken if using in environments where it will be constantly exposed to dust or water.

Solenoid specifications

Item	Description
Rated voltage V	12 DC
Voltage fluctuation range	+10% -20%
Rated current A	0.05
Power consumption W	0.6
Thermal class	B

Individual specifications

Port size	M3GD1/M4GD1	M3GD2/M4GD2	M4GD3	M4GD4
Max. station No.	20 stations	20 stations	20 stations	15 stations
2, 4-port (port A/B)	Push-in fitting ø4,ø6 M5	Push-in fitting ø4,ø6,ø8 Rc1/8	Push-in fitting ø6,ø8,ø10 Rc1/4	Push-in fitting ø8,ø10,ø12 Rc3/8
1, 3, 5-port (Port P/R1/R2)	Rc1/8	Rc1/4	Rc3/8	Rc1/2
Manifold base Weight calculation formula (n: station No.) g	23n+52	47n+64	74n+88	150n+199

For 10 or more manifold station No. (5 stations for 4G3 and 4G4), use ports on both sides for air supply and exhaust. The manifold base weight is the value for screw specifications.

M3GD1, 2*EX/M4GD1, 2, 3, 4*EX Series

Individual wiring manifold; Body piping

Flow characteristics

Model No.	Solenoid position		P → A/B		A/B → R1/R2	
			C[dm ³ /(s·bar)]	b	C[dm ³ /(s·bar)]	b
M3GD1 M4GD1	Two 3-port valves integrated		0.86	0.31	1.1 (0.66)	0.19 (0.22)
	2-position		0.99	0.20	1.2 (0.70)	0.20 (0.12)
	3-position	All ports closed	0.94	0.23	1.1 —	0.20 —
		A/B/R connection	0.93	0.18	1.3 (0.70)	0.23 (0.02)
		P/A/B connection	1.1	0.28	1.1 —	0.23 —
M3GD2 M4GD2	Two 3-port valves integrated		1.7	0.40	2.3 (1.7)	0.29 (0.32)
	2-position		2.3	0.36	2.9 (1.7)	0.24 (0.33)
	3-position	All ports closed	2.1	0.35	2.5 —	0.32 —
		A/B/R connection	2.2	0.37	2.9 (1.8)	0.32 (0.29)
		P/A/B connection	2.4	0.34	2.5 —	0.33 —
M4GD3	2-position		3.2	0.37	3.8 (2.5)	0.13 (0.28)
	3-position	All ports closed	2.9	0.35	3.3 —	0.35 —
		A/B/R connection	3.0	0.34	3.8 (2.6)	0.12 (0.27)
		P/A/B connection	3.3	0.30	3.3 —	0.32 —
M4GD4	2-position		7.3	0.12	9.0 —	0.17 —
	3-position	All ports closed	6.4	0.15	8.2 —	0.22 —
		A/B/R connection	6.3	0.33	8.9 —	0.26 —
		P/A/B connection	8.0	0.08	8.3 —	0.22 —

*1: Effective cross-sectional area S and sonic conductance C use the conversion formula $S \approx 5.0 \times C$.

*2: Values in () are with the exhaust check valve.

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
Specifications sheet

Precautions for use

M3GD1, 2*EX/M4GD1, 2, 3, 4*EX Series

Individual wiring manifold; Body piping

How to order

Manifold model No.

M 4GD1 1 0 EX - C4 - RN H - 6 - 4

3-port manifold model No.

M 3GD1 66 0 EX - M5 - RN H - 2 - 4

Discrete valve for integrated base

4GD1 1 9 EX - C6 - RN H - 4

3-port discrete valve for integrated base

3GD1 66 9 EX - M5 - RN H - 4

A Model No.

B Solenoid position

C Explosion-proof Series

D Port size

E Electrical connections

F Option

G Mount type

H Station No.

I Voltage

A Model No.

3GD1 3GD2 4GD1 4GD2 4GD3 4GD4

Code	Description	3GD1	3GD2	4GD1	4GD2	4GD3	4GD4
B Solenoid position							
1	2 position single			●	●	●	●
2	2-position double			●	●	●	●
3	3-position all ports closed			●	●	●	●
4	3-position ABR connection			●	●	●	●
5	3-position PAB connection			●	●	●	●
66	Two 3-port valves ^{*1/2} integrated A side valve: Normally Closed B side valve: Normally Closed	●	●				
8	Mix manifold (when there are multiple solenoid positions)	●	●	●	●	●	●

C Explosion-proof Series							
EX	CCC and NEPSI certification (China) IECEX certified (international) KCs (South Korea), TS (Taiwan) compliant product	●	●	●	●	●	●

D Port size [2(B), 4(A) port]							
Port	4(A)/2(B) port	Port P/R1/R2 (2) = Rc1/8 (3) = Rc1/4 (4) = Rc3/8 (5)=Rc1/2					
C4	ø4 push-in fitting	(2)	(3)	(2)	(3)		
C6	ø6 push-in fitting	(2)	(3)	(2)	(3)	(4)	
C8	ø8 push-in fitting		(3)		(3)	(4)	(5)
C10	ø10 push-in fitting					(4)	(5)
C12	ø12 push-in fitting						(5)
CX	Push-in fitting mix ^{*3}	(2)	(3)	(2)	(3)	(4)	(5)
M5	M5	(2)		(2)			
06	Rc1/8		(3)		(3)		
08	Rc1/4					(4)	
10	Rc3/8						(5)

E Electrical connections							
RN	M8 connector without cable	●	●	●	●	●	●
R1	M8 connector straight cable ^{*4}	●	●	●	●	●	●
R2	M8 connector L-type cable ^{*4}	●	●	●	●	●	●

F Option							
Blank	Manual override of non-locking/locking common (standard)	●	●	●	●	●	●
H	With exhaust check valve ^{*5, *7}	●	●	●	●	●	●
F	Port A/B filter ^{*6}	●	●	●	●	●	●
Z1	Air supply spacer ^{*7, *8}	●	●	●	●	●	●
Z3	Exhaust spacer ^{*7, *8}	●	●	●	●	●	●

G Mount type							
Blank	Direct mount	●	●	●	●	●	●


H Station No.							
2	2 stations						
to	to	●	●	●	●	●	2 to 15
20	20 stations (Refer to page 41 for the max. station number)						

I Voltage							
4	12 VDC	●	●	●	●	●	●

⚠ Precautions for model No. selection

- *1 M4GD*80EX when using a mixture of 3, 5-port valves. M3GD*80EX when used with a masking plate.
- *2 Dimensions are the same as the respective 2-position double solenoid.
- *3 The push-in fitting cannot be mixed with the single valve's 4(A) or 2(B) port.
- *4 M8 connector length is 300mm. Select other lengths from page 64 as needed.
- *5 3-position all ports closed and PAB connection are not provided with exhaust check specifications (H). Refer to page 79 for details on the exhaust check valve.
- *6 A filter is built into port P as standard.
- *7 4G4 cannot be selected for exhaust check valves (H), air supply spacers (Z1), or exhaust spacers (Z3).
- *8 Specify the spacer mounting position/quantity in the manifold specifications sheet. Stacking of spacers is not possible. Combination with the masking plate is not supported. Refer to pages 59 to 62 for details.
- *9 Explosion-proof barrier sold separately. Select from page 69.

Manifold configuration explanation and parts list



Main configuration parts list

Part No.	Configuration parts name	Model No.	Item	Remarks
1	Discrete valve for integrated base	4GD <input type="checkbox"/> 9EX- <input type="checkbox"/> <div> Port size - Electrical connections Option - Voltage </div> <div> Solenoid position </div> <div> Series flow rate size </div>	Discrete valve Gasket Mounting screws 2 (PR check valve 2)	Details on page 43
2	Masking plate	3G1/4G1 4G1R-MP 3G2/4G2 4G2R-MP 4G3 4G3R-MP 4G4 4G4R-MP	Masking plate Gasket Mounting screws 2	* Two PR check valves are included with 4G3/4G4.
3	Manifold base assembly	M4GD <input type="checkbox"/> R-00 <div> Option - Station No. </div> <div> Series flow rate size </div>	Manifold base	

Parts list

Part No.	Part name	Model No.	Part No.	Part name	Model No.
-	M8 connector cable	4GEX-M8CC- <input type="checkbox"/> Direction - <input type="checkbox"/> Length *Details on page 64	-	Cartridge push-in fitting and related parts	4G1 ø4 straight 4G1R-JOINT-C4 4G1 ø6 straight 4G1R-JOINT-C6 4G2 ø4 straight 4G2R-JOINT-C4 4G2 ø6 straight 4G2R-JOINT-C6 4G2 ø8 straight 4G2R-JOINT-C8 4G3 ø6 straight 4G3R-JOINT-C6 4G3 ø8 straight 4G3R-JOINT-C8 4G3 ø10 straight 4G3R-JOINT-C10 4G4 ø8 straight 4G4-JOINT-C8 4G4 ø10 straight 4G4-JOINT-C10 4G4 ø12 straight 4G4-JOINT-C12
-	Explosion-proof barrier	Details on pages 69 to 73			

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold specifications sheet

Precautions for use

M4GD1*0EX Series



Individual wiring manifold; Body piping

Dimensions


M4GD1*0EX

● Without connector (RN)


* The two 3-port valve built-in type has the same dimensions as the double model.




● M5 female thread (M5)



● M8 connector/straight cable (R1)



● M8 connector/L-type cable (R2)




Station No.	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	45.3	55.8	66.3	76.8	87.3	97.8	108.3	118.8	129.3	139.8	150.3	160.8	171.3	181.8	192.3	202.8	213.3	223.8	234.3
L ₁	30.3	40.8	51.3	61.8	72.3	82.8	93.3	103.8	114.3	124.8	135.3	145.8	156.3	166.8	177.3	187.8	198.3	208.8	219.3

Dimensions

M4GD2*0EX

- Without connector (RN)


* The two 3-port valve built-in type has the same dimensions as the double model.



- Rc1/8 female thread (06)

- M8 connector/straight cable (R1)

- M8 connector/L-type cable (R2)



Station No.	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	54.0	70.0	86.0	102.0	118.0	134.0	150.0	166.0	182.0	198.0	214.0	230.0	246.0	262.0	278.0	294.0	310.0	326.0	342.0
L ₁	42.0	58.0	74.0	90.0	106.0	122.0	138.0	154.0	170.0	186.0	202.0	218.0	234.0	250.0	266.0	282.0	298.0	314.0	330.0



M4GD3*0EX Series

Individual wiring manifold; Body piping


Dimensions

M4GD3*0EX


● Without connector (RN)




● Rc1/4 female thread (08)



● M8 connector/straight cable (R1)



● M8 connector/L-type cable (R2)





Station No.	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	62.0	81.0	100.0	119.0	138.0	157.0	176.0	195.0	214.0	233.0	252.0	271.0	290.0	309.0	328.0	347.0	366.0	385.0	404.0
L ₁	50.0	69.0	88.0	107.0	126.0	145.0	164.0	183.0	202.0	221.0	240.0	259.0	278.0	297.0	316.0	335.0	354.0	373.0	392.0



Dimensions

M4GD4*0EX


- Without connector (RN)




- Rc3/8 female thread (10)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



Station No.	2	3	4	5	6	7	8	9	10	11	12	13	14	15
L	83	108	133	158	183	208	233	258	283	308	333	358	383	408
L ₁	66	91	116	141	166	191	216	241	266	291	316	341	366	391

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold specifications sheet

Precautions for use



Individual wiring manifold
Base piping
Direct mount


M3GE1, 2EX/M4GE1, 2, 3, 4EX Series

● Applicable cylinder bore size: ø20 to ø140




JIS symbol


- Two 3-port valves integrated
(A side valve: NC, B side valve: NC)



- 5-port valve
2 position single




2-position double




3-position


All ports closed



3-position A/B/R connection



3-position P/A/B connection



Manifold common specifications

Item		Description
Manifold		Integrated base
Mounting method		Direct mount/DIN rail mount
Air supply and exhaust method		Common supply/common exhaust (With internal exhaust check valve)
Pilot exhaust method	Internal pilot	Main valve/pilot valve common exhaust (Standard) (Pilot exhaust check valve built-in)
Piping direction		Side direction of base
Valve and operation		Pilot operated soft spool valve
Working fluid		Compressed air
Max. working pressure MPa		0.7
Min. working pressure MPa		0.2
Proof pressure MPa		1.05
Ambient temperature °C		-5 to 55 (no freezing)
Fluid temperature °C		5 to 55
Manual override		Non-locking/locking common
Lubrication *1		Not required
Degree of protection *2		IP67
Vibration resistance m/s ²		50 or less
Shock resistance m/s ²		300 or less
Atmosphere		Cannot be used in corrosive gas environments

*1 Use turbine oil Class 1 ISO VG32 for lubrication. Excessive or intermittent lubrication results in unstable operation.
*2 Tested according to the test method for IP67 (IEC60529) standards. Note that while the unit is protected from dust and water, it cannot be used immersed in water. Countermeasures such as covering the unit should also be taken if using in environments where it will be constantly exposed to dust or water.

Solenoid Specifications

Item	Description	
Rated voltage	V	12 DC
Voltage fluctuation range		+10% -20%
Holding current	A	0.05
Power consumption	W	0.6
Thermal class		B

Individual specifications

Port size	M3GE1/M4GE1	M3GE2/M4GE2	M4GE3	M4GE4	
				Rc1/4 Rc3/8	Rc1/2
Max. station No.	20 stations	20 stations	20 stations	15 stations	12 stations
2, 4-port (port A/B)	Push-in fitting ø4, ø6 M5	Push-in fitting ø4, ø6, ø8 Rc1/8	Push-in fitting ø6, ø8, ø10 Rc1/4	Push-in fitting ø8, ø10, ø12 Rc1/4, Rc3/8	Rc1/2
1, 3, 5-port (Port P/R1/R2)	Rc1/8	Rc1/4	Rc3/8	Rc3/8	Rc1/2
Manifold base Weight calculation formula (n: station No.)	35n+61	71n+106	113n+170	273n+329	391n+560

For 10 or more manifold station No. (5 stations for 4G3 and 4G4), use ports on both sides for air supply and exhaust. The manifold base weight is the value for screw specifications.

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

M3GE1, 2/M4GE1, 2, 3, 4*EX Series

Individual wiring manifold; BasePiping

Flow characteristics

Model No.	Solenoid position		P → A/B		A/B → R1/R2	
			C[dm ³ /(s·bar)]	b	C[dm ³ /(s·bar)]	b
M3GE1 M4GE1	Two 3-port valves integrated		0.86	0.35	1.1 (0.67)	0.22 (0.23)
	2-position		1.1	0.22	1.2 (0.70)	0.20 (0.10)
	3-position	All ports closed	0.98	0.22	1.1 —	0.24 —
		A/B/R connection	0.97	0.35	1.3 (0.68)	0.22 (0.24)
		P/A/B connection	1.1	0.38	1.1 —	0.21 —
M3GE2 M4GE2	Two 3-port valves integrated		1.7	0.44	2.1 (1.6)	0.32 (0.30)
	2-position		2.4	0.34	2.7 (1.7)	0.24 (0.31)
	3-position	All ports closed	2.2	0.34	2.4 —	0.29 —
		A/B/R connection	2.2	0.34	2.8 (1.8)	0.24 (0.27)
		P/A/B connection	2.4	0.29	2.4 —	0.29 —
M4GE3	2-position		3.5	0.34	3.8 (2.6)	0.11 (0.27)
	3-position	All ports closed	3.1	0.33	3.3 —	0.22 —
		A/B/R connection	3.0	0.30	3.8 (2.7)	0.11 (0.22)
		P/A/B connection	3.6	0.36	3.3 —	0.28 —
M4GE4 1-port size Rc3/8	2-position		6.4	0.42	6.9 —	0.12 —
	3-position	All ports closed	6.0	0.37	6.8 —	0.12 —
		A/B/R connection	6.0	0.31	7.1 —	0.11 —
		P/A/B connection	6.0	0.37	6.8 —	0.13 —
M4GE4 1-port size Rc1/2	2-position		8.3	0.23	9.0 —	0.21 —
	3-position	All ports closed	7.4	0.15	8.8 —	0.19 —
		A/B/R connection	7.5	0.28	9.4 —	0.17 —
		P/A/B connection	7.7	0.21	8.7 —	0.18 —

*1: Effective cross-sectional area S and sonic conductance C use the conversion formula $S \approx 5.0 \times C$.

*2: Values in () are with the exhaust check valve.

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

M3GE1, 2/M4GE1, 2, 3, 4*0EX Series

Individual wiring manifold;BasePiping

How to order

Manifold model No.

M 4GE1 1 0 EX - C4 - RN H - 6 - 4

3-port manifold model No.

M 3GE1 66 0 EX - M5 - RN H - 2 - 4

Discrete valve for integrated base

4GE1 1 9 EX - 00 - RN H - 4

3-port discrete valve for integrated base

3GE1 66 9 EX - 00 - RN H - 4

A Model No.

B Solenoid position

C Explosion-proof Series

D Port size

E Electrical connections

F Option

G Mount type

H Station No.

I Voltage

A Model No.

3GE1 3GE2 4GE1 4GE2 4GE3 4GE4

Code	Description	3GE1	3GE2	4GE1	4GE2	4GE3	4GE4
B Solenoid position							
1	2 position single			●	●	●	●
2	2-position double			●	●	●	●
3	3-position all ports closed			●	●	●	●
4	3-position ABR connection			●	●	●	●
5	3-position PAB connection			●	●	●	●
66	Two 3-port valves *1/2 integrated A side valve: Normally Closed B side valve: Normally Closed	●	●				
8	Mix manifold (when there are multiple solenoid positions)	●	●	●	●	●	●

C Explosion-proof Series							
EX	CCC and NEPSI certification (China) IECEX certified (international) KCs (South Korea), TS (Taiwan) compliant product	●	●	●	●	●	●

D Port size [2(B), 4(A) port]							
Port	4(A)/2(B) port	Port P/R1/R2 (2) = Rc1/8 (3) = Rc1/4 (4) = Rc3/8 (5)=Rc1/2					
C4	ø4 push-in fitting	(2)	(3)	(2)	(3)		
C6	ø6 push-in fitting	(2)	(3)	(2)	(3)	(4)	
C8	ø8 push-in fitting		(3)		(3)	(4)	(4)
C10	ø10 push-in fitting					(4)	(4)
C12	ø12 push-in fitting						(4)
CX	Push-in fitting mix	(2)	(3)	(2)	(3)	(4)	(4)
M5	M5	(2)		(2)			
06	Rc1/8		(3)		(3)		
08	Rc1/4					(4)	(4)
10	Rc3/8						(4)
15	Rc1/2						(5)
00	Valve for base mounting	●	●	●	●	●	●

E Electrical connections							
RN	M8 connector without cable	●	●	●	●	●	●
R1	M8 connector straight cable *3	●	●	●	●	●	●
R2	M8 connector L-type cable *3	●	●	●	●	●	●

F Option							
Blank	Manual override of non-locking/locking common (standard)	●	●	●	●	●	●
H	With exhaust check valve *4, *6	●	●	●	●	●	
F	Port A/B filter *5	●	●	●	●	●	●
Z1	Air supply spacer *6, *7	●	●	●	●	●	
Z3	Exhaust spacer *6, *7	●	●	●	●	●	

G Mount type							
Blank	Direct mount *8	●	●	●	●	●	●

H Station No.							
2	2 stations						2
to	to	●	●	●	●	●	to
20	20 stations (Refer to page 49 for the max. station number)						15

I Voltage							
4	12 VDC	●	●	●	●	●	●

⚠ Precautions for model No. selection

*1 M4GE*80EX when using a mixture of 3, 5-port valves. When used with a masking plate, M3GE*80EX.

*2 Dimensions are the same as the respective 2-position double solenoid.

*3 M8 connector length is 300mm. Select other lengths from page 64 as needed.

*4 3-position all ports closed and PAB connection are not provided with exhaust check valve specifications (H). Refer to page 79 for details on the exhaust check valve.

*5 A filter is built into port P as standard.


*6 4G4 cannot be selected for exhaust check valves (H), air supply spacers (Z1), or exhaust spacers (Z3).

*7 Specify the spacer mounting position/quantity in the manifold specifications sheet. Stacking of spacers is not possible. Combination with the masking plate is not supported. Refer to pages 59 to 62 for details.

*8 The manifold max. station No. for port size 12 M4GE4 is 12.

*9 Explosion-proof barrier sold separately. Select from page 69.

Manifold configuration explanation and parts list



Main configuration parts list

Part No.	Configuration parts name		Model No.	Item	Remarks														
1	Discrete valve for integrated base		4GE <table><tr><td><input type="checkbox"/></td><td><input type="checkbox"/></td><td>9EX -00</td></tr><tr><td colspan="2" rowspan="3"><div></div></td><td>Electrical connections</td></tr><tr><td>Option</td></tr><tr><td>Voltage</td></tr><tr><td colspan="2"></td><td>Solenoid position</td></tr><tr><td colspan="2"></td><td>Series flow rate size</td></tr></table>	<input type="checkbox"/>	<input type="checkbox"/>	9EX -00	<div></div>		Electrical connections	Option	Voltage			Solenoid position			Series flow rate size	Discrete valve Gasket Mounting screws 2 (2 PR check valves)	Details on page 51
<input type="checkbox"/>	<input type="checkbox"/>	9EX -00																	
<div></div>		Electrical connections																	
		Option																	
		Voltage																	
		Solenoid position																	
		Series flow rate size																	
2	Masking plate	3G1/4G1	4G1R-MP	Masking plate Gasket Mounting screws 2	*Two PR check valves are included with 4G3/4G4.														
3G2/4G2		4G2R-MP																	
4G3		4G3R-MP																	
4G4		4GB4-MP																	
3	Manifold base assembly		M4GE <table><tr><td><input type="checkbox"/></td><td>R</td></tr><tr><td colspan="2" rowspan="2"><div></div></td><td>Bore size</td></tr><tr><td>Option</td></tr><tr><td colspan="2"></td><td>Station No.</td></tr><tr><td colspan="2"></td><td>Series flow rate size</td></tr></table>	<input type="checkbox"/>	R	<div></div>		Bore size	Option			Station No.			Series flow rate size	Manifold base			
<input type="checkbox"/>	R																		
<div></div>		Bore size																	
		Option																	
		Station No.																	
		Series flow rate size																	

Parts list

PARTS LIST			PARTS LIST		
Part No.	Part name	Model No.	Part No.	Part name	Model No.
-	M8 connector cable	4GEX-M8CC- <div>Direction</div> - <div>Length</div> *Details on page 64	-	Cartridge push-in fitting and related parts	4G1 <div>ø4 straight</div> 4G1R-JOINT-C4
		4G1 <div>ø6 straight</div> 4G1R-JOINT-C6			
		4G1 <div>Plug cartridge</div> 4G1R-JOINT-CPG			
		4G2 <div>ø4 straight</div> 4G2R-JOINT-C4			
		4G2 <div>ø6 straight</div> 4G2R-JOINT-C6			
		4G2 <div>ø8 straight</div> 4G2R-JOINT-C8			
		4G2 <div>Plug cartridge</div> 4G2R-JOINT-CPG			
		4G3 <div>ø6 straight</div> 4G3R-JOINT-C6			
		4G3 <div>ø8 straight</div> 4G3R-JOINT-C8			
		4G3 <div>ø10 straight</div> 4G3R-JOINT-C10			
		4G3 <div>Plug cartridge</div> 4G3R-JOINT-CPG			
		4G4 <div>ø8 straight</div> 4G4-JOINT-C8			
		4G4 <div>ø10 straight</div> 4G4-JOINT-C10			
		4G4 <div>ø12 straight</div> 4G4-JOINT-C12			
-	Explosion-proof barrier	Details on pages 69 to 73			

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use



M4GE1*0EX Series

Individual wiring manifold; Base piping




Dimensions

M4GE1*0EX



- Direct mount installation
Without connector (RN)




Note: The two 3-port valve built-in type has the same dimensions as the double model.




- M5 female thread (M5)



- M8 connector/straight cable (R1)



- M8 connector/L-type cable (R2)



Station No.	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	38.5	49.0	59.5	70.0	80.5	91.0	101.5	112.0	122.5	133.0	143.5	154.0	164.5	175.0	185.5	196.0	206.5	217.0	227.5
L ₁	30.5	41.0	51.5	62.0	72.5	83.0	93.5	104.0	114.5	125.0	135.5	146.0	156.5	167.0	177.5	188.0	198.5	209.0	219.5

M4GE2*0EX Series



Individual wiring manifold; Base piping

Dimensions

M4GE2*0EX

- Without connector (RN)


Note: The two 3-port valve built-in type has the same dimensions as the double model.



- Rc1/8 female thread (06)

- M8 connector/straight cable (R1)

- M8 connector/L-type cable (R2)



Station No.	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	54.0	70.0	86.0	102.0	118.0	134.0	150.0	166.0	182.0	198.0	214.0	230.0	246.0	262.0	278.0	294.0	310.0	326.0	342.0
L ₁	42.0	58.0	74.0	90.0	106.0	122.0	138.0	154.0	170.0	186.0	202.0	218.0	234.0	250.0	266.0	282.0	298.0	314.0	330.0



M4GE3*0EX Series

Individual wiring manifold; Base piping

Dimensions

M4GE3*0EX


● Without connector (RN)



● Rc1/4 female thread (08)

● M8 connector/straight cable (R1)

● M8 connector/L-type cable (R2)




Station No.	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	64.0	83.0	102.0	121.0	140.0	159.0	178.0	197.0	216.0	235.0	254.0	273.0	292.0	311.0	330.0	349.0	368.0	387.0	406.0
L ₁	52.0	71.0	90.0	109.0	128.0	147.0	166.0	185.0	204.0	223.0	242.0	261.0	280.0	299.0	318.0	337.0	356.0	375.0	394.0


Dimensions

M4GE4*0EX


● Without connector (RN)




● Rc1/4, Rc3/8 female thread (08, 10)



● M8 connector/straight cable (R1)



● M8 connector/L-type cable (R2)



Station No.	2	3	4	5	6	7	8	9	10	11	12	13	14	15
L	77	102	127	152	177	202	227	252	277	302	327	352	377	402
L1	63	88	113	138	163	188	213	238	263	288	313	338	363	388



M4GE4*0EX Series

Individual wiring manifold; Base piping


Dimensions

M4GE4*0EX


- Rc1/2 female thread
Without connector (RN)



- M8 connector/straight cable (R1)




- M8 connector/L-type cable (R2)



Station No.	2	3	4	5	6	7	8	9	10	11	12
L	95	124	153	182	211	240	269	298	327	356	385
L ₁	75	104	133	162	191	220	249	278	307	336	365

3GD*0EX 4GD*0EX	3GE*0EX 4GE*0EX	M3GD*0EX M4GD*0EX	M3GE*0EX M4GE*0EX	Related products	Manifold specifications sheet	Precautions for use
--------------------	--------------------	----------------------	----------------------	------------------	----------------------------------	---------------------

MEMO



Specifications

Model No.	P → A/B		A/B → R		Weight g
	C(dm ³ /(s·bar))	b	C(dm ³ /(s·bar))	b	
4G1	0.70	0.23	0.93	0.16	8
4G2	1.6	0.17	1.8	0.16	35
4G3	2.6	0.22	3.1	0.14	56

*1: Values are when a valve is mounted.
*2: Effective cross-sectional area S and sonic conductance C are converted as $S \approx 5.0 \times C$.

How to order discrete units

Air supply spacer model No.

4G 3 R - P - GWS10

A Air supply spacer model No.

B Port size
*1


		Valve model No.		
		4G1	4G2	4G3
Code	Description			
A Air supply spacer model No.				
1	For 4G1	●		
2	For 4G2		●	
3	For 4G3			●
B Port size				
Blank	M5 thread (4G1), Rc thread (4G2/4G3)	①	②	③
GWS4	ø4 fitting	●		
GWS6	ø6 fitting	●	●	
GWS8	ø8 fitting		●	●
GWS10	ø10 fitting			●

is not available.
Accessories: 2 mounting screws, 2 PR check valves, 1 body gasket

⚠ Precautions for model No. selection

*1: Blank, ① M5 ② Rc1/8 ③ Rc1/4.
*2: Specify the air supply spacer mounting position and quantity on the manifold specifications sheet of each catalog.
*3: Combination with the masking plate is not supported.
*4: 4G4 air supply spacers are made to order products. Contact CKD for details.

Dimensions




Note: For A and B dimensions, check the dimensions of the respective specifications.

M4GD1to3/M4GE1to3 *0EX Series

Related products

Related products

● Exhaust spacer



Specifications

Model No.	P → A/B		A/B → R		Weight g
	C(dm ³ /(s·bar))	b	C(dm ³ /(s·bar))	b	
4G1	0.94	0.28	0.68	0.33	7
4G2	1.5	0.24	1.9	0.24	34
4G3	3.4	0.21	2.9	0.27	58

*1: Values are when a valve is mounted.

*2: Effective cross-sectional area S and sonic conductance C are converted as $S \approx 5.0 \times C$.

How to order discrete units

● Exhaust spacer

Exhaust spacer model No.

4G **3** **R - R** - **GWS10**

A Exhaust spacer model No.

B Port size
*1

		Valve model No.		
		4G1	4G2	4G3
A Exhaust spacer model No.				
1	For 4G1	●		
2	For 4G2		●	
3	For 4G3			●
B Port size				
Blank	M5 thread (4G1), Rc thread (4G2/4G3)	①	②	③
GWS4	ø4 fitting	●		
GWS6	ø6 fitting	●	●	
GWS8	ø8 fitting		●	●
GWS10	ø10 fitting			●

is not available.

Accessories: 2 mounting screws (*2), 2 PR check valves, 1 body gasket

⚠ Precautions for model No. selection

*1: Blank, ① M5 ② Rc1/8 ③ Rc1/4.

*2: Specify the exhaust spacer mounting position and quantity on the manifold specifications sheet of each catalog.

*3: Combination with the masking plate is not supported.


*4: 4G4 exhaust spacers are made to order products. Contact CKD for details.

Related products


- Exhaust spacer

Dimensions


● 4G1




Dimensions when mounted




● 4G2




Dimensions when mounted



● 4G3



Dimensions when mounted



Note: For A and B dimensions, check the dimensions of the respective specifications.



M4GD1to4/M4GE1to4*0EX Series

Related products

Related products


● Silencer

● SLM-M5



Model No.	Port size	A	B	C	D	E
SLW-6S	R 1/8	22	13.3	10.5	6	10.5
SLW-8S	R 1/4	28	19	14.8	9	15.4

● SLW-6A, 8A, 10A, 10L, 15A




*1: Select the silencer mounting after confirming the dimensions.

Code Model No.	Noise reduction effect dB (A)	Effective cross-sectional area mm ²	A	B	C	D	E	Port size
SLW-6A	30 or more	10	34.5	28	16.5	10	7	R 1/8
SLW-8A	30 or more	20	44.5	36	20	13	8.5	R 1/4
SLW-10A	30 or more	30	58.5	48.5	25.5	17	12	R 3/8
SLW-10L	30 or more	60	68.2	58.4	28	19	12	R 3/8
SLW-15A	30 or more	75	71.4	58.4	28	19	15	R 1/2

● Plug type


Part name	Model No.	Compatible bore size	Appearance
Blanking plug	GWP4-B	ø4	
	GWP6-B	ø6	
	GWP8-B	ø8	
	GWP10-B	ø10	
	GWP12-B	ø12	
Threaded plug	4G1R-M5P	M5	
	4G2R-06P	Rc1/8	
	4G3R-08P	Rc1/4	
	4G3R-10P	Rc3/8	
	4G4-15P	Rc1/2	

- Push-in fitting tube remover
For ø4/ø6 push-in fittings
4GR-EOT4-6



Related parts


(1) Mounting plate (P) kit



Mounting (P) kit

Model	Kit model No.	Set parts
4GD1	4G1R-MOUNT-PLATE-KIT	Mounting plate, 2 mounting screws, 2 nuts
4GD2	4G2R-MOUNT-PLATE-KIT	Mounting plate, 2 mounting screws
4GD3	4G3R-MOUNT-PLATE-KIT	Mounting plate, 2 mounting screws


(2) Cartridge push-in fitting related parts Discrete




Fitting stopper plate kit

Model	Kit model No.
M4G1	4G1R-JNT-STP-PLATE-KIT
M4G2	4G2R-JNT-STP-PLATE-KIT
M4G3	4G3R-JNT-STP-PLATE-KIT
M4G4	4GB4-JNT-STP-PLATE-KIT


(3) M8 connector cable



Straight cable (R1)



L-type cable (R2)



Straight cable (R3)

◆ Cable Capacitance and Inductance

Type	Capacitance [nF/m] at 1kHz	Inductance [mH/m] at 1kHz
Straight (R1)	0.058	0.003
L type (R2)	0.125	0.003
Straight (R3)	0.065	0.002

◆ Minimum bending radius of cable

Type	No load [mm]	With load [mm]
Straight (R1)	20.0	36.0
L type (R2)	23.5	42.3
Straight (R3)	20.0	-

4GEX - M8CC - R1 - 300

A Direction B Length

A Direction		4G1	4G2	4G3	4G4
R1 *1	Straight cable (color: gray)	●	●	●	●
R2 *1	L type cable (color: black)	●	●	●	●
R3 *2	Straight cable (color: blue)		●	●	●

B Length	
300	Cable length 300 mm
500	Cable length 500 mm
1000	Cable length 1000 mm
3000	Cable length 3000mm

*1: R1 and R2 types come with a blue marker for identification.

*2: Available as made to order.

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet


Precautions for use

M4GD1 to 4/M4GE1 to 4*0EX Series

Related parts

Related parts

(4) Manifold related parts



Masking plate kit

Model	Model No.	Item	Remarks
M3G1/M4G1	4G1R-MP	Masking plate Gasket Mounting screw 2	4G3/4G4 have two PR check valves included.
M3G2/M4G2	4G2R-MP		
M4G3	4G3R-MP		
M4GD4	4GA4-MP		
M4GE4	4GB4-MP		

Gasket

Model	Part model No.
3G1/4G1	4G1R-GASKET
3G1/4G1 (For masking plate)	4G1R-MP-GASKET
3G2/4G2	4G2R-GASKET
3G2/4G2 (For masking plate)	4G2R-MP-GASKET
4G3	4G3R-GASKET
4GD4	4GA4-GASKET
4GE4	4GB4-GASKET

Gasket with exhaust check valve

Model	Part model No.
3G1/4G1	4G1R-CHECK-VALVE
3G2/4G2	4G2R-CHECK-VALVE
4G3	4G3R-CHECK-VALVE

Note: 4G4 does not have a gasket with check valve.

PR check valve kit (2 per set)

Model	Kit model No.
3G1/4G1	4G1R-PR
3G2/4G2	4G2R-PR
4G3	4G3R-PR
4G4	4G4-PR

Mounting screw (10 per set)

Model	Part model No.
3G1/4G1	4G1R-SET-SCREW
3G2/4G2	4G2R-SET-SCREW
4G3	4G3R-SET-SCREW
4G4	4G4-SET-SCREW

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

Related parts

(5) Sub-plate

How to order

- 4GD piping adapter




		A Model No.				
		3G1	3G2	4G1	4G2	4G3
Code	Description					
B Port size (Port P/R1/R2)						
M5	M5	●		●		
06	Rc1/8		●		●	
08	Rc1/4					●
C Option						
P	With mounting plate (included)	●	●	●	●	●

● is not available.

Note: For 4G4, there is no piping adapter.

- 4GE discrete sub-plate



		A Model No.					
		3G1	3G2	4G1	4G2	4G3	4G4
Code	Description						
B Port size (Port A/B/P/R1/R2)							
06	Rc1/8	●		●			
08	Rc1/4		●		●	●	
10	Rc3/8					●	●
15	Rc1/2						●
C Option							
F	A/B port filter integrated *1	●	●	●	●	●	●

*1: A filter is built into port P as standard.

● is not available.

Note: For 4G4, there is no piping adapter.

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

M4GD1 to 4/M4GE1 to 4*0EX Series

Related parts

Related parts

(6) Manifold sub-plate kit individual wiring

● M4GD sub-plate

M4GD1 R - 00 - 2

A Model No.

Code	Description
A Model No.	
M4GD1	Metal base, 4G1 size, body piping
M4GD2	Metal base, 4G2 size, body piping
M4GD3	Metal base, 4G3 size, body piping
M4GD4	Metal base, 4G4 size, body piping
D Station No.	
2	2 stations
to	to
20	Refer to the specifications page for the max. station number.

● M4GE1 sub-plate

M4GE1R - C4 - - 2

A Port size

B Option

C Mount type

D Station No.

Code		Description	
A Port size			
Port	4(A), 2(B) port		Port P/R1/R2
C4	ø4 push-in fitting		Rc1/8
C6	ø6 push-in fitting		
M5	M5		
B Option			
Blank			
F	Port A/B filter built in	*1	
C Mount type			
Blank	Direct mount		
D Station No.			
2	2 stations		
to	to		
20	Refer to the specifications page for the max. station number.		

*1: A filter is built into port P as standard.

● M4GE2/3 sub-plate

M4GE2 R - C4 - - 2

A Model No.

B Port size

C Option

D Station No.

Code		Description		M4GE2	M4GE3
B Port size					
Port	4(A), 2(B) port	Port P/R1/R2 (1) = Rc1/4 (2) = Rc3/8			
C4	ø4 push-in fitting	(1)			
C6	ø6 push-in fitting	(1)	(2)		
C8	ø8 push-in fitting	(1)	(2)		
C10	ø10 push-in fitting		(2)		
06	Rc1/8	(1)			
08	Rc1/4		(3)		
C Option					
Blank					
F	Port A/B filter built in			*1	
D Station No.					
2	2 stations				
to	to				
20	Refer to the specifications page for the max. station number.				

*1: A filter is built into port P as standard.

3GD*0EX 4GD*0EX	3GE*0EX 4GE*0EX	M3GD*0EX M4GD*0EX	M3GE*0EX M4GE*0EX	Related products	Manifold specifications sheet	Precautions for use
--------------------	--------------------	----------------------	----------------------	------------------	----------------------------------	---------------------

MEMO

INSULATED EXPLOSION PROOF BARRIER Dimensions

Model No.: **D5048S**



Explosion-proof certification state

CCC, NEPSI (China)	IECEEx (International)	KCs (South Korea)	TS (Taiwan)
Compatible	Compatible	Compatible	Compatible




Terminal No. display (non-dangerous zone side)

Terminal: No. 1: +
Terminal: No. 2: -
Barrier: 24 VDC \pm 10%

(Terminal: No. 3 and 4 are for malfunction output.)

(Terminal: No. 5 and 6 are for prioritized input.)



Terminal No. display (dangerous zone side)

Terminal: No. 8: +
Terminal: No. 10: -

*Do not use terminals No.7 and 9, as the working voltage and intrinsic safety parameters will not be satisfied when combined with CKD solenoids.



Barrier intrinsic safety parameters


Item	Between terminals No. 8-10
Intrinsic safety circuit max. voltage U_0	24.8V
Intrinsic safety circuit max. current I_0	108mA
Intrinsic safety circuit max. power P_0	667mW
Intrinsic safety circuit allowable capacitance C_0	0.113 μ F
Intrinsic safety circuit allowable inductance L_0	1.42mH
Operating ambient temperature range	-40 to 70°C

- *1: Always use valves in combination with a barrier.
- *2: Connection terminals are polarized. Take care to prevent incorrect wiring.
- *3: Applicable wire is 0.25 to 2.5mm².
- *4: Recommended terminal tightening torque is 0.5 to 0.6N·m.
- *5: Barrier degree of protection is IP20.

Supply source: IDEC Co., Ltd. (G.M.I.)
Refer to the IDEC or G.M.I catalog or website for detailed specifications or a non-judgment document.

About Valve and Barrier Connections

4GD/E EX Series



* Voltage equivalent to 12 VDC is supplied to the valve via an insulating barrier.

Insulating explosion-proof barrier (1CH) Dimensions


Model No.: **EXDO-11**



Explosion-proof certification state

CCC, NEPSI (China)	IECEX (International)	KCs (South Korea)	TS (Taiwan)
Compatible	Unsupported	Unsupported	Unsupported

Terminal No. display (dangerous zone)
Terminal: No.2: +
Terminal: No.1: -



Terminal No. display (non-dangerous zone)
Terminal No.5-6 has control signals
No.5
No.6
Control signal
Terminal No. display (non-dangerous zone)
Power supply voltage 24VDC
Terminal: No.9: +
Terminal: No. 10: -



Barrier intrinsic safety parameters


Item	Item
Intrinsic safety circuit max. voltage Uo	28V
Intrinsic safety circuit max. current Io	93mA
Intrinsic safety circuit max. power Po	0.65 W
Intrinsic safety circuit allowable capacitance Co	0.05 μF
Intrinsic safety circuit allowable inductance Lo	2.4mH

- * Always use valves in combination with a barrier.
- * Connection terminals are polarized. Incorrect wiring leads to breakdown of the barrier.
- * Barrier degree of protection is IP20.

Supply sources:Bei ji an
Refer to the Bei ji an catalog
for detailed specifications.

About Valve and Barrier Connections

4GD/E EX Series



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet

Precautions for use

4G*/M4G*EX Series

Insulating explosion-proof barrier (2CH) Dimensions

Model No.: EXDO-22





Explosion-proof certification state

CCC, NEPSI (China)	IECEX (International)	KCs (South Korea)	TS (Taiwan)
Compatible	Unsupported	Unsupported	Unsupported

Terminal No. display (dangerous zone)
Terminal: No.2: +
Terminal: No.1: -

Terminal No. display (dangerous zone)
Terminal: No.4: +
Terminal: No.3: -



Barrier intrinsic safety parameters


Item	Item	
	1CH	2CH
Intrinsic safety circuit max. voltage Uo	28V	28V
Intrinsic safety circuit max. current Io	93mA	93mA
Intrinsic safety circuit max. power Po	0.65 W	0.65 W
Intrinsic safety circuit allowable capacitance Co	0.05 μF	0.05 μF
Intrinsic safety circuit allowable inductance Lo	2.4mH	2.4mH

- * Always use valves in combination with a barrier.
- * Connection terminals are polarized. Incorrect wiring leads to breakdown of the barrier.
- * Barrier degree of protection is IP20.

Supply sources:Bei ji an
Refer to the Bei ji an catalog
for detailed specifications.

About Valve and Barrier Connections

4GD/E EX Series




Zener barrier (1CH) Dimensions

Model No.: **Z728**



Explosion-proof certification state

CCC, NEPSI (China)	IECEX (International)	KCs (South Korea)	TS (Taiwan)
Compatible	Compatible	Compatible	Compatible



Supply sources: Pepperl+Fuchs Inc.
Refer to the Pepperl+Fuchs Inc. catalogs or the WEB for detailed specifications or a report of the non-judgment.


Barrier intrinsic safety parameters

Item	Item
Intrinsic safety circuit max. voltage U_0	28V
Intrinsic safety circuit max. current I_0	93mA
Intrinsic safety circuit max. power P_0	0.65 W
Intrinsic safety circuit allowable capacitance C_0	0.083 μ F
Intrinsic safety circuit allowable inductance L_0	3.05mH
Operating ambient temperature range	-20 to 60°C
Current limiting resistor	300 Ω

- * Always use valves in combination with a barrier.
- * Connection terminals are polarized. Incorrect wiring leads to breakdown of the barrier.
- * Compatible wires have a allowable area of 2.5mm².
- * Barrier degree of protection is IP20.
- * Type A grounding is required for barrier installation.

About Valve and Barrier Connections

4GD/E EX Series



3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold
specifications sheet


Precautions for use

Zener barrier (2CH) Dimensions

Model No.: **Z779**

Explosion-proof certification state

CCC, NEPSI (China)	IECEEx (International)	KCs (South Korea)	TS (Taiwan)
Compatible	Compatible	Compatible	Compatible




Supply sources: Pepperl+Fuchs Inc.
Refer to the Pepperl+Fuchs Inc. catalogs or
the WEB for detailed specifications or a
report of the non-judgment.

Barrier intrinsic safety parameters

Item	Item	
	CH1	CH2
Intrinsic safety circuit max. voltage U ₀	28V	28V
Intrinsic safety circuit max. current I ₀	93mA	93mA
Intrinsic safety circuit max. power P ₀	0.65 W	0.65 W
Intrinsic safety circuit allowable Capacitance C ₀	0.083 μF	0.083 μF
Intrinsic safety circuit allowable Inductance L ₀	3.05mH	3.05mH
Operating ambient temperature range	-20 to 60°C	-20 to 60°C
Current limiting resistor	301 Ω	301 Ω

- * Always use valves in combination with a barrier.
- * Connection terminals are polarized. Incorrect wiring leads to breakdown of the barrier.
- * Compatible wires have a allowable area of 2.5mm².
- * Barrier degree of protection is IP20.
- * Type A grounding is required for barrier installation.

About Valve and Barrier Connections



3GD*0EX 4GD*0EX	3GE*0EX 4GE*0EX	M3GD*0EX M4GD*0EX	M3GE*0EX M4GE*0EX	Related products	Manifold specifications sheet	Precautions for use
--------------------	--------------------	----------------------	----------------------	------------------	----------------------------------	---------------------

M4G¹₂₃ Individual wiring

M4G^{D_E 1 2 3}Manifold specifications sheet

Date issued / /

Company

Contact

Order No.

● Contact

● Quantity

set(s)

● Delivery date /

Slip No.

Order No.

● Manifold model No.

M **G** ^D_E **0EX-** - - -

Solenoid valves Solenoid position Port size Electrical connections Other options Station No. Voltage

Solenoid valve model No.	Fitting CX		Valve installation position																								Quantity
	A	B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	
4G 9EX																											
4G 9EX																											
4G 9EX																											
4G 9EX																											
4G 9EX																											
3G 9EX																											
3G 9EX																											
Masking plate 4G R-MP																											
Air supply spacer 4G R-P																											
Exhaust spacer 4G R-R																											
Included parts	Blanking plug																		For M G 1 0 EX								
	GWP 4-B		GWP 6-B		GWP 8-B		GWP 10-B		Push-in fitting tube remover (included as standard) Not required (check the box) <input type="checkbox"/>																		
	Threaded plug																										
	4G1R-M5P		4G2R-06P		4G3R-08P																						
	Silencer																										
SLW-6S		SLW-6A		SLW-8S		SLW-8A		SLW-10S		SLW-10A																	

M4G4 individual wiring

M4G^D_E4Manifold specifications sheet

Date issued / /

Company

Contact

Order No.

● Contact

● Quantity

set(s)

● Delivery date /

Slip No.

Order No.

● Manifold model No.

M4G^D_E4 **0EX-** - - -

Solenoid position Port size Electrical connections Option Station No. Voltage

Solenoid valve model No.			Fitting CX		Valve installation position																				Quantity			
			A	B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20		21	22	23
4G	4	9EX-																										
4G	4	9EX-																										
4G	4	9EX-																										
4G	4	9EX-																										
4G	4	9EX-																										
Masking plate 4G 4-MP																												
															</													

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products

Manifold specifications sheet

Precautions for use



Safety Precautions

Be sure to read this section before use.

When designing and manufacturing a device using CKD products, the manufacturer is obligated to check that device safety mechanism, pneumatic control circuit, or water control circuit and the system operated by electrical control that controls the devices is secured.

It is important to select, use, handle and maintain the product appropriately to ensure that the CKD product is used safely.

Observe warnings and precautions to ensure device safety.

Check that device safety is ensured, and manufacture a safe device.



WARNING

- 1** This product is designed and manufactured as a general industrial machine part.
It must be handled by an operator having sufficient knowledge and experience.
 - 2** Use this product in accordance with specifications.
This product must be used within its stated specifications. In addition, never modify or additionally machine this product. This product is intended for use in general industrial machinery equipment or parts. It is not intended for use outdoors (except for products with outdoor specifications) or for use under the following conditions or environments.
(Note that this product can be used when CKD is consulted prior to its usage and the customer consents to CKD product specifications. The customer should provide safety measures to avoid danger in the event of problems.)
 - ① Use for applications requiring safety, including nuclear energy, railways, aircraft, marine vessels, vehicles, medical devices, devices or applications in contact with beverages or foodstuffs, amusement devices, emergency cutoff circuits, press machines, brake circuits, or safety devices or applications.
 - ② Use for applications where life or assets could be significantly affected, and special safety measures are required.
 - 3** Observe organization standards and regulations, etc., related to the safety of device design and control, etc.
ISO4414, JIS B 8370 (Pneumatics fluid power - General rules and safety requirements for systems and their components) JFPS2008 (Principles for pneumatic cylinder selection and use)
Including the High Pressure Gas Safety Act, Industrial Safety and Health Act, other safety rules, organization standards and regulations, etc.
 - 4** Do not handle, pipe, or remove devices before confirming safety.
 - ① Inspect and service the machine and devices after confirming safety of all systems related to this product.
 - ② Note that there may be hot or charged sections even after operation is stopped.
 - ③ When inspecting or servicing the device, turn OFF the energy source (air supply or water supply), and turn OFF power to the facility. Discharge any compressed air from the system, and pay attention to possible water leakage and leakage of electricity.
 - ④ When starting or restarting a machine or device that incorporates pneumatic components, make sure that the system safety, such as pop-out prevention measures, is secured.
 - 5** Observe warnings and cautions in the following pages to prevent accidents.
- The precautions are ranked as "DANGER", "WARNING" and "CAUTION" in this section.

⚠ DANGER: When a dangerous situation may occur if handling is mistaken leading to fatal or serious injuries, and when there is a high degree of emergency to a warning.

⚠ WARNING: If handled incorrectly, a dangerous situation may occur, resulting in death or serious injury.

⚠ CAUTION: When a dangerous situation may occur if handling is mistaken leading to minor injuries or physical damage.

Note that some items described as "CAUTION" may lead to serious results depending on the situation. Every item provides important information and must be observed.

Warranty

- 1** **Warranty period**
The product specified herein is warranted for one (1) year from the date of delivery to the location specified by the customer.
- 2** **Warranty coverage**
If the product specified herein fails for reasons attributable to CKD within the warranty period specified above, CKD will promptly provide a replacement for the faulty product or a part thereof or repair the faulty product at one of CKD's facilities free of charge. However, following failures are excluded from this warranty:
 - 1) Failure caused by handling or use of the product under conditions and in environments not conforming to those stated in the catalog, the Specifications, or the Instruction Manual.
 - 2) Failure caused by use of the product exceeding its durability (cycles, distance, time, etc.) or caused by consumable parts.
 - 3) Failure not caused by the product.
 - 4) Failure caused by use not intended for the product.
 - 5) Failure caused by modifications/alterations or repairs not carried out by CKD.
 - 6) Failure caused by reasons unforeseen at the level of technology available at the time of delivery.
 - 7) Failure caused by acts of nature and disasters beyond control of CKD.

The warranty stated herein covers only the delivered product itself. Any loss or damage induced by failure of the delivered product is excluded from this warranty.
Note: For details on the durability and consumable parts, contact your nearest CKD sales office.
- 3** **Compatibility check**
The customer is responsible for confirming the compatibility of CKD products with the customer's systems, machines and equipment.



Pneumatic components

Safety Precautions

Be sure to read this section before use.

For general precautions for valves, "Pneumatic Valves (No. CB-023SA)" for details.

Product-specific cautions: Pilot operated explosion-proof 3.5-port valve 4G*/M4G* EX Series

Design/selection

⚠ WARNING

- Usable in Class 1 and 2 danger zones (Zones 1 and 2) where there is combustible gas or steam. Cannot be used in special danger zones (Zone 0).
- Explosion-proof performance is Ex ib IIC T4 Gb.
- Use in combination with a barrier. Valves cannot be used independently in dangerous zones.

1. Prohibition of Disassembly and Modification

⚠ WARNING

- Disassembly of pilot valves or barriers not only leads to the risk of decreased explosion-proof performances but may also cause accidents. Accordingly, customers are asked not to disassemble or modify their units.

2. Intrinsic safety explosion-proof circuit wiring

⚠ WARNING

- The intrinsic safety explosion-proof circuit wiring should not be mixed with other circuitry, nor should it be installed so as to be affected by static induction or electromagnetic induction from other circuits.

3. When using the product in combination with low friction cylinders

- Malfunctions could occur because of the exhaust pressure. Contact CKD.

4. Degree of protection IP67

- 4GD/E* The EX Series supports IP67 as standard and is protected from dust and water, but cannot be used immersed in water. Countermeasures such as a protective cover for the unit should also be taken if using in environments where it will be constantly exposed to dust or water.

- Barrier degree of protection is IP20.

Intrinsic safety-related Components (safety retainer, barrier) and intrinsic safety Components (4G EX Series) must meet the explosion-proof specifications below, as well as the safety retention ratings and parameters.

Intrinsic safety component	combination condition	Intrinsic safety related component
Explosion-proof structure and category: ia, ib, ic	≤	Explosion-proof structure and category: ia, ib, ic
Electrical Component group: IIA, IIB, IIC	≤	Electrical Component group: IIA, IIB, IIC
Ui: Intrinsic safety circuit allowable voltage (max. applicable voltage)	≥	Uo: Max. voltage (max. output voltage)
Ii: Intrinsic safety circuit allowable current (max. applicable current)	≥	Io: Max. current (max. output current)
Pi: Intrinsic safety circuit allowable power (max. input power)	≥	Po: Max. power (max. output power)
Ci+Cw Ci: Intrinsic Component's internal capacitance Cw: Intrinsic safety circuit wiring max. capacitance	≤	Co: Allowable capacitance (maximum connectable capacitance)
Li+Lw Li: Intrinsic Component's internal inductance Lw: Intrinsic safety circuit wiring max. inductance	≤	Lo: Allowable inductance (maximum connectable inductance)

The length of the intrinsic safety circuit external wiring can be calculated using the method below, in accordance with the above connection conditions.

Wiring capacitance and inductance are $Co \geq Ci + Cw$ and $Lo \geq Li + Lw$.

The allowable wiring length must be less than or equal to the value of either $(Co - Ci)/Cc$ or $(Lo - Li)/Lc$, whichever is smaller.

Cc: Capacitance per unit length, Lc: Inductance per unit length

3GD*0EX
4GD*0EX

3GE*0EX
4GE*0EX

M3GD*0EX
M4GD*0EX

M3GE*0EX
M4GE*0EX

Related products




Manifold
specifications sheet

Precautions for use

5.Exhaust check valve

CAUTION:The exhaust check valve is a check valve. If the cylinder rod is manually operated directly without pressurization, the check valve opens and the air flow is shut off, preventing cylinder rod adjustment.


Generally, the double acting cylinder connected at the manifold to direct acting cylinders or ABR connection valves may malfunction when adversely affected by the exhaust pressure led in by operation of other cylinders. For the manifold of 4G Series, the "exhaust check valve" integrated to prevent this malfunction can be selected, except for all ports closed valves and PAB connection valves. However, with components that are affected by a small amount of leakage or pressure of low friction cylinders, etc., the functions may not operate properly. Moreover, 4G4 is not compatible with check valves.



Check valve equipped specifications

Model No.	Flow path switching	Option (H) selection
3G ^D _{MD} *669EX	Two 3-port valves integrated NC/NC	Yes
4G ^D _{MD} *19EX	2 position single	Yes
4G ^D _{MD} *29EX	2-position double	Yes
4G ^D _{MD} *39EX	3-position all ports closed	No
4G ^D _{MD} *49EX	3-position ABR connection	Yes
4G ^D _{MD} *59EX	3-position PAB connection	No

Note: Because 3-position all ports closed type and PAB connection type are not adversely affected by the exhaust pressure led in from other cylinders at the neutral position, installation of a check valve is not required.



Mounting, installation and adjustment


1. Body piping (D) Discrete installation method

CAUTION


- When directly installing the manifold
 - The discrete body piping 4GD Series can be installed using the (a) through hole or (b) screw hole. When using the screw holes, be careful of the tightening torque.

Screw hole Tightening torque 0.7 to 1.2 N·m

4GD1 Series
(a) 2 through holes




4GD2 Series
(a) Through hole
(b) 4 common screw holes




4GD3 Series

- (a) Through hole
- (b) 2 places each, dedicated for screws



4 GD4 Series
(a) 2 through holes




Mounting hole shape

	4GD2	4GD3	
	(a) (b) Common use	(a) Through hole	(b) Screw hole
Sectional view of mounting hole			

- When installing the manifold with mounting plate (P)
 - Be careful of the mounting direction and orientation, as damage may result from incorrect mounting of body piping single mounting plate (P).

■ How to mount mounting plate (P)



MountingPlate(P)Kit

	Kit model No.	Set parts
4GD1	4G1R-MOUNT-PLATE-KIT	Mounting plate, 2 mounting screws, 2 nuts
4GD2	4G2R-MOUNT-PLATE-KIT	Mounting plate, 2 mounting screws
4GD3	4G3R-MOUNT-PLATE-KIT	Mounting plate, 2 mounting screws

*Mounting plate is compatible only with single type. Moreover, 4G4 is not compatible.

2 . How to install manifold (Metal base 4G_E^D Series)


CAUTION

■ When directly installing the manifold

- For installation of the M4G2/3 Series, there are two methods of tightening the manifold with bolts: after passing it through the upper side of the manifold base and after tightening it with the bolts from the back side. When using a female thread as shown in the table below, check the thread depth, select a mounting bolt with 10 screw-in threads or more, and be careful with the tightening torque. The screw could be damaged if incorrectly installed.


Installation method

M4G2/3 Series



M4G4 Series

- For installation of M4G4^D_E Series, tighten the manifold with bolts after passing them through the upper side of the manifold base.




Mounting hole shape (sectional view)

	Standard manifold	
	M4GD (Body piping)	M4GE (Base piping)
M4G2		
M4G3		

3 . Port filter


CAUTION

- The port filter prevents the entry of foreign matter, and prevents problems from occurring in the valve. As this does not improve the quality of the compressed air, read Warnings and Precautions on the Intro pages of "Pneumatic Valves (No. CB-023SA)," then mount, install, and adjust accordingly. Do not detach or press down the port filter forcibly. The filter could deform, causing problems. If contaminants and foreign matter are found on the filter surface, blow them off lightly, or remove them with tweezers, etc.




Port A/B filter (option) example of combination

M4G Series



4. M8 connector cable

M8 connector tightening torque is 0.38 to 0.42 N·m.
The degree of protection (IP67) will not be upheld if not tightened to the appropriate torque.



Wire the included M8 connector cable as below.

- Black: 12 V
- Blue: 0 V
- Brown and white: Not used.

Be careful as the solenoid has polarity.

Use/maintenance

1. Continuous energizing

CAUTION

■ If a valve is used in a continuously energized state for long periods, the valve performance may deteriorate more quickly. Furthermore, use caution under the following working conditions likewise.

- When the energized time exceeds non-energized time in intermittent energizing
- When one energizing session exceeds 30 minutes in intermittent energizing

Give sufficient consideration to heat dissipation when installing the product.

2. Manual override

WARNING


■ The 4G Series is an internal pilot solenoid valve. If air is not supplied to port P, the main valve will not be switched even if the manual override is operated.

■ A manual protection cover is provided as standard. The manual protective cover is closed when the valve is shipped to protect it, which cannot be seen when delivered. Open the protective cover and operate the manual override. Note that the protective cover will not close unless the locking manual override is released.

■ Manual override is used for both non-locking and locking. The lock is applied by pressing down and turning the manual override. For locking, be sure to press down and turn. If manual override is turned without being pressed down, it could be damaged or air could leak.


■ Opening and closing the manual protection cover
Do not excessively force the manual protection cover when opening and closing it. Excessive external force may cause breakdown. (Below 5 N)

4G1 Series



Rotary


4G2 to 4 Series



Sliding

How to operate manual override

- Push non-locking operation
Push straight in the direction of the arrow until it stops.
When released, the manual operation is released.
- Push locking operation
Push and hold the button and turn it 90° in the direction of the arrow.
The function is not canceled even when the button is released.




■ When conducting manual operations, make sure that there are no people near the operating cylinder.

3. How to replace the cartridge fitting


CAUTION

■ Check procedures before changing the push-in fitting size. If installed incorrectly, or if the tightening of the mounting screw is insufficient, air leakage could occur.

■ Body piping (D)
4G 1, 2, 3




4G4



- ① Remove the mounting screw.
- ② Pull out the stopper plate and fitting together.
- ③ Align the groove of the replacement fitting with the stopper plate and assemble them temporarily.
- ④ Assemble the stopper plate with the fitting, and tighten the mounting screw. Pull the fitting. Confirm installation.

	Size	Tightening Torque (N·m)
4G1	M1.7	0.18 to 0.22
4G2	M2.5	0.25 to 0.30
4G3	M3	0.6 to 0.7
4G4	M3	0.6 to 0.7

■ Base piping (E)



- ① Remove the mounting screw.
- ② Pull out the stopper plate and fitting together.
- ③ Align the groove of the replacement fitting with the stopper plate and assemble them temporarily.
- ④ Assemble the stopper plate with the fitting, and tighten the mounting screw. Pull on the fitting to confirm that it is properly installed.

Model No. of cartridge push-in fitting

Model	Part name	Model No.
4G1	ø4 straight	4G1R-JOINT-C4
	ø6 straight	4G1R-JOINT-C6
	Plug cartridge	4G1R-JOINT-CPG
4G2	ø4 straight	4G2R-JOINT-C4
	ø6 straight	4G2R-JOINT-C6
	ø8 straight	4G2R-JOINT-C8
	Plug cartridge	4G2R-JOINT-CPG
4G3	ø6 straight	4G3R-JOINT-C6
	ø8 straight	4G3R-JOINT-C8
	ø10 straight	4G3R-JOINT-C10
	Plug cartridge	4G3R-JOINT-CPG
4G4	ø8 straight	4G4-JOINT-C8
	ø10 straight	4G4-JOINT-C10
	ø12 straight	4G4-JOINT-C12

Exporting

1 . About Barriers

⚠ CAUTION

- Please check the following for the request and inquiry of issuance of the non-judgment document and EAR judgment document.

[D5048S]

For inquiries, please contact
GMI Japan Co., Ltd.
TEL :045-228-9502
FAX :045-228-9503
Or, request an issue from
<https://www.gmijapan.co.jp/contact/>


[Z728/Z779]

For inquiries, please contact
Pepperl+Fuchs Inc.
TEL:045-624-9077
E-mail:sales@jp.pepperl-fuchs.com

Related products

ATEX Directive compliant 4GD/E EA Series

- Explosion-proof performance Explosion-proof performance II 2G Ex ib IIC T4 Gb
- Intrinsic safety explosion-proof
- ATEX category 2



CC-1458A



Red cube icon: Distributors

CKD Corporation

Website <https://www.ckd.co.jp/en/>

ASIA

喜開理(上海)機器有限公司

CKD(SHANGHAI) CORPORATION

- 營業部/上海浦西事務所(SALES HEADQUARTERS / SHANGHAI PUXI OFFICE)
Room 601, 6th Floor, Yuanzhongkeyan Building, No. 1905
Hongmei Road, Xinhui District, Shanghai 200233, China
PHONE +86-21-61911888 FAX +86-21-60905356
- 上海浦東事務所(SHANGHAI PUDONG OFFICE)
- 寧波事務所(NINGBO OFFICE)
- 杭州事務所(HANGZHOU OFFICE)
- 無錫事務所(WUXI OFFICE)
- 昆山事務所(KUNSHAN OFFICE)
- 蘇州事務所(SUZHOU OFFICE)
- 南京事務所(NANJING OFFICE)
- 合肥事務所(HEFEI OFFICE)
- 成都事務所(CHENGDU OFFICE)
- 武漢事務所(WUHAN OFFICE)
- 鄭州事務所(ZHENGZHOU OFFICE)
- 長沙事務所(CHANGSHA OFFICE)
- 重慶事務所(CHONGQING OFFICE)
- 西安事務所(XIAN OFFICE)
- 廣州事務所(GUANGZHOU OFFICE)
- 中山事務所(ZHONGSHAN OFFICE)
- 深圳西事務所(WEST SHENZHEN OFFICE)
- 深圳東事務所(EAST SHENZHEN OFFICE)
- 東莞事務所(DONGGUAN OFFICE)
- 廈門事務所(XIAMEN OFFICE)
- 福州事務所(FUZHOU OFFICE)
- 瀋陽事務所(SHENYANG OFFICE)
- 大連事務所(DALIAN OFFICE)
- 長春事務所(CHANGCHUN OFFICE)
- 北京事務所(BEIJING OFFICE)
- 天津事務所(TIANJIN OFFICE)
- 青島事務所(QINGDAO OFFICE)
- 濰坊事務所(WEIFANG OFFICE)
- 濟南事務所(JINAN OFFICE)
- 烟台事務所(YANTAI OFFICE)

CKD INDIA PRIVATE LTD.

- HEADQUARTERS
Unit No. 607, 6th Floor, Welldone Tech Park, Sector 48,
Sohna Road, Gurgaon-122018, Haryana, India
PHONE +91-124-418-8212
- BANGALORE OFFICE
- PUNE OFFICE

- 2-250 Uji, Komaki City, Aichi 485-8551, Japan
- PHONE +81-568-74-1338 FAX +81-568-77-3461

PT CKD TRADING INDONESIA

- HEAD OFFICE
Menara Bidakara 2, 18th Floor, Jl. Jend. Gatot Subroto Kav.
71-73, Pancoran, Jakarta 12870, Indonesia
PHONE +62-21-2938-6601 FAX +62-21-2906-9470
- MEDAN OFFICE
- BEKASI OFFICE
- KARAWANG OFFICE
- SEMARANG OFFICE
- SURABAYA OFFICE

CKD KOREA CORPORATION

- HEADQUARTERS
(3rd Floor), 44, Sinsu-ro, Mapo-gu, Seoul 04088, Korea
PHONE +82-2-783-5201~5203 FAX +82-2-783-5204
- 水原營業所(SUWON OFFICE)
- 天安營業所(CHEONAN OFFICE)
- 蔚山營業所(ULSAN OFFICE)

M-CKD PRECISION SDN.BHD.

- HEAD OFFICE
Lot No.6, Jalan Modal 23/2, Seksyen 23, Kawasan MIEL,
Fasa 8, 40300 Shah Alam, Selangor Darul Ehsan, Malaysia
PHONE +60-3-5541-1468 FAX +60-3-5541-1533
- JOHOR BAHRU BRANCH OFFICE
- PENANG BRANCH OFFICE

CKD SINGAPORE PTE. LTD.

- No.33 Tannery Lane #04-01 Hoesteel Industrial
Building, Singapore 347789, Singapore
PHONE +65-67442623 FAX +65-67442486

CKD CORPORATION BRANCH OFFICE

- No.33 Tannery Lane #04-01 Hoesteel Industrial
Building, Singapore 347789, Singapore
PHONE +65-67447260 FAX +65-68421022

CKD THAI CORPORATION LTD.

- HEADQUARTERS
19th Floor, Smooth Life Tower, 44 North Sathorn Road,
Silom, Bangkok, Bangkok 10500, Thailand
PHONE +66-2-267-6300 FAX +66-2-267-6304-5
- NAVANAKORN OFFICE
- EASTERN SEABOARD OFFICE
- LAMPHUN OFFICE
- KORAT OFFICE
- AMATANAKORN OFFICE
- PRACHINBURI OFFICE
- SARABURI OFFICE

台灣喜開理股份有限公司

TAIWAN CKD CORPORATION

- HEADQUARTERS
16F-3, No. 7, Sec. 3, New Taipei Blvd., Xinzhuang Dist.,
New Taipei City 242, Taiwan
PHONE +886-2-8522-8198 FAX +886-2-8522-8128
- 新竹營業所(HSINCHU OFFICE)
- 台中營業所(TAICHUNG OFFICE)
- 台南營業所(TAINAN OFFICE)
- 高雄營業所(KAOHSIUNG OFFICE)

CKD VIETNAM ENGINEERING CO.,LTD.

- HEADQUARTERS
18th Floor, CMC Tower, Duy Tan Street, Cau Giay
District, Hanoi, Vietnam
PHONE +84-24-3795-7631 FAX +84-24-3795-7637
- HO CHI MINH OFFICE

EUROPE

CKD EUROPE B.V.

- HEADQUARTERS
Beechavenue 125A, 1119 RB Schiphol-Rijk, the Netherlands
PHONE +31-23-554-1490
- CKD EUROPE GERMANY OFFICE
- CKD EUROPE UK
- CKD EUROPE CZECH O.Z.
- CKD CORPORATION EUROPE BRANCH
Beechavenue 125A, 1119 RB Schiphol-Rijk, the Netherlands
PHONE +31-23-554-1490

NORTH AMERICA & LATIN AMERICA

CKD MEXICO, S. DE R.L. DE C.V.

- Cerrada la Noria No. 200 Int. A-01, Querétaro Park II,
Parque Industrial Querétaro, Santa Rosa Jáuregui,
Querétaro, C.P. 76220, México
PHONE +52-442-161-0624

CKD USA CORPORATION

- HEADQUARTERS
1605 Penny Lane, Schaumburg, IL 60173, USA
PHONE +1-847-648-4400 FAX +1-847-565-4923
- LEXINGTON OFFICE
- SAN ANTONIO OFFICE
- SAN JOSE OFFICE/ TECHNICAL CENTER
- DETROIT OFFICE
- BOSTON OFFICE

Revision details

- TS (Taiwan explosion-proof) compatible/Cable added/Barrier added

The goods and/or their replicas, the technology and/or software found in this catalog are subject to complementary export regulations by Foreign Exchange and Foreign Trade Law of Japan.

If the goods and/or their replicas, the technology and/or software found in this catalog are to be exported from Japan, Japanese laws require the exporter makes sure that they will never be used for the development and/or manufacture of weapons for mass destruction.