

# STK

## Stopper Cylinder

ø20, ø32, ø40, ø50



### CONTENTS

Product Introduction	920
Series variation	922
● Double Acting/round Rod End (STK)	924
● Single Acting, pull, round Rod End (STK-Y)	932
● Double Acting, spring integrated, round Rod End (STK-Y1)	940
● Double Acting, Rod End chamfered type (STK-M)	948
● Single Acting, pull type, Rod End shape chamfered type (STK-MY)	956
● Double Acting, with spring type, Rod End shape chamfered type (STK-MY1)	964
● Single Acting, pull type, Rod End shape roller type (STK-JY)	972
● Double Acting, Spring loaded type, Rod End shape roller type (STK-JY1)	978
External Dimensions Diagram with Switch	984
List of mounting bolts	985
Model Selection Guide	986
⚠ Precautions for Use	988

# Stopper Cylinder **STK Series**

## Resists lateral load firmly even in a small space

Square type, space-saving stopper cylinder (ø20, ø32, ø40, ø50) with strong bearings that can withstand large lateral loads such as those encountered when used as a stopper




### Structure of STK Series

#### Long and strong bush

Strengthened bearing part by significantly lengthening the bush

#### Thick Piston Rod

Adopts a rod that is one rank or more thicker than the normal rod diameter




#### Compact body

Direct mounting possible with Hexagon Socket head cap bolts  
Two mounting methods: screwing and through bolts

### Application Example

#### Workpiece stopper applications



#### Position holding during power outage/




A wide variety of variations available to choose from depending on usage and space

### STK Series Product System


Model Variation	Actuation			Rod end shape			Option
	Double Acting Type	Single Acting Retracting Type	Double Acting Spring integrated	Round bar type	Chamfered type	Roller type	Rod end female thread N11
STK	●			●			●
STK-Y		●		●			●
STK-Y1			●	●			●
STK-M	●				●		●
STK-MY		●			●		●
STK-MY1			●		●		●
STK-JY		●				●	●
STK-JY1			●			●	●

### 4 types of Rod End shapes according to usage scene






### Mounting Method

Through hole+taps on both ends equipped as standard



●: Standard, ◎: Option, ■: Not available

Special	Variation	Model No.  Circuit Diagram Code	Bore Size  (mm)	Standard Stroke (mm)					Min Stroke (mm)	Max Stroke (mm)	Option	Switch	Page	Special
				10	15	20	25	30			With Rod End female thread			
											N11			
MVC	Double Acting type, Rod End shape round bar type	STK 	Equivalent to ø20 / Equivalent to ø32	●	●		●	■	■	10	20	◎	924	
			Equivalent to ø40 / Equivalent to ø50	■	■		●	●	●	20	30	◎		
STK	Single Acting, Retraction type Rod End shape round bar type	STK-Y 	Equivalent to ø20 / Equivalent to ø32	●	●		●	■	■	10	20	◎	932	
			Equivalent to ø40 / Equivalent to ø50	■	■		●	●	●	20	30	◎		
MCP	Double Acting, Spring loaded type Rod End shape round bar type	STK-Y1 	Equivalent to ø20 / Equivalent to ø32	●	●		●	■	■	10	20	◎	940	
			Equivalent to ø40 / Equivalent to ø50	■	■		●	●	●	20	30	◎		
GLC	Double Acting type, Rod End shape chamfered type	STK-M 	Equivalent to ø20 / Equivalent to ø32	●	●		●	■	■	10	20	◎	948	
			Equivalent to ø40 / Equivalent to ø50	■	■		●	●	●	20	30	◎		
NHS	Single Acting, Retraction type Rod End shape chamfered type	STK-MY 	Equivalent to ø20 / Equivalent to ø32	●	●		●	■	■	10	20	◎	956	
			Equivalent to ø40 / Equivalent to ø50	■	■		●	●	●	20	30	◎		
HR	Double Acting, Spring loaded type Rod End shape chamfered type	STK-MY1 	Equivalent to ø20 / Equivalent to ø32	●	●		●	■	■	10	20	◎	964	
			Equivalent to ø40 / Equivalent to ø50	■	■		●	●	●	20	30	◎		
LN	Single Acting, Retraction type Rod End shape roller type	STK-JY 	Equivalent to ø20 / Equivalent to ø32	●	●		●	■	■	10	20	■	972	
			Equivalent to ø40 / Equivalent to ø50	■	■		●	●	●	20	30	■		
	Double Acting, Spring loaded type Rod End shape roller type	STK-JY1 	Equivalent to ø20 / Equivalent to ø32	●	●		●	■	■	10	20	■	978	
			Equivalent to ø40 / Equivalent to ø50	■	■		●	●	●	20	30	■		



Stopper Cylinder, Double Acting Type,  
Rod End Shape Round Bar Type


# STK Series

● Bore Size:  $\phi 20$ ,  $\phi 32$ ,  $\phi 40$ ,  $\phi 50$




## Model No. Notation

Without Switch  
(Built-in magnet for switch)



With switch  
(Built-in magnet for switch)



### 1 Bore Size (mm)

Code	Content
20	$\phi 20$
32	$\phi 32$
40	$\phi 40$
50	$\phi 50$

### 2 Piping thread type

Code	Content
Blank	M5 ( $\phi 20$ )
NN	Rc thread ( $\phi 32$ to $\phi 50$ )
NN	NPT thread ( $\phi 32$ or more) (Custom product)
GN	G thread ( $\phi 32$ or more) (Custom product)

### 3 Stroke (mm)

Bore Size	Stroke
$\phi 20$	10 to 20
$\phi 32$	10 to 20
$\phi 40$	20 to 30
$\phi 50$	20 to 30

Note: For Standard Stroke and minimum stroke with switch, please refer to P. 926.

### 4 Switch Model No.

For switch details, refer to P. 1457.  
Switches are shipped with the product.

Contact	Indicator LED Special Function	Wiring (Output)	Load Voltage (V)			Load Current (mA)			Lead wire *1		Image
			AC	DC	AC	DC	Straight	L-shape			
Solid State	1-Color	2-wire	85 to 265	—	5 to 100	—	T1H□	T1V□			
			—	10 to 30	—	5 to 20 *2	T2H□	T2V□			
		3-wire (NPN)	—	—	100 or less	T3H□	T3V□				
			—	30 or less	—	50 or less	T3PH□	T3PV□			
		2-Color	2-wire	—	24 ± 10%	—	5 to 20	T2WH□		T2WV□	
			3-wire (NPN)	—	30 or less	—	50 or less	T3WH□		T3WV□	
	Reed	1-Color	2-wire	—	24 ± 10%	—	5 to 20	T2WLH□	T2WLV□		
				—	10 to 30	—	5 to 20 *2	T2JH□	T2JV□		
		Without Indicator Lamp	2-wire	—	10 to 30	—	5 to 20 *2	T2HR3	T2VR3		
				110	12/24	7 to 20	5 to 50	T0H□	T0V□		
1-Color	2-wire	110	5/12/24	20 or less	50 or less	T5H□	T5V□				
		110/220	12/24	7 to 20 / 7 to 10	5 to 50	T8H□	T8V□				

\*1: For "□" in the switch Model No., enter the code selected from the "Lead wire length, connector specification" table.

\*2: The maximum load current value above, 20 mA, is at 25°C. If the switch operating Ambient Temperature is higher than 25°C, it will be lower than 20 mA. (At 60°C, it will be 5 to 10 mA.)

\*3: This does not guarantee the water resistance of the cylinder.

\*4: Switches other than the Model No.s listed above are also available. (Custom Product) For details, refer to P. 1457.

### 5 Number of Switches

Code	Content
R	With 1 pc on rod side
H	With 1 pc on head side
D	With 2 pcs

### 6 Option

Code	Content	Image
Blank	Rod End without thread	
N11	With Rod End female thread	


Rechargeable Battery Compatible Specification (Catalog No. CC-1226AA)

● Design compatible with rechargeable battery manufacturing process

STK - ... - P4\*

\* Please contact us for details.

## Switch Single Unit Model No. Notation



4 Switch Model

\* Lead wire length, connector specification

Code	Content
Blank	1 m (Standard)
3	3 m (Option)
5	5 m (Option)
W	M8 Connector, 1PIN (+), 4PIN (-) Lead Wire 0.3 m

\*5: Only T2WLH and T2WLV can be selected.

Example) Lead wire length

1 m T0H  
3 m T0H<sup>[3]</sup>  
5 m T0H<sup>[5]</sup>

Special

Special

MVC

MVC

STK

STK

MCP

MCP

GLC

GLC

BBS

BBS

NHS

NHS

HR

HR

LN

LN

Cylinder Switch

Cylinder Switch

Ending

Ending

## Specifications

Item	STK				
	mm	ø20	ø32	ø40	ø50
Bore Size	mm	ø20	ø32	ø40	ø50
Actuation method		Double Acting Type			
Operating Fluid		Compressed Air			
Max Operating Pressure	MPa	1.0			
Min Operating Pressure	MPa	0.15	0.1		
Proof Pressure	MPa	1.6			
Ambient Temperature	°C	-10 to 60 (however, no freezing)			
Port Size		M5	Rc1/8	Rc1/4	
Stroke tolerance	mm	+2.0 0			
Operating Piston Speed	mm/s	50 to 500			
Cushion		With Rubber Cushion			
Lubrication		Not required (Use Turbine Oil Class 1 ISO VG32 if lubricated)			
Rod End shape		Round bar type			
Allowable Absorbed Energy	J	Refer to P. 986.			

MEMO

## Stroke

STK	Bore Size (mm)	Stroke (mm)	Maximum Stroke (mm)	Min Stroke (mm)	Minimum stroke with switch (mm)	
					T2WL	Other switches
MCP	ø20	10, 15, 20	20	10	20	10
	ø32					
GLC	ø40	20, 25, 30	30	20	20	20
	ø50					

Note: Strokes other than Standard Strokes are custom products.

## Cylinder Weight Table

(Unit: g)

Stroke	10	15	20	25	30	Switch Weight (Grommet)
ø20	214	229	243	—	—	Refer to the mass listed in the Switch Specifications on P. 1457.
ø32	438	463	488	—	—	
ø40	-	—	793	834	875	
ø50	-	—	1285	1311	1337	


## Theoretical Thrust Table

(Unit: N)

Bore Size (mm)	Operating Direction	Operating Pressure MPa										
		0.1	0.15	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
ø20	Push	-	-	62.8	94.2	1.26×10 <sup>2</sup>	1.57×10 <sup>2</sup>	1.88×10 <sup>2</sup>	2.20×10 <sup>2</sup>	2.51×10 <sup>2</sup>	2.83×10 <sup>2</sup>	3.14×10 <sup>2</sup>
	Pull	-	-	40.2	60.3	80.4	1.01×10 <sup>2</sup>	1.21×10 <sup>2</sup>	1.41×10 <sup>2</sup>	1.61×10 <sup>2</sup>	1.81×10 <sup>2</sup>	2.01×10 <sup>2</sup>
ø32	Push	80.4	1.21×10 <sup>2</sup>	1.61×10 <sup>2</sup>	2.41×10 <sup>2</sup>	3.22×10 <sup>2</sup>	4.02×10 <sup>2</sup>	4.83×10 <sup>2</sup>	5.63×10 <sup>2</sup>	6.43×10 <sup>2</sup>	7.24×10 <sup>2</sup>	8.04×10 <sup>2</sup>
	Pull	49.0	73.5	98.0	1.47×10 <sup>2</sup>	1.96×10 <sup>2</sup>	2.45×10 <sup>2</sup>	2.94×10 <sup>2</sup>	3.43×10 <sup>2</sup>	3.92×10 <sup>2</sup>	4.41×10 <sup>2</sup>	4.90×10 <sup>2</sup>
ø40	Push	1.26×10 <sup>2</sup>	1.88×10 <sup>2</sup>	2.51×10 <sup>2</sup>	3.77×10 <sup>2</sup>	5.03×10 <sup>2</sup>	6.28×10 <sup>2</sup>	7.54×10 <sup>2</sup>	8.80×10 <sup>2</sup>	1.01×10 <sup>3</sup>	1.13×10 <sup>3</sup>	1.26×10 <sup>3</sup>
	Pull	76.6	1.15×10 <sup>2</sup>	1.53×10 <sup>2</sup>	2.30×10 <sup>2</sup>	3.06×10 <sup>2</sup>	3.83×10 <sup>2</sup>	4.59×10 <sup>2</sup>	5.36×10 <sup>2</sup>	6.13×10 <sup>2</sup>	6.89×10 <sup>2</sup>	7.66×10 <sup>2</sup>
ø50	Push	1.96×10 <sup>2</sup>	2.95×10 <sup>2</sup>	3.93×10 <sup>2</sup>	5.89×10 <sup>2</sup>	7.85×10 <sup>2</sup>	9.82×10 <sup>2</sup>	1.18×10 <sup>3</sup>	1.37×10 <sup>3</sup>	1.57×10 <sup>3</sup>	1.77×10 <sup>3</sup>	1.96×10 <sup>3</sup>
	Pull	1.26×10 <sup>2</sup>	1.88×10 <sup>2</sup>	2.51×10 <sup>2</sup>	3.77×10 <sup>2</sup>	5.03×10 <sup>2</sup>	6.28×10 <sup>2</sup>	7.54×10 <sup>2</sup>	8.80×10 <sup>2</sup>	1.01×10 <sup>3</sup>	1.13×10 <sup>3</sup>	1.26×10 <sup>3</sup>


Dimensional Drawings

● STK-20



Note: For dimensions with each switch, please refer to P. 984.

● STK-20-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-20).)




Note: For dimensions with each switch, please refer to P. 984.


Double Acting type, Rod End shape round bar type

Dimensional Drawings

● STK-32/40/50



● STK-32/40/50-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-32, 40, 50).)




Code	A	B	C	D	EE	F	G	H	I	J	K	KA	KK	L	M	MM	MN	N	O	P	U	V	X	Y
ø32	68	48	20	8	Rc1/8	45	49.5	24	5.5	9 Counterbore Depth 5.5	60	M6 Depth 11	M8 Depth 13	10	32	20	17	34	4.5	36	13	20	30	78
ø40	80.5	52.5	24.5	8.5	Rc1/8	52	57	24	5.5	9 Counterbore Depth 5.5	69	M6 Depth 11	M8 Depth 13	10	41	25	22	40	5	44	15	28	38	90.5
ø50	82	54	24.5	10.5	Rc1/4	64	71	33	6.9	11 Counterbore Depth 6.5	86	M8 Depth 13	M10 Depth 15	15	50	30	27	50	7	56	15	28	43	97

Note: For dimensions with each switch, please refer to P. 984.


## Internal Structure / Materials

● STK-20

MEMO



MVC ● STK-32, 40, 50



Part No.	Part Name	Material	Remarks	Part No.	Part Name	Material	Remarks
1	Piston Rod	ø20: Stainless Steel ø32 to ø50: Steel	ø20: Industrial Chrome Plating ø32 to ø50: Industrial Chrome Plating	10	Magnet	Plastic	
2	Bushing	Bearing Alloy		11	Piston Packing	Nitrile Rubber	
3	Rod Cover	Aluminum Alloy	Alumite	12	Piston	Aluminum Alloy	Chromate
4	Rod Packing	Nitrile Rubber		13	Wear Ring	Polyacetal	
5	Hexagon Socket Set Screw	Steel	Black Oxide	14	Cushion rubber (H)	Urethane Rubber	
6	Metal gasket	Nitrile Rubber		15	Cylinder Body	Aluminum Alloy	Hard Anodized
7	Cushion rubber (R)	Urethane Rubber		16	Cover	ø20: Stainless Steel ø32 to 50: Aluminum Alloy	ø32 to ø50: Anodized
8	Spacer washer	Stainless Steel		With Switch			
9	Spacer	Polyamide		17	Switch		


For maintenance parts, please visit the CKD Equipment Product Site  
[\(https://www.ckd.co.jp/kiki/en/\)](https://www.ckd.co.jp/kiki/en/) → "model No." → Maintenance Parts.



Stopper cylinder Single Acting, pull type  
Rod End shape round bar type

# STK-Y Series

● Bore Size:  $\phi 20$ ,  $\phi 32$ ,  $\phi 40$ ,  $\phi 50$




Single Acting, Retracting Type




## Model No. Notation

Without Switch  
(Built-in magnet for switch)



With Switch  
(Built-in magnet for switch)




## 5 Number of Switches

Code	Content
R	With 1 pc on rod side
H	With 1 pc on head side
D	With 2 pcs

## 6 Option

Code	Content	
Blank	Rod End without thread	
N11	With Rod End female thread	

## Switch Single Unit Model No. Notation



### 1 Bore Size (mm)

Code	Content
20	$\phi 20$
32	$\phi 32$
40	$\phi 40$
50	$\phi 50$

### 2 Piping thread type

Code	Content
Blank	M5 ( $\phi 20$ )
NN	Rc thread ( $\phi 32$ to $\phi 50$ )
GN	NPT thread ( $\phi 32$ or more) (Custom product)
GN	G thread ( $\phi 32$ or more) (Custom product)

### 3 Stroke (mm)

Bore Size	Stroke
$\phi 20$	10 to 20
$\phi 32$	10 to 20
$\phi 40$	20 to 30
$\phi 50$	20 to 30

Note: For Standard Stroke and minimum stroke with switch, please refer to P. 934.

### 4 Switch Model No.

For switch details, refer to P. 1457. Switches are shipped with the product.

Contact	Indicator LED Special Function	Wiring (Output)	Load Voltage (V)		Load Current (mA)		Lead wire *1			
			AC	DC	AC	DC	Straight	L-shape		
Solid State	1-Color	2-wire	85 to 265	—	5 to 100	—	T1H□	T1V□		
			—	10 to 30	—	5 to 20 *2	T2H□	T2V□		
		3-wire (NPN)	—	—	—	100 or less	T3H□	T3V□		
	2-Color	3-wire (PNP)	—	—	—	—	T3PH□	T3PV□		
			—	30 or less	—	—	T2WH□	T2WV□		
	2-Color Improved Water Resistance	2-wire	—	24 ± 10%	—	5 to 20	T2WH□	T2WV□		
			—	30 or less	—	50 or less	T3WH□	T3WV□		
		1-Color Off-Delay Type	2-wire	—	10 to 30	—	5 to 20 *2	T2JH□		T2JV□
				—	10 to 30	—	5 to 20 *2	T2HR3		T2VR3
	1-Color Flexible Lead Wire Type	2-wire	—	10 to 30	—	5 to 20 *2	T2HR3	T2VR3		
1-Color Without Indicator Lamp			110	12/24	7 to 20	5 to 50	T0H□	T0V□		
1-Color			110	5/12/24	20 or less	50 or less	T5H□	T5V□		
Reed	1-Color	2-wire	110/220	12/24	7 to 20 / 7 to 10	5 to 50	T8H□	T8V□		
			—	—	—	—	—	—		

\* Lead wire length, connector specification

Code	Content
Blank	1 m (Standard)
3	3 m (Option)
5	5 m (Option)
W	M8 Connector, 1PIN (+), 4PIN (-) Lead Wire 0.3 m

\*5: Only T2WLH and T2WLV can be selected.

Example) Lead wire length

- 1 m T0H
- 3 m T0H<sup>[3]</sup>
- 5 m T0H<sup>[5]</sup>

\*1: For "□" in the switch Model No., enter the code selected from the "Lead wire length, connector specification" table.

\*2: The maximum load current value above, 20 mA, is at 25°C. If the switch operating Ambient Temperature is higher than 25°C, it will be lower than 20 mA. (At 60°C, it will be 5 to 10 mA.)

\*3: This does not guarantee the water resistance of the cylinder.

\*4: Switches other than the Model No.s listed above are also available. (Custom Product) For details, refer to P. 1457.

Specifications

Item	STK-Y				
	mm	ø20	ø32	ø40	ø50
Bore Size	mm	ø20	ø32	ø40	ø50
Operation type	Single Acting, Retracting Type				
Operating Fluid	Compressed Air				
Max Operating Pressure	MPa	1.0			
Min Operating Pressure	MPa	0.22	0.12		
Proof Pressure	MPa	1.6			
Ambient Temperature	°C	-10 to 60 (however, no freezing)			
Port Size		M5	Rc1/8	Rc1/4	
Stroke tolerance	mm	+2.0			0
Operating Piston Speed	mm/s	50 to 500			
Cushion	With Rubber Cushion				
Lubrication	Not required (Use Turbine Oil Class 1 ISO VG32 if lubricated)				
Rod End shape	Round bar type				
Allowable Absorbed Energy	J	Refer to P. 986.			

Cylinder Weight Table

(Unit: g)

Stroke	10	15	20	25	30	Switch Weight (Grommet)
ø20	217	232	246	—	—	Refer to the mass listed in the Switch Specifications on P. 1457.
ø32	454	479	504	—	—	
ø40	-	—	809	850	891	
ø50	-	—	1299	1325	1351	

Theoretical Thrust Table

(Unit: N)

Bore Size (mm)	Operating Pressure MPa								
	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
ø20	-	45.6	65.7	85.8	1.06×10 <sup>2</sup>	1.26×10 <sup>2</sup>	1.46×10 <sup>2</sup>	1.66×10 <sup>2</sup>	1.86×10 <sup>2</sup>
ø32	66.6	1.16×10 <sup>2</sup>	1.65×10 <sup>2</sup>	2.14×10 <sup>2</sup>	2.63×10 <sup>2</sup>	3.12×10 <sup>2</sup>	3.61×10 <sup>2</sup>	4.10×10 <sup>2</sup>	4.59×10 <sup>2</sup>
ø40	1.09×10 <sup>2</sup>	1.85×10 <sup>2</sup>	2.62×10 <sup>2</sup>	3.38×10 <sup>2</sup>	4.15×10 <sup>2</sup>	4.92×10 <sup>2</sup>	5.68×10 <sup>2</sup>	6.45×10 <sup>2</sup>	7.21×10 <sup>2</sup>
ø50	1.67×10 <sup>2</sup>	2.92×10 <sup>2</sup>	4.18×10 <sup>2</sup>	5.44×10 <sup>2</sup>	6.69×10 <sup>2</sup>	7.95×10 <sup>2</sup>	9.21×10 <sup>2</sup>	1.05×10 <sup>3</sup>	1.17×10 <sup>3</sup>

Stroke

Bore Size (mm)	Stroke (mm)	Max Stroke (mm)	Min Stroke (mm)	Min stroke with switch (mm)	
				T2WL	Other switches
ø20	10, 15, 20	20	10	20	10
ø32					
ø40	20, 25, 30	30	20	20	20
ø50					

Note: Strokes other than Standard Strokes are custom products.


Spring Load

(Unit: N)

Bore Size (mm)	Stroke (mm)	At 0 Stroke	At Full Stroke Operation
ø20	10	11.5	14.7
	15	9.9	
	20	8.2	
ø32	10	24.5	31.4
	15	21.1	
	20	17.6	
ø40	20	29.0	44.4
	25	25.3	
	30	21.5	
ø50	20	55.4	84.8
	25	48.0	
	30	40.7	


Dimensional Drawings

● STK-Y-20



Note: For dimensions with each switch, please refer to P. 984.

● STK-Y-20-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-Y-20).)




Note: For dimensions with each switch, please refer to P. 984.


Single Acting, Retraction type, Rod End shape round bar type

Dimensional Drawings

● STK-Y-32/40/50



● STK-Y-32/40/50-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-Y-32/40/50).)




Code	A	B	C	D	EE	F	G	H	I	J	K	KA	KK	L	M	MM	MN	N	O	P	U	V	X	Y
ø32	68	48	20	8	Rc1/8	45	49.5	24	5.5	9 Counterbore Depth 5.5	60	M6 Depth 11	M8 Depth 13	10	32	20	17	34	4.5	36	13	20	30	78
ø40	80.5	52.5	24.5	8.5	Rc1/8	52	57	24	5.5	9 Counterbore Depth 5.5	69	M6 Depth 11	M8 Depth 13	10	41	25	22	40	5	44	15	28	38	90.5
ø50	82	54	24.5	10.5	Rc1/4	64	71	33	6.9	11 Counterbore Depth 6.5	86	M8 Depth 13	M10 Depth 15	15	50	30	27	50	7	56	15	28	43	97


Note: For dimensions with each switch, please refer to P. 984.

## Internal Structure / Materials

● STK-Y-20



● STK-Y-32/40/50



Part No.	Part Name	Material	Remarks	Part No.	Part Name	Material	Remarks
1	Piston Rod	ø20: Stainless Steel ø32 to ø50: Steel	ø20: Industrial Chrome Plating ø32 to ø50: Industrial Chrome Plating	10	Piston Packing	Nitrile Rubber	
2	Bushing	Bearing Alloy		11	Piston	Aluminum Alloy	Chromate
3	Rod Cover	Aluminum Alloy	Alumite	12	Wear Ring	Polyacetal	
4	Rod Packing	Nitrile Rubber		13	Cushion rubber (H)	Urethane Rubber	
5	Hexagon Socket Set Screw	Steel	Black Oxide	14	Stainless Steel Wire Mesh	Stainless Steel	
6	Metal gasket	Nitrile Rubber		15	Plug	Stainless Steel	
7	Cushion rubber (R)	Urethane Rubber		16	Cylinder Body	Aluminum Alloy	Hard Anodized
8	Spacer	Aluminum Alloy	Chromate	17	Cover	ø20: Steel ø32 to ø50: Aluminum Alloy	ø20: Zinc plating ø32 to ø50: Anodized
9	Magnet	Plastic		18	Coil Spring	Piano Wire	Electrodeposition Coating

MEMO

For maintenance parts, please visit the CKD Equipment Product Site (<https://www.ckd.co.jp/kiki/en/>) → "model No." → Maintenance Parts.



Stopper Cylinder, Double Acting, Spring Loaded Type,  
Rod End Shape Round Bar Type

# STK-Y1 Series

● Bore Size: ø20, ø32, ø40, ø50


Circuit Diagram  
Code

Double Acting, spring loaded type




## Model No. Notation

Without Switch  
(Built-in magnet for switch)



With Switch  
(Built-in magnet for switch)




## 5 Number of Switches

Code	Content
R	With 1 pc on rod side
H	With 1 pc on head side
D	With 2 pcs

## 6 Option

Code	Content	
Blank	Rod End without thread	
N11	With Rod End female thread	

## Switch Single Unit Model No. Notation



### 1 Bore Size (mm)

Code	Content
20	ø20
32	ø32
40	ø40
50	ø50

### 2 Piping thread type

Code	Content
Blank	M5 (ø20) Rc thread (ø32 to ø50)
NN	NPT thread (ø32 or more) (Custom product)
GN	G thread (ø32 or more) (Custom product)

### 3 Stroke (mm)

Bore Size	Stroke
ø20	10 to 20
ø32	10 to 20
ø40	20 to 30
ø50	20 to 30

Note: For Standard Stroke and minimum stroke with switch, please refer to P. 942.

### 4 Switch Model No.

For switch details, refer to P. 1457. Switches are shipped with the product.

Contact	Indicator LED Special Function	Wiring (Output)	Load Voltage (V)		Load Current (mA)		Lead wire *1		
			AC	DC	AC	DC	Straight	L-shape	
Solid State	1-Color	2-wire	85 to 265	—	5 to 100	—	T1H□	T1V□	
			—	10 to 30	—	5 to 20 *2	T2H□	T2V□	
		3-wire (NPN)	—	—	100 or less	T3H□	T3V□		
	3-wire (PNP)	—	30 or less	—	less	T3PH□	T3PV□		
	2-Color	2-wire	—	24 ± 10%	—	5 to 20	T2WH□	T2WV□	
		3-wire (NPN)	—	30 or less	—	50 or less	T3WH□	T3WV□	
Water Resistance Improved	2-wire	2-wire	—	24 ± 10%	—	5 to 20	T2WLH□	T2WLV□	
			—	10 to 30	—	5 to 20 *2	T2JH□	T2JV□	
			—	10 to 30	—	5 to 20 *2	T2HR3	T2VR3	
Without Indicator Lamp	1-Color	2-wire	110	12/24	7 to 20	5 to 50	T0H□	T0V□	
			110	5/12/24	20 or less	50 or less	T5H□	T5V□	
			110/220	12/24	7 to 20 / 7 to 10	5 to 50	T8H□	T8V□	

\* Lead wire length, connector specification

Code	Content
Blank	1 m (Standard)
3	3 m (Option)
5	5 m (Option)
W	M8 Connector, 1PIN (+), 4PIN (-) Lead Wire 0.3 m

\*5: Only T2WLH and T2WLV can be selected.

Example) Lead wire length  
1 m TOH  
3 m TOH<sup>[3]</sup>  
5 m TOH<sup>[5]</sup>

\*1: For "□" in the switch Model No., enter the code selected from the "Lead wire length, connector specification" table.

\*2: The maximum load current value above, 20 mA, is at 25°C. If the switch operating Ambient Temperature is higher than 25°C, it will be lower than 20 mA. (At 60°C, it will be 5 to 10 mA.)

\*3: This does not guarantee the water resistance of the cylinder.

\*4: Switches other than the Model No.s listed above are also available. (Custom Product) For details, refer to P. 1457.

Specifications

Item	STK-Y1			
Bore Size mm	ø20	ø32	ø40	ø50
Operation type	Double Acting spring loaded type			
Operating Fluid	Compressed Air			
Max Operating Pressure MPa	1.0			
Min Operating Pressure MPa	0.22	0.12		
Proof Pressure MPa	1.6			
Ambient Temperature °C	-10 to 60 (however, no freezing)			
Port Size	M5	Rc1/8		Rc1/4
Stroke tolerance mm	+2.0 0			
Operating Piston Speed mm/s	50 to 500			
Cushion	With Rubber Cushion			
Lubrication	Not required (Use Turbine Oil Class 1 ISO VG32 if lubricated)			
Rod End shape	Round bar type			
Allowable Absorbed Energy J	Refer to P. 986.			

Cylinder Weight Table

(Unit: g)

Stroke Bore Size	10	15	20	25	30	Switch weight (Grommet)
ø20	217	232	246	—	—	Refer to the mass listed in the Switch Specifications on P. 1457.
ø32	454	479	504	—	—	
ø40	-	—	809	850	891	
ø50	-	—	1299	1325	1351	

Theoretical Thrust Table

(Unit: N)

Bore Size (mm)	Operating Direction	Operating Pressure MPa									
		0.15	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
ø20	Push	-	-	94.2	1.26×10 <sup>2</sup>	1.57×10 <sup>2</sup>	1.88×10 <sup>2</sup>	2.20×10 <sup>2</sup>	2.51×10 <sup>2</sup>	2.83×10 <sup>2</sup>	3.14×10 <sup>2</sup>
	Pull	-	-	45.6	65.7	85.8	1.06×10 <sup>2</sup>	1.26×10 <sup>2</sup>	1.46×10 <sup>2</sup>	1.66×10 <sup>2</sup>	1.86×10 <sup>2</sup>
ø32	Push	1.21×10 <sup>2</sup>	1.61×10 <sup>2</sup>	2.41×10 <sup>2</sup>	3.22×10 <sup>2</sup>	4.02×10 <sup>2</sup>	4.83×10 <sup>2</sup>	5.63×10 <sup>2</sup>	6.43×10 <sup>2</sup>	7.24×10 <sup>2</sup>	8.04×10 <sup>2</sup>
	Pull	42.1	66.6	1.16×10 <sup>2</sup>	1.65×10 <sup>2</sup>	2.14×10 <sup>2</sup>	2.63×10 <sup>2</sup>	3.12×10 <sup>2</sup>	3.61×10 <sup>2</sup>	4.10×10 <sup>2</sup>	4.59×10 <sup>2</sup>
ø40	Push	1.88×10 <sup>2</sup>	2.51×10 <sup>2</sup>	3.77×10 <sup>2</sup>	5.03×10 <sup>2</sup>	6.28×10 <sup>2</sup>	7.54×10 <sup>2</sup>	8.80×10 <sup>2</sup>	1.01×10 <sup>3</sup>	1.13×10 <sup>3</sup>	1.26×10 <sup>3</sup>
	Pull	70.5	1.09×10 <sup>2</sup>	1.85×10 <sup>2</sup>	2.62×10 <sup>2</sup>	3.38×10 <sup>2</sup>	4.15×10 <sup>2</sup>	4.92×10 <sup>2</sup>	5.68×10 <sup>2</sup>	6.45×10 <sup>2</sup>	7.21×10 <sup>2</sup>
ø50	Push	2.95×10 <sup>2</sup>	3.93×10 <sup>2</sup>	5.89×10 <sup>2</sup>	7.85×10 <sup>2</sup>	9.82×10 <sup>2</sup>	1.18×10 <sup>3</sup>	1.37×10 <sup>3</sup>	1.57×10 <sup>3</sup>	1.77×10 <sup>3</sup>	1.96×10 <sup>3</sup>
	Pull	1.04×10 <sup>2</sup>	1.67×10 <sup>2</sup>	2.92×10 <sup>2</sup>	4.18×10 <sup>2</sup>	5.44×10 <sup>2</sup>	6.69×10 <sup>2</sup>	7.95×10 <sup>2</sup>	9.21×10 <sup>2</sup>	1.05×10 <sup>3</sup>	1.17×10 <sup>3</sup>

Stroke

Bore Size (mm)	Stroke (mm)	Maximum Stroke (mm)	Min Stroke (mm)	Minimum stroke with switch (mm)	
				T2WL	Other switches
ø20	10, 15, 20	20	10	20	10
ø40	20, 25, 30	30	20	20	20

Note: Strokes other than Standard Strokes are custom products.


Spring Load

(Unit: N)

Bore Size (mm)	Stroke (mm)	At 0 Stroke	At Full Stroke Operation
ø20	10	11.5	14.7
	15	9.9	
	20	8.2	
ø32	10	24.5	31.4
	15	21.1	
	20	17.6	
ø40	20	29.0	44.4
	25	25.3	
	30	21.5	
ø50	20	55.4	84.8
	25	48.0	
	30	40.7	


Dimensional Drawings

● STK-Y1-20



Note: For dimensions with each switch, please refer to P. 984.

● STK-Y1-20-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-Y1-20).)




Note: For dimensions with each switch, please refer to P. 984.


Double Acting, Spring loaded type, Rod End shape round bar type

Dimensional Drawings

● STK-Y1-32/40/50



● STK-Y1-32/40/50-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-Y1-32/40/50).)




Code	A	B	C	D	EE	F	G	H	I	J	K	KA	KK	L	M	MM	MN	N	O	P	U	V	X	Y
ø32	68	48	20	8	Rc1/8	45	49.5	24	5.5	9 Counterbore Depth 5.5	60	M6 Depth 11	M8 Depth 13	10	32	20	17	34	4.5	36	13	20	30	78
ø40	80.5	52.5	24.5	8.5	Rc1/8	52	57	24	5.5	9 Counterbore Depth 5.5	69	M6 Depth 11	M8 Depth 13	10	41	25	22	40	5	44	15	28	38	90.5
ø50	82	54	24.5	10.5	Rc1/4	64	71	33	6.9	11 Counterbore Depth 6.5	86	M8 Depth 13	M10 Depth 15	15	50	30	27	50	7	56	15	28	43	97


Note: For dimensions with each switch, please refer to P. 984.

## Internal Structure / Materials

● STK-Y1-20



● STK-Y1-32/40/50



Part No.	Part Name	Material	Remarks	Part No.	Part Name	Material	Remarks
1	Piston Rod	ø20: Stainless Steel ø32 to ø50: Steel	ø20: Industrial Chrome Plating ø32 to ø50: Industrial Chrome Plating	9	Magnet	Plastic	
2	Bushing	Bearing Alloy		10	Piston Packing	Nitrile Rubber	
3	Rod Cover	Aluminum Alloy	Alumite	11	Piston	Aluminum Alloy	Chromate
4	Rod Packing	Nitrile Rubber		12	Wear Ring	Polyacetal	
5	Hexagon Socket Set Screw	Steel	Black Oxide	13	Cushion rubber (H)	Urethane Rubber	
6	Metal gasket	Nitrile Rubber		14	Cylinder Body	Aluminum Alloy	Hard Anodized
7	Cushion rubber (R)	Urethane Rubber		15	Cover	ø20: Steel ø32 to ø50: Aluminum Alloy	ø20: Zinc plating ø32 to ø50: Anodized
8	Spacer	Aluminum Alloy	Chromate	16	Coil Spring	Piano Wire	Electrodeposition Coating

MEMO

For maintenance parts, please visit the CKD Equipment Product Site  
[\(https://www.ckd.co.jp/kiki/en/\)](https://www.ckd.co.jp/kiki/en/) → "model No." → Maintenance Parts.



Stopper cylinder Double Acting, Rod End shape chamfered type


# STK-M Series

● Bore Size:  $\phi 20$ ,  $\phi 32$ ,  $\phi 40$ ,  $\phi 50$




## Model No. Notation

Without Switch  
(Built-in magnet for switch)



With Switch  
(Built-in magnet for switch)




## 5 Number of Switches

Code	Content
R	With 1 pc on rod side
H	With 1 pc on head side
D	With 2 pcs

## 6 Option

Code	Content	
Blank	Rod End without thread	
N11	With Rod End female thread	

## Switch Single Unit Model No. Notation



### 1 Bore Size (mm)

Code	Content
20	$\phi 20$
32	$\phi 32$
40	$\phi 40$
50	$\phi 50$

### 2 Piping thread type

Code	Content
Blank	M5 ( $\phi 20$ ) Rc thread ( $\phi 32$ to $\phi 50$ )
NN	NPT thread ( $\phi 32$ or more) (Custom product)
GN	G thread ( $\phi 32$ or more) (Custom product)

### 3 Stroke (mm)

Bore Size	Stroke
$\phi 20$	10 to 20
$\phi 32$	10 to 20
$\phi 40$	20 to 30
$\phi 50$	20 to 30

Note: For Standard Stroke and minimum stroke with switch, please refer to P. 950.

### 4 Switch Model No.

For switch details, refer to P. 1457. Switches are shipped with the product.

Contact	Indicator LED Special Function	Wiring (Output)	Load Voltage (V)		Load Current (mA)		Lead wire *1		
			AC	DC	AC	DC	Straight	L-shape	
Solid State	1-Color	2-wire	85 to 265	—	5 to 100	—	T1H□	T1V□	
			—	10 to 30	—	5 to 20 *2	T2H□	T2V□	
		3-wire (NPN)	—	—	—	100 or less	T3H□	T3V□	
	3-wire (PNP)	—	30 or less	—	—	T3PH□	T3PV□		
	2-Color	2-wire	—	24 ± 10%	—	5 to 20	T2WH□	T2WV□	
			3-wire (NPN)	—	30 or less	—	50 or less	T3WH□	
		2-Color Improved Water Resistance	—	24 ± 10%	—	5 to 20	T2WLH□	T2WLV□	
	1-Color Off-Delay Type	2-wire	—	10 to 30	—	5 to 20 *2	T2JH□	T2JV□	
	1-Color Flexible Lead Wire Type	—	10 to 30	—	5 to 20 *2	T2HR3	T2VR3		
	Reed	1-Color Without Indicator Lamp	2-wire	110	12/24	7 to 20	5 to 50		T0H□
110				5/12/24	20 or less	50 or less	T5H□	T5V□	
1-Color		—	110/220	12/24	7 to 20 / 7 to 10	5 to 50	T8H□	T8V□	

\* Lead wire length, connector specification

Code	Content
Blank	1 m (Standard)
3	3 m (Option)
5	5 m (Option)
W	M8 Connector, 1PIN (+), 4PIN (-) Lead Wire 0.3 m

\*5: Only T2WLH and T2WLV can be selected.

Example) Lead wire length  
1 m T0H  
3 m T0H<sub>3</sub>  
5 m T0H<sub>5</sub>

\*1: For "□" in the switch Model No., enter the code selected from the "Lead wire length, connector specification" table.

\*2: The maximum load current value above, 20 mA, is at 25°C. If the switch operating Ambient Temperature is higher than 25°C, it will be lower than 20 mA. (At 60°C, it will be 5 to 10 mA.)

\*3: This does not guarantee the water resistance of the cylinder.

\*4: Switches other than the Model No.s listed above are also available. (Custom Product) For details, refer to P. 1457.

## Specifications

Item	STK-M				
	mm	ø20	ø32	ø40	ø50
Bore Size	mm	ø20	ø32	ø40	ø50
Actuation method		Double Acting Type			
Operating Fluid		Compressed Air			
Max Operating Pressure	MPa	1.0			
Min Operating Pressure	MPa	0.15	0.1		
Proof Pressure	MPa	1.6			
Ambient Temperature	°C	-10 to 60 (however, no freezing)			
Port Size		M5	Rc1/8	Rc1/4	
Stroke tolerance	mm	+2.0 0			
Operating Piston Speed	mm/s	50 to 500			
Cushion		With Rubber Cushion			
Lubrication		Not required (Use Turbine Oil Class 1 ISO VG32 if lubricated)			
Rod End shape		Chamfered type			
Allowable Absorbed Energy	J	Refer to P. 986.			

MEMO

## Stroke

	Bore Size (mm)	Stroke (mm)	Max Stroke (mm)	Min Stroke (mm)	Min stroke with switch (mm)	
					T2WL	Other switches
MCP	ø20	10, 15, 20	20	10	20	10
	ø32					
GLC	ø40	20, 25, 30	30	20	20	20
	ø50					

Note: Strokes other than Standard Strokes are custom products.

## Cylinder Weight Table

(Unit: g)

Stroke	10	15	20	25	30	Switch Weight (Grommet)
ø20	215	230	244	—	—	Refer to the mass listed in the Switch Specifications on P. 1457.
ø32	441	466	491	—	—	
ø40	-	—	796	837	878	
ø50	-	—	1288	1314	1340	


## Theoretical Thrust Table

(Unit: N)

Bore Size (mm)	Operating Direction	Operating Pressure MPa										
		0.1	0.15	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
ø20	Push	-	-	62.8	94.2	1.26×10 <sup>2</sup>	1.57×10 <sup>2</sup>	1.88×10 <sup>2</sup>	2.20×10 <sup>2</sup>	2.51×10 <sup>2</sup>	2.83×10 <sup>2</sup>	3.14×10 <sup>2</sup>
	Pull	-	-	40.2	60.3	80.4	1.01×10 <sup>2</sup>	1.21×10 <sup>2</sup>	1.41×10 <sup>2</sup>	1.61×10 <sup>2</sup>	1.81×10 <sup>2</sup>	2.01×10 <sup>2</sup>
ø32	Push	80.4	1.21×10 <sup>2</sup>	1.61×10 <sup>2</sup>	2.41×10 <sup>2</sup>	3.22×10 <sup>2</sup>	4.02×10 <sup>2</sup>	4.83×10 <sup>2</sup>	5.63×10 <sup>2</sup>	6.43×10 <sup>2</sup>	7.24×10 <sup>2</sup>	8.04×10 <sup>2</sup>
	Pull	49.0	73.5	98.0	1.47×10 <sup>2</sup>	1.96×10 <sup>2</sup>	2.45×10 <sup>2</sup>	2.94×10 <sup>2</sup>	3.43×10 <sup>2</sup>	3.92×10 <sup>2</sup>	4.41×10 <sup>2</sup>	4.90×10 <sup>2</sup>
ø40	Push	1.26×10 <sup>2</sup>	1.88×10 <sup>2</sup>	2.51×10 <sup>2</sup>	3.77×10 <sup>2</sup>	5.03×10 <sup>2</sup>	6.28×10 <sup>2</sup>	7.54×10 <sup>2</sup>	8.80×10 <sup>2</sup>	1.01×10 <sup>3</sup>	1.13×10 <sup>3</sup>	1.26×10 <sup>3</sup>
	Pull	76.6	1.15×10 <sup>2</sup>	1.53×10 <sup>2</sup>	2.30×10 <sup>2</sup>	3.06×10 <sup>2</sup>	3.83×10 <sup>2</sup>	4.59×10 <sup>2</sup>	5.36×10 <sup>2</sup>	6.13×10 <sup>2</sup>	6.89×10 <sup>2</sup>	7.66×10 <sup>2</sup>
ø50	Push	1.96×10 <sup>2</sup>	2.95×10 <sup>2</sup>	3.93×10 <sup>2</sup>	5.89×10 <sup>2</sup>	7.85×10 <sup>2</sup>	9.82×10 <sup>2</sup>	1.18×10 <sup>3</sup>	1.37×10 <sup>3</sup>	1.57×10 <sup>3</sup>	1.77×10 <sup>3</sup>	1.96×10 <sup>3</sup>
	Pull	1.26×10 <sup>2</sup>	1.88×10 <sup>2</sup>	2.51×10 <sup>2</sup>	3.77×10 <sup>2</sup>	5.03×10 <sup>2</sup>	6.28×10 <sup>2</sup>	7.54×10 <sup>2</sup>	8.80×10 <sup>2</sup>	1.01×10 <sup>3</sup>	1.13×10 <sup>3</sup>	1.26×10 <sup>3</sup>


Dimensional Drawings

● STK-M-20



Note: For dimensions with each switch, please refer to P. 984.

● STK-M-20-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-M-20).)




Note: For dimensions with each switch, please refer to P. 984.


Double Acting type, Rod End shape chamfered type

Dimensional Drawings

● STK-M-32/40/50



● STK-M-32/40/50-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-M-32/40/50).)



Code	A	B	C	D	EE	F	G	H	I	J	K	KA	KK	L	M	MM	MN	N	O	P	T	U	V	X	Y
ø32	68	48	20	8	Rc1/8	45	49.5	24	5.5	9 Counterbore Depth 5.5	60	M6 Depth 11	M8 Depth 13	10	32	20	17	34	4.5	36	8	13	20	30	78
ø40	80.5	52.5	24.5	8.5	Rc1/8	52	57	24	5.5	9 Counterbore Depth 5.5	69	M6 Depth 11	M8 Depth 13	10	41	25	22	40	5	44	10	15	28	38	90.5
ø50	82	54	24.5	10.5	Rc1/4	64	71	33	6.9	11 Counterbore Depth 6.5	86	M8 Depth 13	M10 Depth 15	15	50	30	27	50	7	56	12	15	28	43	97

Note: For dimensions with each switch, please refer to P. 984.

Special

MVC

STK

MCP

GLC

BBS

NHS

HR

LN

Cylinder Switch

Ending

Special

MVC

STK

MCP

GLC

BBS

NHS

HR


LN

Cylinder Switch


Ending

## Internal Structure / Materials

● STK-M-20



● STK-M-32/40/50



Part No.	Part Name	Material	Remarks	Part No.	Part Name	Material	Remarks
1	Piston Rod	Stainless Steel	Industrial Hard Chrome Plating	11	Piston Packing	Nitrile Rubber	
2	Bushing	Bearing Alloy		12	Piston	Aluminum Alloy	Chromate
3	Rod Cover	Aluminum Alloy	Alumite	13	Wear Ring	Polyacetal	
4	Rod Packing	Nitrile Rubber		14	Cushion rubber (H)	Urethane Rubber	
5	Hexagon Socket Set Screw	Steel	Black Oxide	15	Cylinder Body	Aluminum Alloy	Hard Anodized
6	Metal gasket	Nitrile Rubber		16	Cover	ø20: Stainless Steel ø32 to 50: Aluminum Alloy	ø32 to ø50: Anodized
7	Cushion rubber (R)	Urethane Rubber		17	Non-rotating spacer	Steel	Nickel Plating
8	Spacer washer	Stainless Steel		18	Hexagon Socket Set Screw	Steel	Black Oxide
9	Spacer	Polyamide					
10	Magnet	Plastic					

MEMO

For maintenance parts, please visit the CKD Equipment Product Site  
 (<https://www.ckd.co.jp/kiki/en/>) → "model No." → Maintenance Parts.

Special

Special

MVC

MVC

STK

STK

MCP

MCP

GLC

GLC

BBS

BBS

NHS

NHS

HR

HR

LN

LN

Cylinder Switch

Cylinder Switch

Ending

Ending



Stopper Cylinder, Single Acting, Retraction Type,  
Rod End Shape Chamfered Type

# STK-MY Series

● Bore Size: ø20, ø32, ø40, ø50


Circuit Diagram   
Code

Single Acting, Retracting Type




## Model No. Notation

Without Switch  
(Built-in magnet for switch)



With Switch  
(Built-in magnet for switch)




## 5 Number of Switches

Code	Content
R	With 1 pc on rod side
H	With 1 pc on head side
D	With 2 pcs

## 6 Option

Code	Content	
Blank	Rod End without thread	
N11	With Rod End female thread	

## Switch Single Unit Model No. Notation



### 1 Bore Size (mm)

Code	Content
20	ø20
32	ø32
40	ø40
50	ø50

### 2 Piping thread type

Code	Content
Blank	M5 (ø20)
NN	Rc thread (ø32 to ø50)
GN	NPT thread (ø32 or more) (Custom product)
GN	G thread (ø32 or more) (Custom product)

### 3 Stroke (mm)

Bore Size	Stroke
ø20	10 to 20
ø32	10 to 20
ø40	20 to 30
ø50	20 to 30

Note: For Standard Stroke and minimum stroke with switch, please refer to P. 958.

### 4 Switch Model No.

For switch details, refer to P. 1457. Switches are shipped with the product.

Contact	Indicator LED Special Function	Wiring (Output)	Load Voltage (V)		Load Current (mA)		Lead wire *1		
			AC	DC	AC	DC	Straight	L-shape	
Solid State	1-Color	2-wire	85 to 265	—	5 to 100	—	T1H□	T1V□	
			—	10 to 30	—	5 to 20 *2	T2H□	T2V□	
		3-wire (NPN)	—	—	100 or less	—	T3H□	T3V□	
	2-Color	2-wire	—	24 ± 10%	—	5 to 20	T2WH□	T2WV□	
			3-wire (PNP)	—	30 or less	—	50 or less	T3WH□	
	2-Color Water Resistance Improved	2-wire	—	24 ± 10%	—	5 to 20	T2WLH□	T2WLV□	
			3-wire (NPN)	—	30 or less	—	50 or less	T3WLH□	
	1-Color Off-Delay Type	2-wire	—	10 to 30	—	5 to 20 *2	T2JH□	T2JV□	
			—	10 to 30	—	5 to 20 *2	T2HR3	T2VR3	
	Reed	1-Color Without Indicator Lamp	2-wire	110	12/24	7 to 20	5 to 50	T0H□	T0V□
110				5/12/24	20 or less	50 or less	T5H□	T5V□	
1-Color		110/220	12/24	7 to 20 / 7 to 10	5 to 50	T8H□	T8V□		

\* Lead wire length, connector specification

Code	Content
Blank	1 m (Standard)
3	3 m (Option)
5	5 m (Option)
W	M8 Connector, 1PIN (+), 4PIN (-) Lead Wire 0.3 m

\*5: Only T2WLH and T2WLV can be selected.

Example) Lead wire length  
1 m T0H  
3 m T0H<sub>[3]</sub>  
5 m T0H<sub>[5]</sub>

\*1: For "□" in the switch Model No., enter the code selected from the "Lead wire length, connector specification" table.

\*2: The maximum load current value above, 20 mA, is at 25°C. If the switch operating Ambient Temperature is higher than 25°C, it will be lower than 20 mA. (At 60°C, it will be 5 to 10 mA.)

\*3: This does not guarantee the water resistance of the cylinder.

\*4: Switches other than the Model No.s listed above are also available. (Custom Product) For details, refer to P. 1457.

Specifications

Item	STK-MY				
	mm	ø20	ø32	ø40	ø50
Bore Size	mm	ø20	ø32	ø40	ø50
Operation type	Single Acting, Retracting Type				
Operating Fluid	Compressed Air				
Max Operating Pressure	MPa	1.0			
Min Operating Pressure	MPa	0.22	0.12		
Proof Pressure	MPa	1.6			
Ambient Temperature	°C	-10 to 60 (however, no freezing)			
Port Size		M5	Rc1/8	Rc1/4	
Stroke tolerance	mm	+2.0			
		0			
Operating Piston Speed	mm/s	50 to 500			
Cushion	With Rubber Cushion				
Lubrication	Not required (Use Turbine Oil Class 1 ISO VG32 if lubricated)				
Rod End shape	Chamfered type				
Allowable Absorbed Energy	J	Refer to P. 986.			

Cylinder Weight Table

(Unit: g)

Stroke Bore Size	10	15	20	25	30	Switch Weight (Grommet)
ø20	218	233	247	—	—	Refer to the mass listed in the Switch Specifications on P. 1457.
ø32	457	482	507	—	—	
ø40	-	—	812	853	894	
ø50	-	—	1302	1328	1354	

Theoretical Thrust Table

(Unit: N)

Bore Size (mm)	Operating Pressure MPa								
	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
ø20	-	45.6	65.7	85.8	1.06×10 <sup>2</sup>	1.26×10 <sup>2</sup>	1.46×10 <sup>2</sup>	1.66×10 <sup>2</sup>	1.86×10 <sup>2</sup>
ø32	66.6	1.16×10 <sup>2</sup>	1.65×10 <sup>2</sup>	2.14×10 <sup>2</sup>	2.63×10 <sup>2</sup>	3.12×10 <sup>2</sup>	3.61×10 <sup>2</sup>	4.10×10 <sup>2</sup>	4.59×10 <sup>2</sup>
ø40	1.09×10 <sup>2</sup>	1.85×10 <sup>2</sup>	2.62×10 <sup>2</sup>	3.38×10 <sup>2</sup>	4.15×10 <sup>2</sup>	4.92×10 <sup>2</sup>	5.68×10 <sup>2</sup>	6.45×10 <sup>2</sup>	7.21×10 <sup>2</sup>
ø50	1.67×10 <sup>2</sup>	2.92×10 <sup>2</sup>	4.18×10 <sup>2</sup>	5.44×10 <sup>2</sup>	6.69×10 <sup>2</sup>	7.95×10 <sup>2</sup>	9.21×10 <sup>2</sup>	1.05×10 <sup>3</sup>	1.17×10 <sup>3</sup>

Stroke

Bore Size (mm)	Stroke (mm)	Maximum Stroke (mm)	Min Stroke (mm)	Minimum stroke with switch (mm)	
				T2WL	Other switches
ø20	10, 15, 20	20	10	20	10
ø32					
ø40	20, 25, 30	30	20	20	20
ø50					

Note: Strokes other than Standard Strokes are custom products.


Spring Load

(Unit: N)

Bore Size (mm)	Stroke (mm)	At 0 Stroke	At Full Stroke Operation
ø20	10	11.5	14.7
	15	9.9	
	20	8.2	
ø32	10	24.5	31.4
	15	21.1	
	20	17.6	
ø40	20	29.0	44.4
	25	25.3	
	30	21.5	
ø50	20	55.4	84.8
	25	48.0	
	30	40.7	


Dimensional Drawings

● STK-MY-20



Note: For dimensions with each switch, please refer to P. 984.

● STK-MY-20-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-MY-20).)




Note: For dimensions with each switch, please refer to P. 984.


Single Acting, Retraction type, Rod End shape chamfered type

Dimensional Drawings

● STK-MY-32/40/50



● STK-MY-32/40/50-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-MY-32/40/50).)




Code	A	B	C	D	EE	F	G	H	I	J	K	KA	KK	L	M	MM	MN	N	O	P	T	U	V	X	Y
ø32	68	48	20	8	Rc1/8	45	49.5	24	5.5	9 Counterbore Depth 5.5	60	M6 Depth 11	M8 Depth 13	10	32	20	17	34	4.5	36	8	13	20	30	78
ø40	80.5	52.5	24.5	8.5	Rc1/8	52	57	24	5.5	9 Counterbore Depth 5.5	69	M6 Depth 11	M8 Depth 13	10	41	25	22	40	5	44	10	15	28	38	90.5
ø50	82	54	24.5	10.5	Rc1/4	64	71	33	6.9	11 Counterbore Depth 6.5	86	M8 Depth 13	M10 Depth 15	15	50	30	27	50	7	56	12	15	28	43	97


Note: For dimensions with each switch, please refer to P. 984.

## Internal Structure / Materials

### ● STK-MY-20



### ● STK-MY-32/40/50



Part No.	Part Name	Material	Remarks	Part No.	Part Name	Material	Remarks
1	Piston Rod	Stainless Steel	Industrial Hard Chrome Plating	12	Wear Ring	Polyacetal	
2	Bushing	Bearing Alloy		13	Cushion rubber (H)	Urethane Rubber	
3	Rod Cover	Aluminum Alloy	Alumite	14	Cylinder Body	Aluminum Alloy	Hard Anodized
4	Rod Packing	Nitrile Rubber		15	Cover	ø20: Steel ø32 to 50: Aluminum Alloy	ø20: Zinc plating ø32 to ø50: Anodized
5	Hexagon Socket Set Screw	Steel	Black Oxide	16	Non-rotating spacer	Steel	Nickel Plating
6	Metal gasket	Nitrile Rubber		17	Hexagon Socket Set Screw	Steel	Black Oxide
7	Cushion rubber (R)	Urethane Rubber		18	Coil Spring	Piano Wire	Electrodeposition Coating
8	Spacer	Aluminum Alloy		19	Stainless Steel Wire Mesh	Stainless Steel	
9	Magnet	Plastic	Chromate	20	Plug	Stainless Steel	
10	Piston Packing	Nitrile Rubber					
11	Piston	Aluminum Alloy	Chromate				

MEMO


For maintenance parts, please visit the CKD Equipment Product Site (<https://www.ckd.co.jp/kiki/en/>) → "model No." → Maintenance Parts .



Stopper Cylinder, Double Acting, Spring Loaded Type, Rod End Shape Chamfered Type

# STK-MY1 Series

● Bore Size:  $\phi 20$ ,  $\phi 32$ ,  $\phi 40$ ,  $\phi 50$




Double Acting, spring loaded type



## STK-MY1 Series

Model No. Notation

### Model No. Notation




### 5 Number of Switches

Code	Content
R	With 1 pc on rod side
H	With 1 pc on head side
D	With 2 pcs

### 6 Option

Code	Content
Blank	Rod End without thread
N11	With Rod End female thread

### Switch Single Unit Model No. Notation



### 1 Bore Size (mm)

Code	Content
20	$\phi 20$
32	$\phi 32$
40	$\phi 40$
50	$\phi 50$

### 2 Piping thread type

Code	Content
Blank	M5 ( $\phi 20$ ) Rc thread ( $\phi 32$ to $\phi 50$ )
NN	NPT thread ( $\phi 32$ or more) (Custom product)
GN	G thread ( $\phi 32$ or more) (Custom product)

### 3 Stroke (mm)

Bore Size	Stroke
$\phi 20$	10 to 20
$\phi 32$	10 to 20
$\phi 40$	20 to 30
$\phi 50$	20 to 30

Note: For Standard Stroke and minimum stroke with switch, please refer to P. 966.

### 4 Switch Model No.

For switch details, refer to P. 1457. Switches are shipped with the product.

Contact	Indicator LED Special Function	Wiring (Output)	Load Voltage (V)		Load Current (mA)		Lead wire *1		Image
			AC	DC	AC	DC	Straight	L-shape	
Solid State	1-Color	2-wire	85 to 265	—	5 to 100	—	T1H□	T1V□	*3
			—	10 to 30	—	5 to 20 *2	T2H□	T2V□	
		3-wire (NPN)	—	—	—	100 or less	T3H□	T3V□	
	3-wire (PNP)	—	30 or less	—	—	T3PH□	T3PV□		
	2-Color	2-wire	—	24 ± 10%	—	5 to 20	T2WH□	T2WV□	
			—	30 or less	—	50 or less	T3WH□	T3WV□	
Reed	2-Color Improved Water Resistance	2-wire	—	24 ± 10%	—	5 to 20	T2WLH□	T2WLV□	
			—	10 to 30	—	5 to 20 *2	T2JH□	T2JV□	
	1-Color Off-Delay Type	2-wire	—	10 to 30	—	5 to 20 *2	T2HR3	T2VR3	
			—	10 to 30	—	5 to 20 *2	T2HR3	T2VR3	
1-Color Flexible Lead Wire Type	2-wire	110	12/24	7 to 20	5 to 50	T0H□	T0V□		
		110	5/12/24	20 or less	50 or less	T5H□	T5V□		
1-Color Without Indicator Lamp	2-wire	110/220	12/24	7 to 20 / 7 to 10	5 to 50	T8H□	T8V□		

\*Lead wire length, connector specification

Code	Content
Blank	1 m (Standard)
3	3 m (Option)
5	5 m (Option)
W	M8 Connector, 1PIN (+), 4PIN (-) Lead Wire 0.3 m

\*5: Only T2WLH and T2WLV can be selected.

Example) Lead wire length  
1 m T0H  
3 m T0H<sub>3</sub>  
5 m T0H<sub>5</sub>

\*1: For "□" in the switch Model No., enter the code selected from the "Lead wire length, connector specification" table.  
\*2: The maximum load current value above, 20 mA, is at 25°C. If the switch operating Ambient Temperature is higher than 25°C, it will be lower than 20 mA. (At 60°C, it will be 5 to 10 mA.)  
\*3: This does not guarantee the water resistance of the cylinder.  
\*4: Switches other than the Model No. listed above are also available. (Custom Product) For details, refer to P. 1457.

Specifications

Item	STK-MY1				
	mm	ø20	ø32	ø40	ø50
Bore Size	mm	ø20	ø32	ø40	ø50
Operation type	Double Acting spring loaded type				
Operating Fluid	Compressed Air				
Max Operating Pressure	MPa	1.0			
Min Operating Pressure	MPa	0.22	0.12		
Proof Pressure	MPa	1.6			
Ambient Temperature	°C	-10 to 60 (however, no freezing)			
Port Size		M5	Rc1/8	Rc1/4	
Stroke tolerance	mm	+2.0			0
Operating Piston Speed	mm/s	50 to 500			
Cushion	With Rubber Cushion				
Lubrication	Not required (Use Turbine Oil Class 1 ISO VG32 if lubricated)				
Rod End shape	Chamfered type				
Allowable Absorbed Energy	J	Refer to P. 986.			

Cylinder Weight

(Unit: g)

Stroke Bore Size	10	15	20	25	30	Switch Weight (Grommet)
ø20	218	233	247	—	—	Refer to the mass listed in the Switch Specifications on P. 1457.
ø32	457	482	507	—	—	
ø40	-	—	812	853	894	
ø50	-	—	1302	1328	1354	

Theoretical Thrust Table

(Unit: N)

Bore Size (mm)	Operating Direction	Operating Pressure MPa									
		0.15	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
ø20	Push	-	-	94.2	1.26×10 <sup>2</sup>	1.57×10 <sup>2</sup>	1.88×10 <sup>2</sup>	2.20×10 <sup>2</sup>	2.51×10 <sup>2</sup>	2.83×10 <sup>2</sup>	3.14×10 <sup>2</sup>
	Pull	-	-	45.6	65.7	85.8	1.06×10 <sup>2</sup>	1.26×10 <sup>2</sup>	1.46×10 <sup>2</sup>	1.66×10 <sup>2</sup>	1.86×10 <sup>2</sup>
ø32	Push	1.21×10 <sup>2</sup>	1.61×10 <sup>2</sup>	2.41×10 <sup>2</sup>	3.22×10 <sup>2</sup>	4.02×10 <sup>2</sup>	4.83×10 <sup>2</sup>	5.63×10 <sup>2</sup>	6.43×10 <sup>2</sup>	7.24×10 <sup>2</sup>	8.04×10 <sup>2</sup>
	Pull	42.1	66.6	1.16×10 <sup>2</sup>	1.65×10 <sup>2</sup>	2.14×10 <sup>2</sup>	2.63×10 <sup>2</sup>	3.12×10 <sup>2</sup>	3.61×10 <sup>2</sup>	4.10×10 <sup>2</sup>	4.59×10 <sup>2</sup>
ø40	Push	1.88×10 <sup>2</sup>	2.51×10 <sup>2</sup>	3.77×10 <sup>2</sup>	5.03×10 <sup>2</sup>	6.28×10 <sup>2</sup>	7.54×10 <sup>2</sup>	8.80×10 <sup>2</sup>	1.01×10 <sup>3</sup>	1.13×10 <sup>3</sup>	1.26×10 <sup>3</sup>
	Pull	70.5	1.09×10 <sup>2</sup>	1.85×10 <sup>2</sup>	2.62×10 <sup>2</sup>	3.38×10 <sup>2</sup>	4.15×10 <sup>2</sup>	4.92×10 <sup>2</sup>	5.68×10 <sup>2</sup>	6.45×10 <sup>2</sup>	7.21×10 <sup>2</sup>
ø50	Push	2.95×10 <sup>2</sup>	3.93×10 <sup>2</sup>	5.89×10 <sup>2</sup>	7.85×10 <sup>2</sup>	9.82×10 <sup>2</sup>	1.18×10 <sup>3</sup>	1.37×10 <sup>3</sup>	1.57×10 <sup>3</sup>	1.77×10 <sup>3</sup>	1.96×10 <sup>3</sup>
	Pull	1.04×10 <sup>2</sup>	1.67×10 <sup>2</sup>	2.92×10 <sup>2</sup>	4.18×10 <sup>2</sup>	5.44×10 <sup>2</sup>	6.69×10 <sup>2</sup>	7.95×10 <sup>2</sup>	9.21×10 <sup>2</sup>	1.05×10 <sup>3</sup>	1.17×10 <sup>3</sup>

Stroke

Bore Size (mm)	Stroke (mm)	Maximum Stroke (mm)	Min Stroke (mm)	Minimum stroke with switch (mm)	
				T2WL	Other switches
ø20	10, 15, 20	20	10	20	10
ø32					
ø40	20, 25, 30	30	20	20	20
ø50					

Note: Strokes other than Standard Strokes are custom products.


Spring Load

(Unit: N)

Bore Size (mm)	Stroke (mm)	At 0 Stroke	At Full Stroke Operation
ø20	10	11.5	14.7
	15	9.9	
	20	8.2	
ø32	10	24.5	31.4
	15	21.1	
	20	17.6	
ø40	20	29.0	44.4
	25	25.3	
	30	21.5	
ø50	20	55.4	84.8
	25	48.0	
	30	40.7	


Dimensional Drawings

● STK-MY1-20



Note: For dimensions with each switch, please refer to P. 984.

● STK-MY1-20-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-MY1-20).)




Note: For dimensions with each switch, please refer to P. 984.


Double Acting, Spring loaded type, Rod End shape chamfered type

Dimensional Drawings

● STK-MY1-32/40/50




● STK-MY1-32/40/50-N11 (Dimensions other than displayed dimensions are the same as those of the above (STK-MY1-32/40/50).)




Code	A	B	C	D	EE	F	G	H	I	J	K	KA	KK	L	M	MM	MN	N	O	P	T	U	V	X	Y
ø32	68	48	20	8	Rc1/8	45	49.5	24	5.5	9 Counterbore Depth 5.5	60	M6 Depth 11	M8 Depth 13	10	32	20	17	34	4.5	36	8	13	20	30	78
ø40	80.5	52.5	24.5	8.5	Rc1/8	52	57	24	5.5	9 Counterbore Depth 5.5	69	M6 Depth 11	M8 Depth 13	10	41	25	22	40	5	44	10	15	28	38	90.5
ø50	82	54	24.5	10.5	Rc1/4	64	71	33	6.9	11 Counterbore Depth 6.5	86	M8 Depth 13	M10 Depth 15	15	50	30	27	50	7	56	12	15	28	43	97

Note: For dimensions with each switch, please refer to P. 984.

● STK-MY1-20



● STK-MY1-32/40/50



Part No.	Part Name	Material	Remarks	Part No.	Part Name	Material	Remarks
1	Piston Rod	Stainless Steel	Industrial Hard Chrome Plating	11	Piston	Aluminum Alloy	Chromate
2	Bushing	Bearing Alloy		12	Wear Ring	Polyacetal	
3	Rod Cover	Aluminum Alloy	Alumite	13	Cushion rubber (H)	Urethane Rubber	
4	Rod Packing	Nitrile Rubber		14	Cylinder Body	Aluminum Alloy	Hard Anodized
5	Hexagon Socket Set Screw	Steel	Black Oxide	15	Cover	ø20: Steel ø32 to 50: Aluminum Alloy	ø20: Zinc plating ø32 to ø50: Anodized
6	Metal gasket	Nitrile Rubber		16	Non-rotating spacer	Steel	Nickel Plating
7	Cushion rubber (R)	Urethane Rubber		17	Hexagon Socket Set Screw	Steel	Black Oxide
8	Spacer	Aluminum Alloy	Chromate	18	Coil Spring	Piano Wire	Electrodeposition Coating
9	Magnet	Plastic					
10	Piston Packing	Nitrile Rubber					

MEMO

For maintenance parts, please visit the CKD Equipment Product Site  
 (<https://www.ckd.co.jp/kiki/en/>) → "model No." → Maintenance Parts .

Special

MVC

STK

MCP

GLC

BBS

NHS

HR

LN

Cylinder Switch

Ending

Special

MVC

STK

MCP

GLC

BBS

NHS

HR

LN

Cylinder Switch

Ending



Stopper Cylinder, Single Acting, Retraction Type, Rod End Shape Roller Type

# STK-JY Series

● Bore Size:  $\phi 20$ ,  $\phi 32$ ,  $\phi 40$ ,  $\phi 50$




Single Acting, Retracting Type




## Model No. Notation

Without Switch  
(Built-in magnet for switch)




With Switch  
(Built-in magnet for switch)



## 5 Number of Switches

Code	Content
R	With 1 pc on rod side
H	With 1 pc on head side
D	With 2 pcs

## Switch Single Unit Model No. Notation



### 1 Bore Size (mm)

Code	Content
20	$\phi 20$
32	$\phi 32$
40	$\phi 40$
50	$\phi 50$

### 2 Piping thread type

Code	Content
Blank	M5 ( $\phi 20$ ) Rc thread ( $\phi 32$ to $\phi 50$ )
NN	NPT thread ( $\phi 32$ or more) (Custom product)
GN	G thread ( $\phi 32$ or more) (Custom product)

### 3 Stroke (mm)

Bore Size	Stroke
$\phi 20$	10 to 20
$\phi 32$	10 to 20
$\phi 40$	20 to 30
$\phi 50$	20 to 30

Note: For Standard Stroke and minimum stroke with switch, please refer to P. 974.

### 4 Switch Model No.

For switch details, refer to P. 1457. Switches are shipped with the product.

Contact	Indicator LED Special Function	Wiring (Output)	Load Voltage (V)		Load Current (mA)		Lead wire *1		Image	
			AC	DC	AC	DC	Straight	L-shape		
Solid State	1-Color	2-wire	85 to 265	—	5 to 100	—	T1H□	T1V□		
			—	10 to 30	—	5 to 20 *2	T2H□	T2V□		
		3-wire (NPN)	—	30 or less	—	100 or less	T3H□	T3V□		
	3-wire (PNP)	—	—	—	—	T3PH□	T3PV□			
	2-Color	2-wire	—	24 ± 10%	—	5 to 20	T2WH□	T2WV□		
			3-wire (NPN)	—	30 or less	—	50 or less	T3WH□		T3WV□
2-Color Improved Water Resistance	2-wire	2-wire	—	24 ± 10%	—	5 to 20	T2WLH□	T2WLV□		
			1-Color Off-Delay Type	—	10 to 30	—	5 to 20 *2	T2JH□		T2JV□
			1-Color Flexible Lead Wire Type	—	10 to 30	—	5 to 20 *2	T2HR3		T2VR3
Reed	1-Color No Indicator LED	2-wire	110	12/24	7 to 20	5 to 50	T0H□	T0V□		
			110	5/12/24	20 or less	50 or less	T5H□	T5V□		
	1-Color	2-wire	110/220	12/24	7 to 20 / 7 to 10	5 to 50	T8H□	T8V□		

### \*Lead wire length, connector specification

Code	Content
Blank	1 m (Standard)
3	3 m (Option)
5	5 m (Option)
W	M8 Connector, 1PIN (+), 4PIN (-) Lead Wire 0.3 m

\*5: Only T2WLH and T2WLV can be selected.

Example) Lead wire length  
1 m T0H  
3 m T0H<sub>3</sub>  
5 m T0H<sub>5</sub>

\*1: For "□" in the switch Model No., enter the code selected from the "Lead wire length, connector specification" table.

\*2: The maximum load current value above, 20 mA, is at 25°C. If the switch operating Ambient Temperature is higher than 25°C, it will be lower than 20 mA. (At 60°C, it will be 5 to 10 mA.)

\*3: This does not guarantee the water resistance of the cylinder.

\*4: Switches other than the Model No. listed above are also available. (Custom Product) For details, refer to P. 1457.

Specifications

Item	STK-JY				
	mm	ø20	ø32	ø40	ø50
Bore Size	mm	ø20	ø32	ø40	ø50
Operation type	Single Acting, Retracting Type				
Operating Fluid	Compressed Air				
Max Operating Pressure	MPa	1.0			
Min Operating Pressure	MPa	0.22	0.12		
Proof Pressure	MPa	1.6			
Ambient Temperature	°C	-10 to 60 (however, no freezing)			
Port Size		M5	Rc1/8	Rc1/4	
Stroke tolerance	mm	+2.0			0
Operating Piston Speed	mm/s	50 to 500			
Cushion	With Rubber Cushion				
Lubrication	Not required (Use Turbine Oil Class 1 ISO VG32 if lubricated)				
Rod End shape	Roller type				
Allowable Absorbed Energy	J	Refer to P. 986.			

Cylinder Weight

(Unit: g)

Stroke Bore Size	10	15	20	25	30	Switch Weight (Grommet)
ø20	225	240	254	—	—	Refer to the mass listed in the Switch Specifications on P. 1457.
ø32	482	507	532	—	—	
ø40	-	—	862	903	944	
ø50	-	—	1362	1388	1414	

Theoretical Thrust Table

(Unit: N)

Bore Size (mm)	Operating Pressure MPa								
	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
ø20	-	45.6	65.7	85.8	1.06×10 <sup>2</sup>	1.26×10 <sup>2</sup>	1.46×10 <sup>2</sup>	1.66×10 <sup>2</sup>	1.86×10 <sup>2</sup>
ø32	66.6	1.16×10 <sup>2</sup>	1.65×10 <sup>2</sup>	2.14×10 <sup>2</sup>	2.63×10 <sup>2</sup>	3.12×10 <sup>2</sup>	3.61×10 <sup>2</sup>	4.10×10 <sup>2</sup>	4.59×10 <sup>2</sup>
ø40	1.09×10 <sup>2</sup>	1.85×10 <sup>2</sup>	2.62×10 <sup>2</sup>	3.38×10 <sup>2</sup>	4.15×10 <sup>2</sup>	4.92×10 <sup>2</sup>	5.68×10 <sup>2</sup>	6.45×10 <sup>2</sup>	7.21×10 <sup>2</sup>
ø50	1.67×10 <sup>2</sup>	2.92×10 <sup>2</sup>	4.18×10 <sup>2</sup>	5.44×10 <sup>2</sup>	6.69×10 <sup>2</sup>	7.95×10 <sup>2</sup>	9.21×10 <sup>2</sup>	1.05×10 <sup>3</sup>	1.17×10 <sup>3</sup>

Stroke

Bore Size (mm)	Stroke (mm)	Maximum Stroke (mm)	Min Stroke (mm)	Minimum stroke with switch (mm)	
				T2WL	Other switches
ø20	10, 15, 20	20	10	20	10
ø32					
ø40	20, 25, 30	30	20	20	20
ø50					

Note: Strokes other than Standard Strokes are custom products.


Spring Load

(Unit: N)

Bore Size (mm)	Stroke (mm)	At 0 Stroke	At Full Stroke Operation
ø20	10	11.5	14.7
	15	9.9	
	20	8.2	
ø32	10	24.5	31.4
	15	21.1	
	20	17.6	
ø40	20	29.0	44.4
	25	25.3	
	30	21.5	
ø50	20	55.4	84.8
	25	48.0	
	30	40.7	


Dimensional Drawings

● STK-JY-20



Note: For dimensions with each switch, please refer to P. 984.

● STK-JY-32/40/50




Code	A	B	C	D	EE	F	G	H	I	J	K	KA	L	M	MM	N	O	P	Q	R	S	T	U	V	W
● $\phi 32$	68	48	20	8	Rc1/8	45	49.5	24	5.5	9 Counterbore Depth 5.5	60	M6 Depth 11	10	32	20	34	4.5	36	3	19	18	8	13	20	8
● $\phi 40$	80.5	52.5	24.5	8.5	Rc1/8	52	57	24	5.5	9 Counterbore Depth 5.5	69	M6 Depth 11	10	41	25	40	5	44	4	25	24	10	15	28	9
● $\phi 50$	82	54	24.5	10.5	Rc1/4	64	71	33	6.9	11 Counterbore Depth 6.5	86	M8 Depth 13	15	50	30	50	7	56	4	25	28	12	15	28	10


Note: For dimensions with each switch, please refer to P. 984.

Internal Structure / Materials

● STK-JY-20



● STK-JY-32/40/50



Part No.	Part Name	Material	Remarks	Part No.	Part Name	Material	Remarks
1	Piston Rod	Stainless Steel	Industrial Hard Chrome Plating	13	Cushion rubber (H)	Urethane Rubber	
2	Bushing	Bearing Alloy		14	Stainless Steel	Stainless Steel	
3	Rod Cover	Aluminum Alloy	Alumite	15	Plug	Stainless Steel	
4	Rod Packing	Nitrile Rubber		16	Cylinder Body	Aluminum Alloy	Hard Anodized
5	Hexagon Socket Set Screw	Steel	Black Oxide	17	Cover	$\phi 20$ : Steel $\phi 32$ to $\phi 50$ : Aluminum Alloy	$\phi 20$ : Zinc plating $\phi 32$ to $\phi 50$ : Anodized
6	Metal gasket	Nitrile Rubber		18	Roller	Resin	
7	Cushion rubber (R)	Urethane Rubber		19	Spring Pin	Steel	
8	Spacer	Aluminum Alloy	Chromate	20	Non-rotating spacer	Steel	Nickel Plating
9	Magnet	Plastic		21	Hexagon Socket Set Screw	Steel	Black Oxide
10	Piston Packing	Nitrile Rubber		22	Coil Spring	Piano Wire	Electrodeposition Coating
11	Piston	Aluminum Alloy	Chromate				
12	Wear Ring	Polyacetal					

For maintenance parts, please visit the CKD Equipment Product Site  
(<https://www.ckd.co.jp/kiki/en/>) → "model No." → Maintenance Parts .

Special

Special

MVC

MVC

STK

STK

MCP

MCP

GLC

GLC

BBS

BBS

NHS

NHS

HR

HR

LN

LN

Cylinder Switch

Cylinder Switch

Ending


Ending



Stopper Cylinder, Double Acting, Spring Loaded Type,  
Rod End Shape Roller Type

# STK-JY1 Series

● Bore Size:  $\phi 20$ ,  $\phi 32$ ,  $\phi 40$ ,  $\phi 50$




Double Acting, spring loaded type




## Model No. Notation

Without Switch  
(Built-in magnet for switch)




With Switch  
(Built-in magnet for switch)



## 5 Number of Switches

Code	Content
R	With 1 pc on rod side
H	With 1 pc on head side
D	With 2 pcs

## Switch Single Unit Model No. Notation



### 1 Bore Size (mm)

Code	Content
20	$\phi 20$
32	$\phi 32$
40	$\phi 40$
50	$\phi 50$

### 2 Piping thread type

Code	Content
Blank	M5 ( $\phi 20$ ) Rc thread ( $\phi 32$ to $\phi 50$ )
NN	NPT thread ( $\phi 32$ or more) (Custom product)
GN	G thread ( $\phi 32$ or more) (Custom product)

### 3 Stroke (mm)

Bore Size	Stroke
$\phi 20$	10 to 20
$\phi 32$	10 to 20
$\phi 40$	20 to 30
$\phi 50$	20 to 30

Note: For Standard Stroke and minimum stroke with switch, please refer to P. 980.

### 4 Switch Model No. For switch details, refer to P. 1457. Switches are shipped with the product.

Contact	Indicator LED Special Function	Wiring (Output)	Load Voltage (V)		Load Current (mA)		Lead wire *1		Image		
			AC	DC	AC	DC	Straight	L-shape			
Solid State	1-Color	2-wire	85 to 265	—	5 to 100	—	T1H□	T1V□			
			—	10 to 30	—	5 to 20 *2	T2H□	T2V□			
		3-wire (NPN)	—	30 or less	—	100 or less	T3H□	T3V□			
			3-wire (PNP)	—	30 or less	—	50 or less	T3PH□		T3PV□	
		2-Color	2-wire	—	24 ± 10%	—	5 to 20	T2WH□	T2WV□		
				3-wire (NPN)	—	30 or less	—	50 or less	T3WH□		T3WV□
	Reed	1-Color	2-wire	—	24 ± 10%	—	5 to 20	T2WLH□	T2WLV□		
				—	10 to 30	—	5 to 20 *2	T2JH□	T2JV□		
			Without Indicator Lamp	2-wire	—	10 to 30	—	5 to 20 *2	T2HR3	T2VR3	
					110	12/24	7 to 20	5 to 50	T0H□	T0V□	
1-Color	2-wire	110	5/12/24	20 or less	50 or less	T5H□	T5V□				
		110/220	12/24	7 to 20 / 7 to 10	5 to 50	T8H□	T8V□				

### \*Lead wire length, connector specification

Code	Content
Blank	1 m (Standard)
3	3 m (Option)
5	5 m (Option)
W	M8 Connector, 1PIN (+), 4PIN (-) Lead Wire 0.3 m

\*5: Only T2WLH and T2WLV can be selected.

### Example) Lead wire length

1 m TOH  
3 m TOH<sub>3</sub>  
5 m TOH<sub>5</sub>

\*1: For "□" in the switch Model No., enter the code selected from the "Lead wire length, connector specification" table.

\*2: The maximum load current value above, 20 mA, is at 25°C. If the switch operating Ambient Temperature is higher than 25°C, it will be lower than 20 mA. (At 60°C, it will be 5 to 10 mA.)

\*3: This does not guarantee the water resistance of the cylinder.

\*4: Switches other than the Model No. listed above are also available. (Custom Product) For details, refer to P. 1457.

Specifications

Item	STK-JY1			
Bore Size mm	ø20	ø32	ø40	ø50
Operation type	Double Acting spring loaded type			
Operating Fluid	Compressed Air			
Max Operating Pressure MPa	1.0			
Min Operating Pressure MPa	0.22	0.12		
Proof Pressure MPa	1.6			
Ambient Temperature °C	-10 to 60 (however, no freezing)			
Port Size	M5	Rc1/8	Rc1/4	
Stroke tolerance mm	+2.0 0			
Operating Piston Speed mm/s	50 to 500			
Cushion	With Rubber Cushion			
Lubrication	Not required (Use Turbine Oil Class 1 ISO VG32 if lubricated)			
Rod End shape	Roller type			
Allowable Absorbed Energy J	Refer to P. 986.			

Cylinder Weight Table

(Unit: g)

Stroke Bore Size	10	15	20	25	30	Switch Weight (Grommet)
ø20	225	240	254	—	—	Refer to the mass listed in the Switch Specifications on P. 1457.
ø32	482	507	532	—	—	
ø40	-	—	862	903	944	
ø50	-	—	1362	1388	1414	

Theoretical Thrust Table

(Unit: N)

Bore Size (mm)	Operating Direction	Operating Pressure MPa									
		0.15	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
ø20	Push	-	-	94.2	1.26×10 <sup>2</sup>	1.57×10 <sup>2</sup>	1.88×10 <sup>2</sup>	2.20×10 <sup>2</sup>	2.51×10 <sup>2</sup>	2.83×10 <sup>2</sup>	3.14×10 <sup>2</sup>
	Pull	-	-	45.6	65.7	85.8	1.06×10 <sup>2</sup>	1.26×10 <sup>2</sup>	1.46×10 <sup>2</sup>	1.66×10 <sup>2</sup>	1.86×10 <sup>2</sup>
ø32	Push	1.21×10 <sup>2</sup>	1.61×10 <sup>2</sup>	2.41×10 <sup>2</sup>	3.22×10 <sup>2</sup>	4.02×10 <sup>2</sup>	4.83×10 <sup>2</sup>	5.63×10 <sup>2</sup>	6.43×10 <sup>2</sup>	7.24×10 <sup>2</sup>	8.04×10 <sup>2</sup>
	Pull	42.1	66.6	1.16×10 <sup>2</sup>	1.65×10 <sup>2</sup>	2.14×10 <sup>2</sup>	2.63×10 <sup>2</sup>	3.12×10 <sup>2</sup>	3.61×10 <sup>2</sup>	4.10×10 <sup>2</sup>	4.59×10 <sup>2</sup>
ø40	Push	1.88×10 <sup>2</sup>	2.51×10 <sup>2</sup>	3.77×10 <sup>2</sup>	5.03×10 <sup>2</sup>	6.28×10 <sup>2</sup>	7.54×10 <sup>2</sup>	8.80×10 <sup>2</sup>	1.01×10 <sup>3</sup>	1.13×10 <sup>3</sup>	1.26×10 <sup>3</sup>
	Pull	70.5	1.09×10 <sup>2</sup>	1.85×10 <sup>2</sup>	2.62×10 <sup>2</sup>	3.38×10 <sup>2</sup>	4.15×10 <sup>2</sup>	4.92×10 <sup>2</sup>	5.68×10 <sup>2</sup>	6.45×10 <sup>2</sup>	7.21×10 <sup>2</sup>
ø50	Push	2.95×10 <sup>2</sup>	3.93×10 <sup>2</sup>	5.89×10 <sup>2</sup>	7.85×10 <sup>2</sup>	9.82×10 <sup>2</sup>	1.18×10 <sup>3</sup>	1.37×10 <sup>3</sup>	1.57×10 <sup>3</sup>	1.77×10 <sup>3</sup>	1.96×10 <sup>3</sup>
	Pull	1.04×10 <sup>2</sup>	1.67×10 <sup>2</sup>	2.92×10 <sup>2</sup>	4.18×10 <sup>2</sup>	5.44×10 <sup>2</sup>	6.69×10 <sup>2</sup>	7.95×10 <sup>2</sup>	9.21×10 <sup>2</sup>	1.05×10 <sup>3</sup>	1.17×10 <sup>3</sup>

Stroke

Bore Size (mm)	Stroke (mm)	Max Stroke (mm)	Min Stroke (mm)	Min stroke with switch (mm)	
				T2WL	Other switches
ø20	10, 15, 20	20	10	20	10
ø32					
ø40	20, 25, 30	30	20	20	20
ø50					

Note: Strokes other than Standard Strokes are custom products.


Spring Load

(Unit: N)

Bore Size (mm)	Stroke (mm)	At 0 Stroke	At Full Stroke Operation
ø20	10	11.5	14.7
	15	9.9	
	20	8.2	
ø32	10	24.5	31.4
	15	21.1	
	20	17.6	
ø40	20	29.0	44.4
	25	25.3	
	30	21.5	
ø50	20	55.4	84.8
	25	48.0	
	30	40.7	


Dimensional Drawings

● STK-JY1-20



Note: For dimensions with each switch, please refer to P. 984.

● STK-JY1-32/40/50




Code	A	B	C	D	EE	F	G	H	I	J	K	KA	L	M	MM	N	O	P	Q	R	S	T	U	V	W
ø32	68	48	20	8	Rc1/8	45	49.5	24	5.5	8 Counterbore Depth 5.5	60	M6 Depth 11	10	32	20	34	4.5	36	3	19	18	8	13	20	8
ø40	80.5	52.5	24.5	8.5	Rc1/8	52	57	24	5.5	9 Counterbore Depth 5.5	69	M6 Depth 11	10	41	25	40	5	44	4	25	24	10	15	28	9
ø50	82	54	24.5	10.5	Rc1/4	64	71	33	6.9	11 Counterbore Depth 6.5	86	M8 Depth 13	15	50	30	50	7	56	4	25	28	12	15	28	10


Note: For dimensions with each switch, please refer to P. 984.

Internal Structure / Materials

● STK-JY1-20



● STK-JY1-32/40/50




Part No.	Part Name	Material	Remarks	Part No.	Part Name	Material	Remarks
1	Piston Rod	Stainless Steel	Industrial Hard Chrome Plating	12	Wear Ring	Polyacetal	
2	Bushing	Bearing Alloy		13	Cushion rubber (H)	Urethane Rubber	
3	Rod Cover	Aluminum Alloy	Alumite	14	Cylinder Body	Aluminum Alloy	Hard Anodized
4	Rod Packing	Nitrile Rubber		15	Cover	ø20: Steel ø32 to 50: Aluminum Alloy	ø20: Zinc plating ø32 to ø50: Anodized
5	Hexagon Socket Set Screw	Steel	Black Oxide	16	Non-rotating spacer	Steel	Nickel Plating
6	Metal gasket	Nitrile Rubber		17	Hexagon Socket Set Screw	Steel	Black Oxide
7	Cushion rubber (R)	Urethane Rubber		18	Coil Spring	Piano Wire	Electrodeposition Coating
8	Spacer	Aluminum Alloy	Chromate	19	Roller	Resin	
9	Magnet	Plastic		20	Spring Pin	Steel	
10	Piston Packing	Nitrile Rubber					
11	Piston	Aluminum Alloy	Chromate				

For maintenance parts, please visit the CKD Equipment Product Site  
(<https://www.ckd.co.jp/kiki/en/>) → "model No." → Maintenance Parts.

STK Series External Dimensions Diagram with Switch


● T0, T5, T2, T3, T3P, T2□R3, T2W, T3W, T2WL



Code	STK, STK-M								STK-Y□, STK-MY□, STK-JY□							
	T0, T5, T2, T3, T3P, T2□R3				T2W, T3W, T2WL				T0, T5, T2, T3, T3P, T2□R3				T2W, T3W, T2WL			
Bore Size (mm)	FA	FB	RD	HD	FA	FB	RD	HD	FA	FB	RD	HD	FA	FB	RD	HD
ø20	18.5	12.5	21	5.5	18.5	12.5	23	7.5	18.5	12.5	19.5	7	18.5	12.5	21.5	9
ø32	23	20.5	21	9.5	23	20.5	23	11.5	23	20.5	20	10.5	23	20.5	22	12.5
ø40	26.5	27.5	24	10.5	26.5	27.5	26	12.5	26.5	27.5	23	11.5	26.5	27.5	25	15
ø50	32.5	28.5	24	11.5	32.5	28.5	26	13.5	32.5	28.5	23	12.5	32.5	28.5	25	14.5

Note: For switch mountability, refer to the Model No. display method for each variation.

● T8, T2J, T1, T2YD, T2YDT



[For T8, T2J]

[For T1, T2YD, T2YDT]

Code	STK, STK-M											
	T8				T2J				T1, T2YD, T2YDT			
Bore Size (mm)	FA	FB	RD	HD	FA	FB	RD	HD	FA	FB	RD	HD
ø20	24.3	16	15	0	24.3	16	20	4.5	29.3	16	20	4.5
ø32	28.8	24	15	3.5	28.8	24	20	8.5	33.8	24	20	8.5
ø40	32.3	31	18	4.5	32.3	31	23	9.5	37.3	31	23	9.5
ø50	38.3	32	18	5.5	38.3	32	23	10.5	43.3	32	23	10.5

Code	STK-Y□, STK-MY□, STK-JY□											
	T8				T2J				T1, T2YD, T2YDT			
Bore Size (mm)	FA	FB	RD	HD	FA	FB	RD	HD	FA	FB	RD	HD
ø20	24.3	16	13.5	1	24.3	16	18.5	6	29.3	16	18.5	6
ø32	28.8	24	14	4.5	28.8	24	19	9.5	33.8	24	19	9.5
ø40	32.3	31	17	5.5	32.3	31	22	10.5	37.3	31	22	10.5
ø50	38.3	32	17	6.5	38.3	32	22	11.5	43.3	32	22	11.5

Note: For switch mountability, refer to the Model No. display method for each variation.


Mounting Bolt Model No.

Mounting Bolt Model No.

**STK - BOLT - M5×60**

Mounting bolts (Bolts are a set of 4.)

How to read the list




Mounting bolt for STK-□

Model No.	ℓ	d×L
STK-20-10	10.5	M5×60
15		×65
20		×70
STK-32-10	12.5	M5×65
15		×70
20		×75

Model No.	ℓ	d×L
STK-40-20	13	M5×80
25		×85
30		×90
STK-50-20	12.5	M6×80
25		×85
30		×90

Stopper Cylinder Model Selection Guide

Allowable absorbed energy differs depending on the mounting method. Please check whether mounting is A or B in the diagram below and select accordingly.



1. Selection method for operating range

Select a model so that it is below the allowable absorbed energy in the graph on the right, based on the conveyed weight (m) and conveyance speed (V).

Formula for Kinetic Energy

$$E = \frac{1}{2} mV^2$$


E: Kinetic energy J  
m: Transport weight kg  
V: Transport speed m/s

(Example) Conveyance speed 15 m/min, Conveyed weight 40 kg  
A. In case of rod side mounting


[How to Read the Graph]

To select the above specifications, find the intersection of the speed 15 m/min on the horizontal axis and the weight 40 kg on the vertical axis from graph Figure 1 on the upper right, and select STK-40 which is within the allowable absorbed energy range.

A. Rod side mounting



B. Head side mounting



(Note) Rod End shape: Applicable to all round bar, chamfered, and roller types.

Lateral load and Operating Pressure

Since the Operating Pressure during cylinder retraction varies depending on the magnitude of the lateral load applied to the Rod End, please calculate the necessary Operating Pressure according to the following steps.

1. Determine the lateral load (F) applied to the rod tip.

$$F = 10 \cdot m \cdot n \cdot \mu_1$$

F : Lateral load (N)

m : Transport weight (kg)

n : Quantity of transported items

$\mu_1$ : Coefficient of friction between transport pallet and conveyor

2. Determine the necessary thrust (P) during cylinder retraction.

$$P = F \cdot \mu_2$$


P : Required thrust (N)

$\mu_2$ : Coefficient of friction between transported item and rod

(Note) Since the coefficient of friction varies depending on the material of the conveyed object, refer to the coefficients in the table below.


Please consider.

Material of transported item	Steel	Aluminum	Urethane
$\mu_2$	0.5	0.8	2.0




Allowable Lateral Load (Unit: N)

Bore Size	Stroke				
	10	15	20	25	30
ø20	106.5	99.4	93.2	—	—
ø32	272.8	254.6	238.7	—	—
ø40	-	—	371.3	352.1	334.8
ø50	-	—	582.8	552.8	525.8



3. Determine the Operating Pressure from the necessary thrust (P) from Figure 3.



Special

MVC

STK

MCP

GLC

BBS

NHS

HR

LN

Cylinder Switch

Ending

Special

MVC

STK

MCP

GLC

BBS

NHS

HR

LN

Cylinder Switch

Ending



# To Use This Product Safely

Be sure to read this before use. For general cylinder information, see Intro 41, and for Cylinder Switches, see P. 1512.

## Individual Precautions: Stopper cylinder STK Series

### Design / Selection

#### 1. Common


##### CAUTION

■ When using a stopper cylinder to brake loads directly connected to cylinder, etc

- The specified range is only for stopping pallets on the conveyor. When stopping a load directly connected to a cylinder, etc. with a stopper cylinder, the cylinder thrust becomes a lateral load, so please select a cylinder so that it is within the range of allowable absorbed energy and allowable lateral load.


■ If there is a magnetic body such as an iron plate near the cylinder switch, it will cause a malfunction, so please keep a distance of 10 mm or more from the cylinder surface.

(Common to all Bore Sizes)




■ The cylinder switch could malfunction if cylinders are installed adjacently. Check that the following distances are allocated between cylinders.

(Common to all Bore Sizes)



■ There are restrictions on usable piping fittings. Refer to the following and use accordingly.



Item Bore Size (mm)	Port Size	Port position dimension		Usable Fittings	Fitting outer diameter øC	Unusable fittings
		A	B			
ø20	M5	8	5.5	SC3W-M5-4 SC3W-M5-6 GWS4-M5-S GWS4-M5 GWL4-M5 GWL6-M5	ø11 or less	GWS6-M5
		8	8	SC3W-6-4/6/8 GWS4-6 GWS6-6 GWS8-6 GWL4-6 GWL6-6		
ø32	Rc1/8	12	8.5	SC3W-8-6/8/10 GWS4-8 GWS6-8 GWS10-8 GWL4 to 12-8	ø15 or less	GWS10-6 GWL-8-6 GWL10-6
ø40		10.5	10.5			
ø50	Rc1/4	10.5	10.5		ø21 or less	GWS-12-8

#### 2. Single Acting type STK-Y

##### CAUTION

■ Do not apply pressure from the head side for the Single Acting type.

- If air is introduced for the head side for Single Acting, air leakage will occur.

■ Do not leave Single Acting cylinders pressurized. If left pressurized, the Piston Rod may not return by spring force when the pressure is released.

#### 3. Double Acting type with spring STK-Y1

##### CAUTION

■ Spring integrated Double Acting is usually used as a Double Acting. When the air is shut off for any reason, the rod is Push and the stopper function is maintained.

#### 4. Rod End shape chamfered type with female thread STK-M-N11

##### CAUTION

■ Avoid using the product so as to apply rotation torque to the Piston Rod.

The non-rotating spacer may come off and the orientation of the chamfered Piston Rod may change.

### During Use

#### 1. Common

##### CAUTION

■ Do not apply rotation torque to the Piston Rod. Install the Piston Rod so that its contact surface is parallel to the pallet contact surface to avoid applying rotational torque.

■ Avoid using oil, etc., for the Piston Rod sliding section.


- Otherwise, cylinder malfunctions, etc., may result.

■ When changing the direction of the rotation-stop type, loosen the rod cover Set Screws (3 positions) to change position arbitrarily and then tighten them again.

#### 2. Rod End shape chamfered type with female thread STK-M-N11

##### CAUTION

■ When fixing a workpiece onto the end of the Piston Rod, push the Piston Rod to the stroke end and apply a wrench to the section projecting from the rod's parallel section. Be careful when tightening so that torque is not applied to the Cylinder Body.



For precautions during mounting, installation, adjustment, use, and maintenance, refer to "During Use" in this catalog and the CKD Components Product website (<https://www.ckd.co.jp/kiki/en/>) -> "Model No." -> [Instruction Manual](#).